

3M

Thermal Transfer Polyester

Label Material

7876

Technical Data

May 2017

Product Description	3M™ Thermal Transfer Polyester Label Material 7876 is a clear polyester label material that offers premium durability and moisture resistance. This label product utilizes 3M™ High Performance Acrylic Adhesive 350, it offers excellent chemical resistance and holding strength even at high temperatures.
---------------------	---

Construction

Facestock	Adhesive	Liner
.2in. Clear Polyester Gloss TC (51 microns)	350 Acrylic 1.8 mils (46 microns)	55# Densified Kraft 3.2 mils (81 microns)

(Calipers are nominal values.)

Features

- Facestock is topcoated for thermal transfer printing. Resin ribbons are recommended for optimum durability. The topcoat also provides improved ink anchorage for traditional forms of press printing.
- Adhesive can permanently bond to high surface energy (HSE) and low surface energy (LSE) plastics, textured and contoured surfaces, powder coatings, and slightly oily metals.
- Thick adhesive caliper provides for stronger bond on textured surfaces.
- 55# densified kraft liner assures consistent die cutting.
- UL recognized (File MH16411) and CSA accepted (File 99316). See the UL and CSA listings for details.
- UL listing includes approval for use on powder coated surfaces.

Application Ideas

- Barcode labels and rating plates
- Property identification and asset labeling
- Warning, instruction, and service labels for durable goods
- Nameplates and durable goods

3M™ Thermal Transfer Polyester Label Material

7876

Typical Physical Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Adhesive Coat Weight	2.70 to 3.24 g/100 in. ²	TM-2279
Release Range	5 to 70 g/2 in.	TLMI Method, 180° removal, 300 in./min.
Service Temperature	-40°F to 257°F (-40°C to 125°C)	
Minimum Application Temperature	50°F (5°C)	
Convertability	In order to capture the superior performance properties of 3M™ High Holding Acrylic Adhesive 350, thicker calipers are utilized for LSE or textured substrates. Its higher caliper, while desirable for the end use applications, may require extra care during processing. Please refer to the die cutting/converting section of this data page or the “Guide to Converting and Handling Label Products” technical bulletin for additional information.	

Typical Peel Adhesion Properties

Adhesion: 180° peel test procedure is ASTM D 3330
90° peel test procedure is ASTM D 3330 modified for the angle change

	Initial (10 Minute Dwell/RT)				Conditioned for 3 Days at Room Temperature 72°F (22°C)			
	180° Peel		90° Peel		180° Peel		90° Peel	
Surface	Oz./In.	N/100	Oz./In.	N/100	Oz./In.	N/100	Oz./In.	N/100
Stainless Steel	79	88	56	61	90	98	78	85
Polycarbonate	81	89	61	67	88	94	67	73
Polypropylene	65	71	30	33	74	81	29	32
Glass	83	91	65	71	89	97	75	82
HD Polyethylene	46	50	28	31	51	56	32	35
LD Polyethylene	46	50	29	32	49	54	35	38
Smooth Powder Coating*	73	80	48	52	77	84	50	55
Finely Textured Powder Coating*	42	46	27	30	44	46	26	28

	Conditioned for 3 Days at 120F (49°C)				Conditioned for 24 hours at 90°F (32°C) at 90% Relative Humidity			
	180° Peel		90° Peel		180° Peel		90° Peel	
Surface	Oz./In.	N/100 mm	Oz./In.	N/100 mm	Oz./In.	N/100 mm	Oz./In.	N/100 mm
Stainless Steel	97	106	94	103	93	102	80	88
Polycarbonate	63	69	33	36	68	74	57	62
Polypropylene	79	86	34	37	68	74	42	46
Glass	96	105	83	91	80	88	70	77
HD Polyethylene	48	52	30	33	42	46	37	40
LD Polyethylene	14	15	13	14	38	42	38	42
Smooth Powder Coating*	83	91	60	66	77	84	58	63
Finely Textured Powder Coating*	49	54	33	36	45	49	28	31

*Calculated using averages of different powder coated surfaces.

3M™ Thermal Transfer Polyester Label Material

7876

Environmental Performance

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

The properties defined are based on four hour immersions at room temperature (72°F/22°C) unless otherwise noted. Samples were applied to stainless steel panels 24 hours prior to immersion and were evaluated one hour after removal from the solution for peel adhesion. Adhesion measured at 180° peel angle (ASTM D 3330) at 12 inches/minute.

Chemical Resistance:

Chemical	Adhesion to Stainless Steel		Appearance	Edge Penetration
	Oz./in.	N/100 mm	Visual	Millimeters
Isopropyl Alcohol	82	90	No change	0.9
Detergent 1% Alconox® Cleaner	85	93	No change	0.8
Engine Oil (10W30) @ 250°F (121°C)	96	105	No change	0.6
Water for 48 hours	61	67	No change	0.3
pH 4	79	86	No change	0.4
pH 10	74	81	No change	0.8
Formula 409® Cleaner	82	90	No change	0.9
Toluene	41	45	No change	6.3
Acetone	52	57	No change	5.6
Brake Fluid	85	93	No change	0.1
Gasoline	50	55	No change	4.8
Diesel Fuel	80	88	No change	0.8
Mineral Spirits	66	74	No change	2.4
Hydraulic Fluid	83	91	No change	0.0

Temperature Resistance:

300°F (149°C) for 24 hours: Some yellowing of facestock

-40°F (-40°C) for 10 days: No significant visual change

Humidity Resistance:

24 hours at 100°F (38°C) and 100% relative humidity: No significant change in appearance or adhesion

Accelerated Aging:

ASTM D 3611:96 hours at 150°F (65°C) and 80% relative humidity

	Rate of Removal	Grams/Inch Width	N/100 mm
180° Removal of Liner from Facestock	90 inches/minute	13	0.50
	Rate of Removal	Grams/Inch Width	N/100 mm
180° Peel Adhesion from Stainless Steel	12 inches/minute	76	83

3M™ Thermal Transfer Polyester Label Material

7876

Application Techniques

For maximum bond strength, the surface should be clean and dry. Typical cleaning solvents are heptane and isopropyl alcohol.*

For best bonding conditions, application surface should be at room temperature or higher. Low temperature surfaces, below 50°F (10°C), can cause the adhesive to become so firm that it will not develop maximum contact with the substrate. Higher initial bonds can be achieved through increased rubdown pressure.

*When using solvents, read and follow the manufacturer's precautions and directions for use.

Printing

Facestock is topcoated for improved ink receptivity and is designed for thermal transfer printing. It is printable by all standard roll processing methods including flexography, hot stamp, letterpress, and screen printing. Refer to UL Listing for specific ribbons.

Die Cutting / Converting

Rotary die cutting is recommended. Fanfolding of labels is not recommended. Small labels should be evaluated carefully. Winding tensions should be kept at a minimum to help prevent the adhesive from oozing.

Packaging

Finished labels should be stored in plastic bags.

3M™ Thermal Transfer Polyester Label Material

7876

Storage	Store at room temperature conditions of 72°F (22°C) and 50% relative humidity.
Shelf Life	If stored under proper conditions, product retains its performance and properties for two years from date of manufacture.
Technical Information	The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.
Product Selection and Use	Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.
Warranty, Limited Remedy and Disclaimer	Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.
Limitation of Liability	Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

ISO 9001

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.



Industrial Adhesives and Tapes Division
Converter Markets
3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550
3M.com/converter

3M is a trademark of 3M Company. Alconox is a registered trademark of Alconox, Inc. Formula 409 Cleaner is a registered trademark of Clorox, Inc.
©3M 2017 E 70-0709-4633-3 (5/17)