



# Scotch-Weld™

## Structural Plastic Adhesives

### DP8010 Blue • DP8010NS Blue

#### Technical Data Sheet

February, 2016

#### Product Description

3M™ Scotch-Weld™ Structural Plastic Adhesive DP8010 Blue and DP8010NS Blue are two-part, acrylic-based adhesives (10:1 ratio by volume) that can bond many low surface energy plastics, including many grades of Polypropylene, Polyethylene and TPO's *without special surface preparation*.

These adhesives can replace screws, rivets, plastic welding, and two-step processes which include chemical etchants, priming or surface treatments in many applications.

#### Features

- Ability to structurally bond polyolefins without special surface preparation
- Regular and Non-Sag Formulations
- Excellent water and humidity resistance
- One step process; no pre-treatment of polyolefin substrates necessary
- Convenient hand-held applicator
- Ability to bond dissimilar Substrates
- Room temperature cure
- Very good chemical resistance
- Solvent-free adhesive system
- Available in bulk

#### Typical Uncured Properties

**Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes. Unless otherwise indicated, all properties measured at 22°C (72°F)**

Property		3M™ Scotch-Weld™ Structural Plastic Adhesive DP8010 Blue	3M™ Scotch-Weld™ Structural Plastic Adhesive DP8010NS Blue
Colour	Base (B)	Off-white	
	Accelerator (A)	Blue	
Viscosity <sup>1</sup>	Base (B)	27,000 cP	64,000 cP
	Accelerator (A)	17,000 – 40,000 cP	
Density	Base (B)	8.5 lb/gal	
	Accelerator (A)	8.3 – 8.7 lb/gal	
Mix ratio	By volume	10:1	
	By weight	10:1	
Work life <sup>2</sup>		Approx. 8 minutes	
Open time <sup>3</sup>		10 minutes	
Skin Time <sup>4</sup>		Approximately 3 minutes (See Below)	
Time to handling strength <sup>5</sup>		60 minutes	

1. Viscosity measured using Brookfield RTV, spindle #7, 20 RPM @ 27°C (80°F)
2. Maximum time that adhesive can remain in a static mixing nozzle and still be expelled without undue force on the applicator.
3. Maximum time allowed after applying adhesive to one substrate before bond must be closed and fixed in place.
4. An open bead line will show some skinning in approximately 3 minutes. It is possible to bond parts with good strength if the parts are made within 10 minutes. Therefore, the adhesive has a 10 minute open time for making bonds.
5. Minimum time required to achieve 50 psi of overlap shear strength, measured on HDPE

**Note: The data in this sheet were generated using the 3M™ EPX Applicator System equipped with an EPX static mixer, according to manufacturer's directions. Thorough hand-mixing will afford comparable results.**

# 3M™ Scotch-Weld™

## Structural Plastic Adhesive

DP8010 Blue • DP8010NS Blue

**Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes. Unless otherwise indicated, all properties measured at 22°C (72°F)**

### Typical Mixed Properties

Property	3M™ Scotch-Weld™ Structural Plastic Adhesive DP8010 Blue	3M™ Scotch-Weld™ Structural Plastic Adhesive DP8010 Blue
Colour	Blue-Green	
Full cure time	24 hours	
Dispense Viscosity 23°C (73°F)	25,000 cP	64,000 cP

### Typical Cured Physical Properties

Property	3M™ Scotch-Weld™ Structural Plastic Adhesive DP8010 Blue
<b>Physical</b> Shore D Hardness Storage Modulus (DMA) Tensile Strength (ASTM D638) Tensile Modulus (ASTM D638) Strain at Break (ASTM D638)	55-60 970 MPa 1300 PSI 77,000 PSI 90%
<b>Thermal</b> Tg (Glass Transition Temperature) (DMA)  Coefficient of Thermal Expansion (in/in/°C) Below Tg Above Tg	61°C  116 245
<b>Electrical</b> Dielectric Strength (ASTM D 149) Volume Resistivity (ASTM D 257) Surface Resistivity (ASTM D257) Dielectric Constant (ASTM D150) Dissipation Factor (ASTM D150)	603 V/mil 4.10E+11 (Ω-cm) 8.00E+10 (Ω) 4.36 at 1 KHz 0.068 at 1 KHz

# 3M™ Scotch-Weld™

## Structural Plastic Adhesive

DP8010 Blue • DP8010NS Blue

Typical Cured  
Physical  
Properties  
(continued)

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Overlap Shear (psi)<sup>7</sup>, ASTM D1002

Substrate	3M™ Scotch-Weld™ Structural Plastic Adhesive DP8010 Blue	3M™ Scotch-Weld™ Structural Plastic Adhesive DP8010NS Blue
Aluminum (MEK/abrade/MEK)	1960 CF	1780 CF
Cold-rolled steel (MEK/abrade/MEK)	1800 CF	1870 CF
Stainless Steel (MEK/abrade/MEK)	1820 CF	1990 CF
Copper (MEK/abrade/MEK)	1870 CF	1500 CF
Galvanized steel (MEK/abrade/MEK)	1330 CF	840 mixed
PP (IPA wipe)	1150 SF	1150 SF
LDPE (IPA wipe)	360 SF	360 SF
HDPE (IPA wipe)	1040 SF	1100 SF
UHMW-PE (IPA wipe)	770 CF	750 SF
Gelcoat (fibreglass--smooth side)	900 SF	1100 SF
Acrylic	1100 SF	1190 SF
PVC	1730 SF	1740 SF
PC	760 AF	740 AF
ABS	1250 SF	1240 SF
Polystyrene (HIPS)	580 SF	570 SF
FRP (Epoxy)	2830 CF	2860 CF
Acetal	90 AF	70 AF
SMC (Fibreglass--rough side)	760 SF	800 SF
Glass	530 SF	670 SF
PTFE (IPA/abrade/IPA)	320 AF	360 AF

Overlap Shear (psi); Etched Aluminum, at Temperature<sup>7</sup>, ASTM D1002

Temperature	3M™ Scotch-Weld™ Structural Plastic Adhesive DP8010 Blue	3M™ Scotch-Weld™ Structural Plastic Adhesive DP8010NS Blue
-29°C (-20°F)	2000 mixed	2000 mixed
23°C (73°F)	1800 CF	1700 CF
49°C (120°F)	1000 mixed	700 mixed
66°C (150°F)	450 AF	340 AF
82°C (180°F)	300 AF	100 AF

7. Overlap shear values measured using ASTM D1002; adhesives allowed to cure for 7 days at room temperature; ½" overlap; 0.008" bond line thickness; samples pulled at 0.1 in/min for metals and 2 in/min for plastics; all surfaces prepared with light abrasion and solvent clean; substrates used were 1/16" thick aluminum and 1/8" thick plastics; failure modes: AF: adhesive failure CF: cohesive failure SF: substrate failure mixed: AF/CF

# 3M™ Scotch-Weld™

## Structural Plastic Adhesive

DP8010 Blue • DP8010NS Blue

**Typical Cured  
Physical  
Properties  
(continued)**

**Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.**

**Environmental Resistance<sup>8</sup> Expressed as Percent Retention of Control Strength  
(Measured on 1/8" thick HDPE via Overlap Shear, ASTM D1002)**

Condition	Substrate	3M™ Scotch-Weld™ Structural Plastic Adhesive DP8010 Blue	3M™ Scotch-Weld™ Structural Plastic Adhesive DP8010NS Blue
Control	HDPE	100% SF	100 % SF
71°C water soak		80% CF	80% CF
66°C/80% RH		95% CF	97% CF
NaOH 10% by wt		100% SF/CF	100% SF
HCl 16% by volume		100% SF	100% SF/CF
IPA soak		95% CF	91% CF
Diesel Fuel soak		97% SF/CF	93% SF
50% Antifreeze soak		100% SF/CF	100% SF
Gasoline soak		70% CF	70% CF
Acetone soak		20% AF	25% AF

8. Values indicate overlap shear test performance retained after 14 days of continuous exposure relative to a control sample left at room temperature; samples conditioned for 7 days at room temperature and 50% relative humidity prior to tests.

**Floating Roller Peel (lb/inch width)<sup>9</sup> ASTM D3167**

Substrate	3M™ Scotch-Weld™ Structural Plastic Adhesive DP8010 Blue and 3M™ Scotch-Weld™ Structural Plastic Adhesive DP8010NS Blue
HDPE	Substrate Failure

<sup>9</sup>Floating roller peel values measured using ASTM D3167; allowed to cure for 24 hours at room temperature; 1" wide samples; 0.017" bond line thickness; samples pulled at 20 in/min. Flexible HDPE was 1mm thick and rigid HDPE was 4.8mm thick.

AF: adhesive failure CF: cohesive failure SF: substrate failure

**Directions  
For Use**

- To obtain the highest strength structural bonds, paint, oxide films, oils, dust, mold release agents, and all other surface contaminants must be completely removed. The amount of surface preparation depends on the required bond strength and environmental aging resistance desired by user. For suggested surface preparations on common substrates, see the section on surface preparation.
- Mixing  
**For Duo-Pak Cartridges**  
Store cartridges with cap end up to allow any air bubbles to rise towards the tip. To use, simply insert the cartridge into the EPX applicator and start the plunger into the cylinders using light pressure on the trigger. Then remove the cap and expel a small amount of adhesive to ensure material flows freely from both sides of cartridge. For automatic mixing, attach an EPX mixing nozzle to the cartridge and begin dispensing the adhesive. For hand mixing, expel the desired amount of adhesive and mix thoroughly. Mix approximately 15 seconds after obtaining a uniform colour.

# 3M™ Scotch-Weld™

## Structural Plastic Adhesive

DP8010 Blue • DP8010NS Blue

---

### Directions For Use (continued)

#### For Bulk Containers

Mix thoroughly by weight or volume in the proportion specified on the product label or in the typical uncured properties section. Mix approximately 15 seconds after obtaining a uniform colour.

3. Apply adhesive and join surfaces within the open time listed for the specific product. Larger quantities and/or higher temperatures will reduce this working time.
4. Allow adhesive to cure at 16°C (60°F) or above until completely firm. Applying heat up to 66°C (150°F) will increase cure speed.
5. Keep parts from moving during cure. Apply contact pressure or fixture in place if necessary. Optimum bond line thickness ranges from 0.005 to 0.020 inch; shear strength will be maximized with thinner bond lines, while peel strength reaches a maximum with thicker bond lines.
6. Excess uncured adhesive can be cleaned up with ketone type solvents.\*

**\*Note: When using solvents, extinguish all ignition sources, including pilot lights, and follow the manufacturer's precautions and directions for use.**

---

### Surface Preparation

3M™ Scotch-Weld™ Structural Plastic Adhesives are designed to be used on metal, wood, and most plastic surfaces. The following cleaning methods are suggested for common surfaces:

#### Steel:

1. Wipe free of dust and dirt with pure solvent such as acetone or isopropyl alcohol.\*
2. Sandblast or abrade using clean fine grit abrasives.
3. Wipe again with clean solvent to remove loose particles.\*

#### Aluminum:

1. Wipe free of dust and dirt with pure solvent such as acetone or isopropyl alcohol.\*
2. Sandblast or abrade using clean fine grit abrasives.
3. Wipe again with clean solvent to remove loose particles.\*
4. When using a primer, apply adhesive within 4 hours of primer application.

#### Plastics/Rubbers:

1. Wipe with isopropyl alcohol.\*
2. Abrade using fine grit abrasives.
3. Wipe with isopropyl alcohol.\*

#### Glass:

1. Solvent wipe surface using acetone or MEK.\*
2. Apply a thin coating of a silane adhesion promoter to the glass surfaces to be bonded and allow to dry completely before bonding.

**\*Note: When using solvents, extinguish all ignition sources, including pilot lights, and follow the manufacturer's precautions and directions for use.**

# 3M™ Scotch-Weld™

## Structural Plastic Adhesive

DP8010 Blue • DP8010NS Blue

---

**Storage** Store product at at 4°C (40°F). Do not freeze. Allow product to reach room temperature prior to use.

---

**Shelf Life** 3M™ Scotch-Weld™ Structural Plastic Adhesives have a shelf life of 6 months in unopened original containers kept at recommended storage conditions.

---

**Precautionary Information** Refer to Product Label and Material Safety Data Sheet for health and safety information before using this product. For additional health and safety information, call 1-800-364-3577 or 651-737-6501.

---

**For Additional Information** To request additional product information or to arrange for sales assistance, call toll free 1-800-362-3550 or visit [www.3M.com/structuraladhesives](http://www.3M.com/structuraladhesives).

---

**Product Use** All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.

---

**Warranty and Limited Remedy** Unless stated otherwise in 3M's product literature, packaging inserts or product packaging for individual products, 3M warrants that each 3M product meets the applicable specifications at the time 3M ships the product. Individual products may have additional or different warranties as stated on product literature, package inserts or product packages. 3M MAKES NO OTHER WARRANTIES OR CONDITION, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's application. If the 3M product is defective within the warranty period, your exclusive remedy and 3M's and seller's sole obligation will be, at 3M's option, to replace the product or refund the purchase

---

**Limitation of Liability** Except where prohibited by law, 3M and seller will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, (including lost profits) regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

---

ISO 9001

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.

---

**3M**

3M Industrial Adhesives and Tapes Division  
3M Canada  
London, ON N6A 4T1  
1-800-3M-HELPS  
[www.3M.ca](http://www.3M.ca)

3M and Scotch-Weld are trademarks of 3M. Used under license in Canada.  
© 2016, 3M. All rights reserved. BA-16-21007 160104559 E