

3M Science.
Applied to Life.™



**Lightweight & slim design -
delivering a world
of comfort to you.**

The balanced and compact 3M™ Versaflo™ TR-300+ Powered Air Respirator is the key to easy-to-use, versatile, respirator systems for particulate environments.

Introducing the New 3M™ Versaflo™ Powered Air Turbo TR-300+

The 3M™ Versaflo™ Powered Respirator System TR-300+ combines performance, protection and functionality with modern, stylish design and comfort. It is the key to easy-to-use, versatile, respiratory protection systems for particulate environments.

Features and Benefits:

Comfortable Airflow

- Two user selectable flow rates to maximise comfort: 185l/mn and 205l/mn
- Controlled airflow delivers steady flow as battery discharges or filter loads with particulates

Ease of Use

- Electronic audible and visual alarm in case of low battery and/or low air flow
- TR-300+ display shows battery charge status, particulate filter loading status during use as well as selected airflow
- Charge status is indicated by a useful LED display
- No user calibration of turbo required

Comfort

- Light and small - extremely slim, lightweight, balanced design for comfort

Multiple Applications

- High efficiency filter captures hazardous dust, mist and fume plus options for nuisance level gases and vapours
- IP53 rating. Suitable for use in decontamination shower

Safety

- Approved to EN 12941, TH2 or TH3 depending on headtop



Typical Applications

- Pharmaceutical manufacturing
- Food & beverage
- Woodworking
- Metal working
- Surface preparation
- Smelting

3M™ Versaflo™ Powered Air Turbo TR-302E+

This unit comes with an airflow indicator and spark arrestors (x2). To adapt to your type of environment see options below.

3M™ Versaflo™ Starter Kit TR-315E+

This Versaflo Starter Kit includes the TR-302E+ Turbo, particulate filter, pre-filter, spark arrestors (x2), standard belt, high capacity battery pack, battery charger kit (not shown on the picture below), self-adjusting breathing tube and airflow indicator.



Filter

- TR-3712E P
- TR-3802E P + Nuisance Level* Organic Vapour
- TR-3822E P + Nuisance Level* Acid Gas Filter (Hydrogen Fluoride up to 10 x Occupational Exposure Limit)

* Nuisance level refers to concentrations below the occupational exposure limit (OEL).

Batteries

- TR-330 Standard Battery
- TR-332 High Capacity Battery

Belts

- TR-325 Standard Belt
- TR-327 Easy-Clean Belt
- TR-326 Leather Belt

Spares & Accessories

- TR-3600 Pre-filter
- TR-971 Air Flow Indicator
- TR 371+ Filter Cover
- BPK-01 Backpack
- TR-362 Spark Arrestor
- TR-329 Braces
- TR-380 Filter Surround Gasket

Chargers

- TR-341E Single Station Battery Charger Kit
- TR-344E 4-Station Battery Charger Kit

Note: 3M does not accept responsibility or liability, direct or consequential, arising from reliance upon any information provided and the user should determine the suitability of the products for their intended use. Nothing in this statement will be deemed to exclude or restrict 3M's liability for death or personal injury arising from its negligence or fraudulent misrepresentation.



Personal Safety Division
 3M United Kingdom
 3M Centre
 Cain Road, Bracknell
 Berkshire, RG 12 8HT
 Tel: 0870 60 800 60
www.3M.eu/Versaflo



To find out how you can expand your world of comfort, scan this QR code with your smartphone or visit www.3M.eu/Versaflo.

Please recycle. Printed in the United Kingdom.
 ©2015 3M. All Rights Reserved.