



Science.
Applied to Life.™



3M™ Cleaning & Workplace Safety Supplies

Full Line Catalogue ANZ

Discover a world of affordable, smart cleaning equipment and supplies, backed by practical advice and technical know-how, to enhance your building and transform your business.

3M provides facility managers and contract cleaners with innovative, sustainable high-value solutions to help protect a building's life and enhance the performance and productivity of employees.

3M facilities care and cleaning solutions enhance protection, performance and productivity for the life of a building. Whether you need cleaning supplies or janitorial supplies, facility maintenance materials, or specialty items from floor mats to safety tapes and treads, 3M products deliver. We also provide industry-leading Scotch-Brite™ products for food services cleaning needs, from griddle cleaning to appliance cleaning, as well as food quality and food safety products.



Facility & Operations Managers

To help meet the important challenges faced by facilities managers, 3M develops innovative cleaning, and floor protection products that deliver measurable commercial benefits and sustainability advantages.

3M is committed to developing cleaning equipment and supplies that help lower your total maintenance costs. For example, floor care is not measured merely by the expense of cleaning and polishing floor pads, it also includes the cost and difficulty of effort, a measure of floor performance over time and the durability of products used.

Our wide range of cleaning equipment and supplies are designed to:

- ▶ Safely clean and protect your building, especially in visible high traffic areas
- ▶ Deliver quality results
- ▶ Provide superior cleaning performance
- ▶ Be truly cost effective, by lowering your total costs

Building Service Contractors

The key to running a successful cleaning business is the ability to provide outstanding services in a highly competitive environment. It requires hardworking, reliable and well-trained cleaners, backed by experienced cleaning supervisors—and the support of partners who understand what it takes to maintain a first class reputation.

3M has supported successful contract cleaning firms with innovative janitorial cleaning supplies and maintenance products and entrance and safety matting. 3M continuously innovates to create green cleaning products—making life easier for contract cleaners and helping you manage costs.



Health Care Environmental Services Professionals

For more than 50 years, 3M has offered our health care and education industry partners innovative facility cleaning and facility maintenance and safety solutions to help protect patients, students and staff while reducing overall costs and providing the highest return on investment. From floor safety products to disinfectant cleaners, 3M can help reduce illnesses in schools and healthcare-associated Infections (HAIs) in health care environments.

3M's goal is to provide healthy and clean environments. This is achieved by providing quality facility cleaning, maintenance and safety products, a thorough training curriculum, personnel documentation for regulatory compliance, and quality assurance programs. Specific products and programs have been designed to help educational facility and maintenance managers decrease labour costs and effectively train employees. 3M helps validate the efficacy and performance of your cleaning.



Food Service Professionals

The Scotch-Brite™ brand has been recognised as a leading restaurant cleaning supplies brand in the food service industry. The quality, durability and efficiency of Scotch-Brite™ cleaning products is why they have become a top choice for food services professionals around the world. Through innovation and technology, 3M continues to develop efficient and cost-effective products for your commercial kitchen cleaning needs.



Solutions for Architects

Being an Architect you just can't afford to specify materials in your designs that might let you down. It's really not worth compromising on product performance and reliability when you could be putting your reputation at risk. 3M understands this and the demands your clients place on you – the need for performance, durability and long-term cost effectiveness. For this reason most architects worldwide feel confident in specifying 3M products and solutions, and work with us to help develop new and innovative solutions for the next generation of sustainable and more efficient buildings.



Table of Contents

Hand Pads & Scourers	7	Floor Cleaning & Dusting Tools	26
Why choose 3M?	8	Doodlebug™ Pads	27
Applications	8	3M™ Doodlebug™ Holder & Pole 6472	27
Scotch-Brite™ White Cleaning Pad – 449 / 98 - Light Duty	9	3M™ Doodlebug™ Holder & Adaptor 6475	27
3M™ 230/ Niagara™ General Purpose - Economy Handpad	9	3M™ Doodlebug™ Cleaning System	27
Scotch-Brite™ General Purpose Scouring Pad 96 - Medium Duty	9	3M™ Doodlebug™ White Cleansing 8440 Pad – Light Duty	28
Scotch-Brite™ Green Scouring Pad 86 / 75 - Heavy Duty	9	3M™ Doodlebug™ Blue 8242 Pad – Medium Duty	28
Scotch-Brite™ Blue Pot 'n Pan Scourer - Extra Heavy Duty 88	10	3M™ Doodlebug™ Brown Scrub 'n Strip 8541 Pad – Heavy Duty	28
Scotch-Brite™ Power Pad 2000 - Heavy Duty	11	3M™ Doodlebug™ Hi-Pro 8550 Pad – Extra Heavy Duty	28
Scotch-Brite™ Dual Purpose Scour Pad 96HEX	11	Scotch-Brite™ Doodlebug™ Easy Erasing Pad 4610	29
Scotch-Brite™ Purple Pad 2020 - Heavy Duty	12	3M Easy Clean System	30
Scotch-Brite™ White Cleaning Pad 620 Less Scratching - Light Duty	13	3M™ Easy Trap Duster	30
3M™ Sponge Scourer Medium Duty - Economy 230S	13	3M™ Easy Scrub Express Flat Mop Tool With Pad Holder	31
Scotch-Brite™ Aqua Sponge Scourer - Medium Duty 630/74	13	3M™ Easy Shine Applicator System	32
Scotch-Brite™ Easy Erasing Pad 4004	14		
Scotch-Brite™ Power Sponge 3000	14	Floor Finishes & Coatings	33
Scotch-Brite™ Metal Scourer 83 and 84	15	Advanced Floor Care Systems	34
Scotch-Brite™ High Performance Cloth	15	Scotchgard™ Protect & Shine Floor Protector	35
3M™ Twist-Lok™ Pad Holder 961	16	Scotchgard™ Low Maintenance 25 Floor Finish, 9.5 L	35
3M™ Shortening Monitor	16	3M™ Clean and Shine Daily Floor Enhancer	35
		3M™ Neutral Cleaner Concentrate, 9.5 L	35
Griddle & Appliance Cleaning	17	Scotchgard™ Stone Floor Protector, 3.8 L Bag	36
Scotch-Brite™ Fryer and Kitchen Cleaning Tool	18	Scotchgard™ Resilient Floor Protector, 3.8 L Bag	36
Scotch-Brite™ Cool Griddle Cleaning Kit 461	18	3M™ Concrete Floor Cleaner and Densifier	36
Scotch-Brite™ Scotchbrick™ Griddle Scrubber 9537	19	3M™ TroubleShooter™ Baseboard Stripper, 600gms Aerosol	36
Scotch-Brite™ Griddle Screen 200	19		
Grill-Brick™ Grill Cleaner GB12, 3.5 in x 4 in x 8 in, 12/case	19	Floor Pads	37
Scotch-Brite™ Quick Clean Griddle Cleaning System Starter Kit 710, 1/case	20	Floor Pads	38
Scotch-Brite™ Quick Clean Griddle Liquid 701	20	Floor Stripping: Aggressiveness	39
		Deep Scrubbing: Aggressiveness, Floor Finish & Deep Scuff Removal	39
Surface Cleaning Chemicals	21	Burnishing: Durability	39
3M™ Glass and Laminate Cleaner	22	Choose The Right 3M Floor Pad For The Job	40-42
3M™ Stainless Steel Cleaner and Polish	22	Alternate Choices	44
Scotchgard™ Glass Cleaner and Protector	23	Sustainability Certifications for Floor Pads	44
3M™ Sharpshooter™ Extra Strength No-Rinse Mark Remover	23	3M™ Trizact™ Diamond TZ Discs, Gold	45
3M™ Twist 'n Fill™ Cleaning Chemical Management System	24	3M™ Trizact™ Diamond TZ Discs, Red	45
		3M™ Trizact™ Diamond TZ Discs, Blue	45
		Scotch-Brite™ Clean & Shine Pad	46

Table of Contents

Floor Safety	47
Scotchgard™ Anti-Slip and Floor Protection Film P4	48
Scotchgard™ Surface Protection Film 2200	49
3M™ Safety-Walk™ Slip-Resistant Fine Resilient Tapes and Treads - 200 Series	51
3M™ Safety-Walk™ Slip-Resistant Medium Resilient Tapes and Treads - 300 Series	51
3M™ Safety-Walk™ Slip-Resistant Conformable Tapes and Treads - 500 Series	52
3M™ Safety-Walk™ Slip-Resistant General Purpose Tapes and Treads - 600 Series	53
3M™ Safety-Walk™ Coarse Tapes and Treads - 700 Series	54
OEM Custom Converting and Die Cutting	55
3M™ Safety-Walk™ Primer 901	56
3M™ Safety-Walk™ Edge Sealing Compound	56
Matting	57
Matting	58
3M™ Safety-Walk Grip Economy Matting	59
3M™ Safety-Walk Economy Dome Matting	59
3M™ Safety-Walk Economy Open Hole Matting	59
3M™ Safety-Walk Economy Ute Liner Matting	59
3M™ Safety-Walk™ Cushion Matting 5270	60
3M™ Safety-Walk™ Safety Cushion Mat 1200 Black/Red	60
3M™ Safety-Walk™ Cushion Matting 5100	61
3M™ Safety-Walk™ Wet Area Matting 1500	61
3M™ Nomad™ Medium Traffic Scraper Matting 6050	61
3M™ Clean-Walk™ Mats	62
Spill Management	63
Spill Management	64
Cost Benefits of 3M™ Sorbents	65
Different Types of Sorbents	66
3M™ Chemical Sorbent Pad C-PD914DD	67
3M™ Chemical Sorbent Folded C-FL550DD/P-F2001	67
3M™ Chemical Sorbent Roll C-RL15150DD	67

3M™ Chemical Sorbent Mini-Boom P-200	67
3M™ Chemical Sorbent Pillow P-300	67
3M™ Chemical Sorbent Spill Kit SPK10L	67
3M™ Chemical Sorbent Spill Response Kit SRP-Chem	67
3M™ Chemical Sorbent Cab Bag Spill Kit CSRB-Chem	68
3M™ Chemical Sorbent Spill Kit CSRK-35	68
3M™ Chemical Sorbent Spill Response Pack CSRK-180	68
3M™ General Purpose Sorbent Pad M-PD1520DD	68
3M™ General Purpose Sorbent Folded M-FL550DD	68
3M™ General Purpose Sorbent Roll M-RL38150DD	69
3M™ General Purpose Sorbent Mini-Boom M-MB308	69
3M™ Floorsweep Sorbent FLS-10	69
3M™ General Purpose Spill Kit Cabin Bag SRCB-Gen	69
3M™ General Purpose Spill Kit Wheelie Bin MSRK-130	69
3M™ General Purpose Spill Kit Wheelie Bin MSRK-210	69
3M™ Petroleum Sorbent Pad HP-156	70
3M™ Petroleum Sorbent Pad HP-255	70
3M™ Petroleum Sorbent Pad H-157	70
3M™ Petroleum Sorbent Folded P-FL550DD	70
3M™ Petroleum Sorbent Roll HP-100	70
3M™ Petroleum Sorbent Single Boom T-270	70
3M™ Petroleum Sorbent Double Boom T-280	70
3M™ Petroleum Sorbent Mini-Boom T-4	70
3M™ Petroleum Sorbent Pillow T-240	71
3M™ Oil & Petroleum Sorbent Spill Kit Cabin Bag SRCB-Gen	71
3M™ Oil & Petroleum Sorbent Spill Kit Drum OSRK-45	71
3M™ Oil & Petroleum Sorbent Spill Kit Wheelie Bin OSRK-190	71
3M™ Oil HP Workshop Spill Kit OPWSK-300	71



Hand Pads & Scourers

Scotch-Brite™ Commercial Hand Pads/Scourers have a uniform mineral/abrasive coating on fibres throughout the pad. As the pads are used, new mineral is continually exposed throughout the life of the pad ensuring optimum cleaning performance and long life.

The quality, durability and efficiency of Scotch-Brite™ cleaning products is why they have become a top choice for food services professionals around the world. 3M offers the right tool for each cleaning job - from light duty to extra heavy.

Most 3M hand pads are HACCP approved*

*please contact 3M for HACCP endorsement certification details for specific products you are reviewing/purchasing

Why choose 3M?

- **Quality**

- ▶ Efficient and cost-effective products

- **Durability**

- ▶ Long lasting usage

- **Performance**

- ▶ Effective and consistent performance throughout the life of the pad

- **Saves Money**

- ▶ Durable, long lasting

- **Saves Labour**

- ▶ Scourers faster, gets the job done faster

- **Breadth of Product Line**

- ▶ Variety of pads, right product for the right application

Applications

Facilities	Type of Soils	Applications & Surfaces	
<ul style="list-style-type: none"> • Restaurants <ul style="list-style-type: none"> ▶ Quick Serve ▶ Full Serve • Food Processing Facilities <ul style="list-style-type: none"> ▶ Meat & Seafood Processing ▶ Vegetable Processing ▶ Others • Commercial Buildings <ul style="list-style-type: none"> ▶ Business ▶ Hospitals • Public Buildings <ul style="list-style-type: none"> ▶ Government ▶ Schools & Universities 	<ul style="list-style-type: none"> • Non-Food <ul style="list-style-type: none"> ▶ Stains, Marks, Scuffs ▶ Soap Scum, Hard Water Stains • Non-Baked On Food <ul style="list-style-type: none"> ▶ Thin, Soft, Non-Sticky ▶ Thick, Soft, Sticky • Baked On & Burnt Food <ul style="list-style-type: none"> ▶ Thin, Crispy ▶ Thick, Hard, Stubborn 	<ul style="list-style-type: none"> ▶ Acrylic ▶ Aluminum ▶ Appliance ▶ Baseboard ▶ Booths, Tables, and Chairs ▶ Brass/Silver ▶ Ceramic ▶ China ▶ Chrome ▶ Cooking Equipment ▶ Copper ▶ Countertops/ Laminates ▶ Desks ▶ Elevator Doors ▶ Glass 	<ul style="list-style-type: none"> ▶ Glass Cookware ▶ Griddle ▶ Kitchen Equipment ▶ Maintenance Equipment ▶ Mirrors ▶ Non-Stick Cookware ▶ Painted Surfaces ▶ Plasticware ▶ Porcelain ▶ Pots and Pans ▶ Railings ▶ Sinks/Tubs/Showers ▶ Stainless Steel Equipment ▶ Vinyl ▶ Wood

Hand Pads & Scourers

Scotch-Brite™ White Cleaning Pad - 449 - Light Duty

► Soft fibres and a mild abrasive enable this pad to clean most surfaces gently but thoroughly without scratching. Ideal for 'non-stick' and delicate surfaces including glass, plastic, fine china, rubber, porcelain, stainless steel and painted fixtures.

Country	3M Order Code	Product Number	Product Detail	Packout
AU	XE006002937	449	230mm x 150mm	50 pads/case



3M™ 230/ Niagara™ General Purpose - Economy Handpad

► Economy pad suited to everyday cleaning of most cooking utensils and equipment.

Country	3M Order Code	Product Number	Product Detail	Packout
AU	XE006002903	150	150mm x 100mm	100 pads/case
AU	XE006002887	230	230mm x 150mm	50 pads/case
AU	XE006002911	230	300mm x 300mm	50 pads/case



Scotch-Brite™ General Purpose Scouring Pad 96 - Medium Duty

► Use for everyday cleaning of most cooking utensils and equipment. High performance pads for every day use in Commercial and Industrial applications. Ideal for cleaning pots, cooking utensils, bench tops and metal surfaces. Multiple Sizes available.

Country	3M Order Code	Product Number	Product Detail	Packout
AU	XE006000022	96	230mm x 150mm	50 pads/case
NZ	XC000702818	96HP	200mm x 150mm	10 pads/pack, 10 packs/case
NZ	XN000738445	96HP	200mm x 150mm	100 pads/case
NZ	70007000881	96HPCC	230mm x 150mm	10 pads/pack, 6 packs/case



Scotch-Brite™ Green Scouring Pad 86 / 75 - Heavy Duty

► The heavy duty cleaning power of this scourer makes for light work when cleaning grease, grime and baked-on foods. Open weave construction for easy cleaning. Open construction pad with tough fibers and abrasives make fast work of heavy duty cleaning jobs. Use in the kitchen to replace scrapers, steel wool and metal sponges. Typical applications include heavily baked-on food and food processing equipment. Mineral: the product contains abrasive particles that are effective in scrubbing operation.

Country	3M Order Code	Product Number	Product Detail	Packout
AU	XP003817093	75	125mm x 175mm	50 pads/case
AU	70071657897	86CC	150mm x 225mm	10 pads/pack, 6 packs/case
NZ	XP003817994	86HP	143mm x 216mm	90 pads/case






Scotch-Brite™ Blue Pot ‘n Pan Scourer - Extra Heavy Duty 88

► The hardest working pad available; even the most stubborn deposits are scoured clean, especially useful for heavily encrusted pots and pans, kitchen and maintenance equipment. Ideal replacement for stainless steel wool and metal scourers. Open weave construction for easy cleaning.

Country	3M Order Code	Product Number	Product Detail	Packout
ANZ	70007001194	88	125mm x 90mm	10 pads/pack, 4 packs/case



Hand Pads & Scourers




Scotch-Brite™ Power Pad 2000 - Heavy Duty

Scours 2-4 times faster than conventional commercial scouring pads, and is 6-10 times less abrasive than other medium/heavy-duty commercial scouring products to reduce scratching.*

- ▶ Fiber: durable synthetic fibers that are crimped and heat set to create a strong web
- ▶ Scouring Particles: unique soil-removing particles for effective scouring, cleaning, and scrubbing. Particles are evenly distributed throughout the pad to ensure effective, consistent scouring, and lasting performance throughout the life of the pad
- ▶ Resin: high quality bonding resin system designed to provide resistance to degradation from exposure to hot water, detergents and normal cleaning liquids

Country	3M Order Code	Product Number	Product Detail	Packout
ANZ	70070724235	2000	139mm x 99mm	20 pads/case



Scotch-Brite™ Dual Purpose Scour Pad 96HEX

Features a yellow raised power dot side that aggressively scours away tough messes with less elbow grease. The smooth side scours away fine particles and grease, leaving a clean and shiny surface.

Use for general purpose cleaning, including:

- ▶ Pots and pans
- ▶ Cooking appliances and utensils
- ▶ Kitchen and maintenance equipment
- ▶ Stainless steel

Country	3M Order Code	Product Number	Product Detail	Packout
ANZ	75040055362	96HEX	139mm x 139mm	15 pads/case

*Internal test conducted in the 3M USA laboratory



Hand Pads & Scourers

Scotch-Brite™ Purple Pad 2020 - Heavy Duty

Cleans your dirtiest pots and pans twice as fast as conventional heavy duty scouring with less scratching.* Food debris rinses out of the pad easily. Unique web construction stands up to your toughest jobs. Scratches less than other heavy duty pads.

- ▶ Designed to provide heavy-duty scouring and scrubbing capability with significantly lower scratching potential
- ▶ Contains durable synthetic fibers that are manufactured to develop a strong, open pad surface
- ▶ Mineral particles are distributed evenly on the surface and through the pad to provide consistent scouring over the life of the pad
- ▶ Constructed with resin that resists degradation from exposure to hot water, detergents and most cleaning liquids
- ▶ A good replacement for most applications where steel wool and stainless steel scrubbers are currently used



Country	3M Order Code	Product Number	Product Detail	Packout
ANZ	70007000337	2020	114mm x 70mm	24 pads/case

*Internal test conducted in the 3M USA laboratory



Hand Pads & Scourers

Scotch-Brite™ White Cleaning Pad 620 Less Scratching - Light Duty

► A No. 449 Light Duty Scourer Pad on one side and sponge on the other.
Ideal for light duty cleaning jobs as it will not scratch most surfaces. Ideal for stainless steel, glass, ceramic, fine china, porcelain, countertops and non-stick surfaces.

Country	3M Order Code	Product Number	Product Detail	Packout
AU	XE006002879	620	150mm x 115mm	30 pads/case



3M™ Sponge Scourer Medium Duty – Economy 230S

► For general cleaning where sponge/scourer dual action is warranted.


Country	3M Order Code	Product Number	Product Detail	Packout
AU	XE006002895	230S	150mm x 100mm	50 pads/case



Scotch-Brite™ Aqua Sponge Scourer – Medium Duty 630/74

► For general scouring use, this scourer is especially effective for cleaning vats, tanks and cheese making equipment.

Country	3M Order Code	Product Number	Product Detail	Packout
AU	XE006000030	630	150mm x 115mm	30 pads/case
NZ	70007000048	74	150mm x 115mm	20 pads/case



Hand Pads & Scourers



Scotch-Brite™ Easy Erasing Pad 4004

Soft, flexible pad cleans many surfaces. Innovative white polymeric foam erases hard-to-clean stains, marks and scuffs. Unique blue urethane layer provides durability and keeps hands away from messes. Easy-to-use! Simply wet pad and squeeze out excess water. Use white side of pad to erase marks. Use blue side to wipe away residue.

- ▶ Trademarked bow-tie shape
- ▶ Soft, flexible pad cleans many surfaces without using additional chemicals - just use water
- ▶ Blue urethane foam sponge holds water to keep pad moist, can be used to wipe after use, and keeps the pad intact over its useful life
- ▶ Pad will not scratch glass, ceramic tile, fiberglass, porcelain, Formica®, metal, Corian®, marble, stainless steel, plastic, vinyl, and most wall coatings
- ▶ Optimal performance of product is achieved when used with water alone. Detergents and sanitizing cleaners are not recommended for use with this product

*Only available in NZ

Country	3M Order Code	Product Number	Product Detail	Packout
NZ	70071657954	4004CC	114mm x 71mm	12 pads/case



Scotch-Brite™ Power Sponge 3000

Two cleaning tools in one – a Scotch-Brite™ Power Pad combined with a sponge. 6-10 times less abrasive than other medium/heavy-duty commercial scouring products to reduce scratching.* Antimicrobial protection is locked-in to resist odours in the sponge

- ▶ Unique bow-tie shape for ease of handling
- ▶ The scouring side of the product scours 2-4 times faster, and is 6-10 times less abrasive than other conventional commercial scouring pads
- ▶ Fiber: Durable synthetic fibers that are crimped and heat set to create strong web
- ▶ Scouring Particles: Unique soil-removing particles for effective scouring, cleaning, and scrubbing. Particles are evenly distributed throughout the scouring pad to ensure effective, consistent scouring, and lasting performance throughout the life of the pad
- ▶ Resin: High quality bonding resin system designed to provide resistance to degradation from exposure to hot water, detergents and normal cleaning liquids
- ▶ Sponge side: Features antimicrobial technology that resists the growth of odor-causing bacteria within the sponge

Country	3M Order Code	Product Number	Product Detail	Packout
ANZ	70007000063	3000	114mm x 71mm	20 pads/case

*Internal test conducted in the 3M USA laboratory

Hand Pads & Scourers

Scotch-Brite™ Metal Scourer 84

- High quality stainless steel for tough cleaning jobs. Won't rust or splinter. Removes baked on food from pots, pans, grills and ovens.

Country	3M Order Code	Product Number	Product Detail	Packout
ANZ	70007000311	84	50gram balls	12 balls/case
AU	75040057095	84CC	50gram balls	72 balls/case (packs of 12)



Scotch-Brite™ High Performance Cloth

- The High Performance cloth is an effective way to clean and polish almost any surface without the use of chemicals. The cloth itself is chemical free and picks up dirt, oil and grease without streaking or smearing. The cloth can be reused by throwing it in the washing machine. The cloth can be used on virtually any surface. Try it on plastic, glass, mirrors, brass, stainless steel, chrome, metal, marble, painted metals, ceramic, fibreglass, electronic equipment, computer monitors. Great for removing lipstick from cups and glasses.

Country	3M Order Code	Product Number	Product Detail	Packout
AU	AN010564241		300mm x 320mm- Green High Perf	10 cloths/pack, 4 packs/case
AU	AN010564258		300mm x 320mm- Assorted Colours High Perf	10 cloths/pack, 4 packs/case
AU	AN010583589		360mm x 360mm- Dark Blue Economy	10 cloths/pack, 5 packs/case
ANZ	AN010583514		360mm x 360mm- Green Economy	10 cloths/pack, 5 packs/case
ANZ	AN010583530		360mm x 360mm- Light Blue Economy	10 cloths/pack, 5 packs/case
ANZ	AN010583522		360mm x 360mm- Red Economy	10 cloths/pack, 5 packs/case
ANZ	AN010583548		360mm x 360mm- Yellow Economy	10 cloths/pack, 5 packs/case



Food Service Accessories

3M™ Twist-Lok™ Pad Holder 961

► A holder specially designed for use with every Scotch-Brite™ hand pad which makes cleanup jobs faster, easier and safer

Country	3M Order Code	Product Number	Product Detail	Packout
ANZ	75040076228	961	Hand Pad/Scourer Holder	10 holders/case



3M™ Oil Quality Test Strips 1004

► A paper test strip with four coloured bands that change colour from blue to yellow as the levels of free fatty acids increase in your shortening

Country	3M Order Code	Product Number	Product Detail	Packout
ANZ	XC003828008	1004	Test Strips	40 strips/bottle, 4 bottles/case





Griddle & Appliance Cleaning

3M offers a wide portfolio of safe and effective cleaning solutions for griddles, fryers and beyond. These solutions range from the traditional griddle brick cleaning system to our advanced Quick Clean Griddle cleaning system. 3M offers a range of scouring pads to suite your cleaning needs.

Griddle & Appliance Cleaning



Scotch-Brite™ Fryer and Kitchen Cleaning Tool will be your versatile, go-to solution to clean a wide range of commercial kitchen surfaces.

Grey heavy duty pad: heat resistant up to 176°C. Ideal for cleaning open vat style fryers and to remove soil build up on flat surfaces. Green medium duty pad: with polishing abrasive, heat resistant up to 176°C. Thin web suited to cleaning hard to reach areas. Use to remove grease and food soil between coils and on flat surfaces. Blue low scratch cleaning pad: low scratch pad that is heat resistant up to 176°C. Use to remove grease and food soil between coils and on flat surfaces.

- Designed to reach and clean tight spaces, gaps and hard to reach areas of fryers.
- Adjustable to three different positions to provide leverage for cleaning various surfaces and hard to reach areas in fryers.
- Ideal for cleaning most fryers and other flat surfaces.
- Heat resistant, durable and long lasting.
- Extended position for longer reach - keeps your hands away from potential hot spots whilst delivering the leverage you need
- High quality bonding resin system designed to provide resistance to degradation from exposure to hot water, detergents, and normal cleaning liquids.

Country	3M Order Code	Product Number	Product Detail	Packout
AU	70071657012	905	Fryer and Kitchen Cleaning Tool	1 tool/case
AU	70071595881	901	Heavy Duty Grey Cleaning Pad	6 pads/case
AU	70071595899	902	Medium Duty Green Cleaning Pad	6 pads/case



Scotch-Brite™ Cool Griddle Cleaning Kit 461

A great solution for quick and effective cleaning of cooled down, flat griddles - kit includes a pad holder, griddle screen and a polishing pad.

- Griddle cleaning kit for quick and effective cleaning of cooled down, flat griddles
- Effectively removes carbonised grease and food debris, and polishes the surface to make food stick less in the future.

Country	3M Order Code	Product Number	Product Detail	Packout
ANZ	70071657988	461	Includes: Pad Holder, No. 46 Polishing Pad & No. 200 Cleaning Screen	10 kits/case

Griddle & Appliance Cleaning




Scotch-Brite™ Scotchbrick™ Griddle Scrubber 9537

This easy-to-use, one-piece griddle scrubber is for flat griddles at any operating temperature. The built-in, heat-resistant handle helps protect hands from burns, grease and grime.

- ▶ Abrasive mineral particles evenly distributed throughout the pad to ensure effective, consistent, and long lasting performance throughout the life of the pad
- ▶ A combination of pad and handle to function as a tool to help keep hands away from hot and dirty surfaces
- ▶ Aggressive, heavy duty and open pad construction to provide fast cleaning and multiple uses, resist clogging, and rinse clean easily

Country	3M Order Code	Product Number	Product Detail	Packout
AU	AN010564266	9537	Griddle Scrubber - Disposable	12 scrubbers/case
NZ	70071657970	9537	Griddle Scrubber - Disposable	12 scrubbers/case



Scotch-Brite™ Griddle Screen 200

Designed for heavy duty cleaning and removal of carbonized grease and food buildup on flat top griddles.

- ▶ High quality synthetic fabric backing to provide long lasting usage
- ▶ Abrasive minerals selected to provide remarkable scouring for the griddle cleaning
- ▶ Aggressive, heavy duty and open screen construction to provide fast cleaning and multiple uses, resist clogging and rinse clean easily
- ▶ Heat resistant screen to allow for cleaning griddle at operating temperature throughout the day

Country	3M Order Code	Product Number	Product Detail	Packout
ANZ	XA006513031	200	101mm x 139mm	20 screens/ pack, 10 packs/case



Grill-Brick™ Grill Cleaner GB12, 3.5 in x 4 in x 8 in, 12/case

- ▶ Specially compounded to disintegrate during use to expose a new unused surface.

Country	3M Order Code	Product Number	Product Detail	Packout
AU	70071314606	GB12	Griddle Brick - Disposable	12 bricks/case

Griddle & Appliance Cleaning



Scotch-Brite™ Quick Clean Griddle Cleaning System Starter Kit 710, 1/ case

A complete system for cleaning commercial griddles. This system is faster, safer and easier than traditional griddle cleaning products.

- ▶ Formulated with ingredients that are considered “Generally Recognized as Safe” (GRAS) in food by the U.S. FDA
- ▶ Green Seal™ Certified (avoids ingredients that are toxic or harmful to humans and the environment and efficiently uses packaging material)
- ▶ No caustic soda
- ▶ No strong chemical odour
- ▶ No water rinse required after use
- ▶ 3 simple steps to clean the griddle in just 3 to 5 minutes
- ▶ Helps increase operational efficiency by reducing the time it takes to clean the griddle
- ▶ Control product usage with pre-measured portions
- ▶ Durable construction of the Scotch-Brite™ Quick Clean Heavy Duty Griddle Pad 746 allows multiple uses
- ▶ HACCP certified product
- ▶ Does not leave behind residue

Country	3M Order Code	Product Number	Product Detail	Packout
AU	70071658218	710	Quick Clean Kit	1 kits/case



Scotch-Brite™ Quick Clean Griddle Liquid 701

A powerful griddle cleaning liquid that is Green Seal™ Certified and safe for use on food contact surfaces. Loosens and lifts carbonized grease and food soil upon contact on a hot griddle for easy removal. No strong chemical odours. Formulation does not contain caustic soda found in other griddle cleaning chemicals.

- ▶ Effectively removes baked-on food and cooking oil from griddles
- ▶ Green Seal™ Certified (avoids ingredients that are toxic or harmful to humans and the environment and efficiently uses packaging material)
- ▶ One-step cleaning
- ▶ Designed for use on medium-hot griddles (150°C-180°C) - saves cool-down time
- ▶ HACCP certified product

Country	3M Order Code	Product Number	Product Detail	Packout
ANZ	70071127057	701	Quick Clean Griddle Liquid Bottle 946mL	4 bottles/case



Surface Cleaning Chemicals

Cleaning power where and when you need it. For years, 3M has been an industry leader in providing automated chemical dispensing and mixing systems, along with top-performing cleaning chemicals. This has meant easy mixing, less waste, simple chemical storage, remarkable cleaning results and potential long-term savings

3M™ Stainless Steel Cleaner and Polish

Ideal for stainless steel, chrome, laminated plastics and aluminum surfaces. With a high-gloss formula, it wipes clean with no streaks or buildup, resists fingerprints and masks surface blemishes. Pleasant citrus fragrance.

- ▶ Cleans and polishes in one step
- ▶ Pleasant citrus fragrance
- ▶ Leaves a light protective film
- ▶ Masks blemishes
- ▶ Slows resoiling
- ▶ Reduces fingerprinting
- ▶ Resists streaking
- ▶ Leaves no greasy build-up on surfaces
- ▶ HACCP certified product



Country	3M Order Code	Product Number	Product Detail	Packout
AU	AN010557807		Aearosol spray can 600g	12 cans/case
NZ	61500061322		Aearosol spray can 600g	12 cans/case



Surface Cleaning Chemicals

Scotchgard™ Glass Cleaner and Protector

3M™ Glass Cleaner and Protector with Scotchgard™ Protection leaves an invisible layer of protection on glass for easier cleaning after routine use. It reduces fogging on windows and mirrors with repeated use, leaving an attractive shine. Cleans (but may not protect) other surfaces.

- ▶ Automatic dispensing eliminates measuring and mixing and helps ensure accurate dilutions
- ▶ Green Seal™ GS-37 Certification
- ▶ Streak-free formula
- ▶ HACCP certified product

Country	3M Order Code	Product Number	Product Detail	Packout
AU	70071595840		Pump spray bottle 946mL	12 bottles/case



3M™ Sharpshooter™ Extra Strength No-Rinse Mark Remover

No-rinse formula cleaner for quick, easy removal of soil and grease. This powerful cleaner penetrates and loosens buildup quickly. Convenient and effective.

- ▶ Removes stubborn marks, spots and stains on almost any washable surface
- ▶ No rinsing required
- ▶ Ready-to-use formulation

Country	3M Order Code	Product Number	Product Detail	Packout
ANZ	70071285335		Pump spray bottle 946mL	12 bottles/case



Surface Cleaning Chemicals

3M™ Twist 'n Fill™ Cleaning Chemical Management System

For years, 3M™ Twist 'n Fill™ Technology has been an industry leader in providing automated chemical dispensing and mixing systems, along with top-performing cleaning chemicals. This has meant easy mixing, less waste, simple chemical storage, remarkable cleaning results and potential long-term savings. Choose from two versatile, accurate dispensing systems to fit your needs.

Features a single dispenser that is designed to accurately dilute and dispense a wide range of cleaning solutions. You pick and choose only the chemicals you need for your cleaning task - and dispense them all through the same dispenser. Mounts on wall or, for portability, on carts or cleaning equipment. Mixing is easy and less wasteful. Your cleaning chemicals are consistent each time you mix.

- ▶ Dispense all chemicals with one dispenser
- ▶ Unique bottle and cap design lets you interchange chemicals in seconds
- ▶ Very compact — fits in most closets
- ▶ Easy to use — just insert bottle, twist and fill
- ▶ Integral air gap prevents chemical backflow
- ▶ 3M™ Bleach Dispenser will easily and accurately dispense a 1:10 bleach solution from concentrate

Country	3M Order Code	Product Number	Product Detail	Packout
NZ	70071683430	1L	2L bottle	6 bottles/case
NZ	70071683653	2L	2L bottle	6 bottles/case
NZ	70071683406	3H	2L bottle	6 bottles/case
NZ	70071126406	5H	2L bottle	6 bottles/case
NZ	70071682960	6H	2L bottle	6 bottles/case
NZ	70071682861	7H	2L bottle	6 bottles/case
NZ	70071683505	8L	2L bottle	6 bottles/case
NZ	70071591856	15L	2L bottle	6 bottles/case
NZ	70071682895	19L	2L bottle	6 bottles/case
NZ	70071315009	23L	2L bottle	6 bottles/case
NZ	70071315199		Dispenser with Installation Kit	1 per case



1L Glass Cleaner



2L Multi Surface



3H Neutral



5H Disinfectant



6H Speed Stripper



15L
Disinfectant
Bathroom
Cleaner



19L
Bathroom
Cleaner



7H
Degreaser



8L General
Purpose



23L Neutral
Disinfectant



*Only available in NZ



Floor Cleaning & Dusting Tools

3M has a range of dusters, mops, sweeper and doodlebugs to make your facilities floor shine. 3M's specially designed 3M™ Easy Clean System is a more efficient way to dust, scrub and shine. The system helps to reduce labour costs, increase performance and cut chemical waste.

Floor Cleaning & Dusting Tools

Doodlebug™ Pads

3M™ Doodlebug™ Cleaning System - Used as part of a general cleaning program to clean baseboards, under equipment and hard to reach areas. There are two types of holders and a variety of pads to ensure fast and efficient cleaning



3M™ Doodlebug™ Holder & Pole 6472

► This pad holder comes with a swivel joint which is ideal for reaching awkward areas. The supplied extension handle helps to clean floors, walls and various other hard to reach places.

Country	3M Order Code	Product Number	Product Detail	Packout
AU	AN010418695	6472	1.2m pole & Holder	10 per case
NZ	70071312071	6472	Holder	2/pack, 4 packs per case



3M™ Doodlebug™ Holder & Adaptor 6475

► This pad holder also comes with a swivel joint, but instead of the extension handle, we have included an adaptor that will enable you to fit a pole of your choice (25mm diameter).

Country	3M Order Code	Product Number	Product Detail	Packout
AU	AT010506643	6475	Swivel Head Pad Holder & Adaptor Only	10 per case



3M™ Doodlebug™ Hand Held 6473 Cleaning System

► Used as part of general cleaning program to clean under equipment, and hard to reach areas.

Country	3M Order Code	Product Number	Product Detail	Packout
ANZ	70071312097	6473	Hand Held Pad Holder - White and Brown Pad	4 packs/case



Floor Cleaning & Dusting Tools

3M™ Doodlebug™ White Cleansing 8440 Pad Light Duty

► For cleaning delicate surfaces. Fits 3M™ Doodlebug™ Pad Holder 6472 or 3M™ Doodlebug™ Handblock Pad Holder 6473.

Country	3M Order Code	Product Number	Product Detail	Packout
ANZ	70071313418	8440	Light Duty 254mm x 117mm	5 per pack, 4 packs per carton



3M™ Doodlebug™ Blue 8242 Pad Medium Duty

► For medium-duty cleaning and scrubbing. Fits 3M™ Doodlebug™ Pad Holder 6472 or 3M™ Doodlebug™ Handblock Pad Holder 6473.

Country	3M Order Code	Product Number	Product Detail	Packout
ANZ	70071312105	8242	Medium Duty 254mm x 117mm	5 per pack, 4 packs per carton



3M™ Doodlebug™ Brown Scrub 'n Strip 8541 Pad Heavy Duty

► Designed for tough jobs like removing finish and wax buildup from baseboards and floor edges. A great way to strip stairs. Fits 3M™ Doodlebug™ Pad Holder 6472 or 3M™ Doodlebug™ Handblock Pad Holder 6473.

Country	3M Order Code	Product Number	Product Detail	Packout
ANZ	70071567872	8541	Heavy Duty 254mm x 117mm	5 per pack, 4 packs per carton



3M™ Doodlebug™ Hi Pro 8550 Pad Extra Heavy Duty

► For extra heavy-duty cleaning and stripping. Uniform coating throughout every 3M™ Doodlebug™ pad reduces the number of knots and clumps. Will not be significantly affected by water, detergents, or cleaners normally used for floor maintenance. Fits 3M™ Doodlebug™ Pad Holder 6472 or 3M™ Doodlebug™ Handblock Pad Holder 6473.

Country	3M Order Code	Product Number	Product Detail	Packout
ANZ	70071312113	8550	Extra Heavy Duty 115mm x 250mm	5 per pack, 4 packs per carton




Floor Cleaning & Dusting Tools

Scotch-Brite™ Doodlebug™ Easy Erasing Pad 4610

► Ideal for removing stains, marks, ink and more. Just use water; no chemicals or sprays needed. Fits 3M™ Doodlebug™ Handblock Pad Holder 6473 or 3M™ Doodlebug™ Pad Holder 6472.

Country	3M Order Code	Product Number	Product Detail	Packout
AU	70071313491	4610	Erasing Pad 254mm x 117mm	5 per pack, 4 packs per carton



Floor Cleaning & Dusting Tools

3M Easy Clean System

- ▶ **1. 3M™ Easy Trap Duster System...**
Holds up to 8X more debris than conventional flat fringed cotton dust mops or a competitive sweeping dust cloth brand.*
- ▶ **2. 3M™ Easy Scrub Express System...**
Operator-controlled dispensing mechanism helps cut chemical waste by as much as 80% vs. mop and bucket method.*
- ▶ **3. 3M™ Easy Scrub Flat Mop System...**
Helps reduce disinfectant consumption and amount entering waste stream. Cuts chemical waste by as much as 80% vs. mop and bucket method.*
- ▶ **4. 3M™ Easy Shine System...**
Helps reduce finish usage by up to 35% vs. traditional mop and bucket method. Helps reduce employee and patient exposure to odours and floor finish disposed into waste stream.*

*Internal test conducted in the 3M USA laboratory

3M™ Easy Trap Duster

3M™ Easy Trap Duster - sweep & dust sheets reduce the risk of bad impressions by trapping up to 8X more dirt, dust and sand than when using traditional dust mops or a competitive sweeping dust cloth brand. Convenient disposable sheets mean no laundering. The Easy Trap Duster glides through and traps debris, especially hair. Use under any flat floor tool or high duster. Take as little or as much as needed - comes in rolls perforated every 6". Use both sides. Expect minimum training and maximum results in veterinarian clinics, hair salons, hospitals, gyms, schools - nearly anywhere

- ▶ Traps up to 8X more dirt, dust and sand than conventional flat fringed cotton dust mops or a competitive sweeping dust cloth brand.
- ▶ No special tool required. Use on existing floor tool or high duster.
- ▶ Glides through and traps hair even on wet surfaces.
- ▶ Convenient disposable sheets, no laundering required.
- ▶ Ideal for picking up glitter and other small particles.
- ▶ After one side is used, flip it over and use the other side.
- ▶ Sheets are made with a minimum of 60% recycled content.
- ▶ Packaging is made from a minimum 65% total recycled content. A minimum 35% of the total recycled content comes from post-consumer waste.

Country	3M Order Code	Product Number	Product Detail	Packout
ANZ	70071659752		125mm x 150mm	8 boxes/case



Floor Cleaning & Dusting Tools



3M™ Easy Scrub Express Flat Mop Tool With Pad Holder

Changing chemicals and cleaning products is a snap with the 3M™ Easy Scrub Express Flat Mop System. Interchangeable bottles fit quickly into a lightweight handle to help reduce waste and ensure precise dispensing of solutions to the work site.

- ▶ Easy maneuverability helps reduce worker fatigue
- ▶ Innovative technologies reduce mop drag up to 10X compared to other traditional flat mop systems
- ▶ Operator-controlled dispensing mechanism helps cut chemical waste by as much as 80%
- ▶ Can be used in conjunction with all other 3M™ Easy Clean System products to help provide exceptional cleaning results
- ▶ Durable long lasting material
- ▶ Resistant to Bleach

Patient room cleaning can be a much more productive process with the 3M™ Easy Scrub Flat Mop System, helping you save time and money.

Clean more with less effort.

- ▶ Mop drag is up to 10X less than other traditional flat mops
- ▶ Cleans and scrubs up to 3X faster than other flat mops
- ▶ Reduces cleaning time up to 50% compared to mop and bucket
- ▶ Reduces chemical waste by up to 80%
- ▶ Helps eliminate mops and buckets
- ▶ Other common applications include classroom cleaning, cafeteria tables, stairwells, wrestling mats, restrooms and spot mopping

3M™ Easy Scrub Flat Mop - Recommended Usage		
	Area	Mop Colour
Health Care	Patient Rooms	White
	Operating Emergency Rooms	Blue
	Restroom Floors	Red
	Kitchen Floors	Green
	General Public Areas	White
Facilities	Restroom Floor	Red
	Kitchen Floors	Green
	Dining Floors	White
	General Floors	White

Country	3M Order Code	Product Number	Product Detail	Packout
ANZ	AN010574208/70071312147		Flat mop tool	1 each/case
ANZ	70071593746	55594	White 457mm	100 pads/case
ANZ	70071312196		Easy Scrub Express Bottles	72 bottles/case
ANZ	70071593761	59026	Red 457mm	40 pads/case
ANZ	70071593787	59028	Blue 457mm	40 pads/case

Floor Cleaning & Dusting Tools

3M™ Easy Shine Applicator System

With the 3M™ Easy Shine Applicator System you can use most conventional floor finishes and cleaning chemicals to get results you can be proud of every time.

- ▶ Reduce labour costs by as much as 70%
- ▶ Reduce finish usage by up to 35%
- ▶ Easy to apply finish in corners and along baseboards
- ▶ Low drag mop helps deliver smooth, even coats of finish
- ▶ Specially designed filling station allows use of most conventional floor finishes and cleaning chemicals
- ▶ Helps eliminate mops and buckets

Country	3M Order Code	Product Number	Product Detail	Packout
AU	AN010564191	55433	Includes: 1 Applicator Handle, 1 Applicator Pad Holder 457mm, 1 Backpack, 1 Reusable pouch, 2 Applicator pads 457mm, 1 Supply Tube, 5 Delivery Tubes.	1 each/case
AU	70071593803		Scotchgard™ Floor Protector Applicator 18" Pad - Blue	2 pads/ bag, 5 bags/case





Change your products, not your process.

Get a first-class shine without all the burnishing, scrubbing, stripping and recoating — or the harsh chemicals. The 3M™ Advanced Floor Care System helps you get the results you want with the tasks you do every day.

- **Beautiful appearance.** High gloss with less labour and fewer chemicals.
- **Cost savings.** Fewer needed procedures; and less equipment and product use means lower total cost of ownership.
- **Less labour and disruption.** Reduced need for the recurring maintenance tasks that are most disruptive to your facility and your guests.
- **Protect your investment.** As use of hand sanitisers becomes more widespread, protect your floors with a coating that can resist the surface damage they can cause.

For best results, use all the elements of the 3M Advanced Floor Care System as part of your routine floor maintenance. Using the whole system can significantly reduce or eliminate the need for burnishing.

A system that fits your routine.

The 3M™ Advanced Floor Care System helps you achieve a beautiful, high-gloss floor while reducing maintenance costs. **For best results, incorporate all three products into your routine maintenance.**



A better solution for uncoated concrete floors.

You can finally let your concrete floors shine. The 3M™ Concrete Floor Polishing and Maintenance System effectively cleans, polishes and maintains uncoated concrete floors. It doesn't rely on coatings, so it's better for your customers and the environment. The system may reduce the need for major restoration work, so you can improve the gloss and DOI of your floors with less time and effort.

Long-lasting polishing power.

Scotch-Brite™ Diamond Floor Brush

3M's proprietary floor bristle brush uses flexible bristles that conform to uneven floors or floor irregularities, including low spots in floors.

- Simplifies maintenance by providing both cleaning and gloss recovery in one step
- No assembly or presoaking required
- No sharp blades to worry about
- Diamond Floor Brush 1000 is for dull floors where a low to medium gloss/DOI is desired; Diamond Brush 3000 is for polished floors where a medium to high gloss/DOI is desired
- Longer brush life and durability means less waste in landfills compared with floor pads



Maximum appearance.

3M™ Concrete Floor Cleaner & Densifier

Choose a daily floor cleaner concentrate with excellent cleaning ability and a densifier to provide improved shine and durability on uncoated concrete.

- Works in tandem with the Scotch-Brite™ Diamond Floor Brush to maximize floor appearance



Floor Finishes & Coatings

Scotchgard™ Protect & Shine Floor Protector

Water based formula penetrates and protects resilient flooring surfaces such as vinyl, vinyl composition (VCT), and solid vinyl tile (SVT). Part of the 3M™ Advanced Floor Care System designed to help reduce or even eliminate burnishing in some instances.

Durable floor coating with superior soil and abrasion resistance compared to traditional acrylic finishes that can help reduce or eliminate the need for stripping.

Country	3M Order Code	Product Number	Product Detail	Packout
NZ	75040074009		3.785L Bag	2 bags/case
NZ	75040074017		9.5L Bottle	2 bags/case



Scotchgard™ Low Maintenance 25 Floor Finish, 9.5 L

▶ Exceptionally tough and durable, 25% solids, low maintenance floor finish provides a “wet-look” gloss with less burnishing. Dries fast for outstanding image and film clarity. Use on resilient tile and terrazzo floors

Country	3M Order Code	Product Number	Product Detail	Packout
ANZ	70071683372		9.4L Bottle	2 each/case



3M™ Clean & Shine Daily Floor Enhancer

Floor cleaner that does double duty by cleaning the floor and improving gloss with daily use. Couple it with the Scotch-Brite Clean and Shine Floor Pad & the Scotchgard Protect & Shine Floor Protector for a full system that reduces labour and product cost associated with routine floor maintenance.

- ▶ Repairs fine scratches, reducing the need for burnishing.
- ▶ Reduces frequency of top scrubbing and stripping which means less disruption of day-to-day facility operations.

Country	3M Order Code	Product Number	Product Detail	Packout
ANZ	75040075246		9.5L Bottle	2 per case
ANZ	75040075253		946mls Doser Bottle	6 per case



3M™ Neutral Cleaner Concentrate, 9.5 L

No-rinse, low-foaming formula won’t harm washable hard floors or leave soapy residue that can dull or soften floor finish.

- ▶ Use with mop or automatic scrubber
- ▶ Fresh scent.
- ▶ Dilution rate: 1:391.
- ▶ For use with Scotchgard™ Hard Floor Protection Products

Country	3M Order Code	Product Number	Product Detail	Packout
AU	70071683596		9.4L Bottle	2 each/case



Floor Finishes & Coatings

Scotchgard™ Stone Floor Protector, 3.8 L Bag

Every year, poorly maintained floors are responsible for more than two million customer and employee fall injuries. The result is billions of dollars in medical, insurance and litigation costs. In just two coats, Scotchgard™ Stone Floor Protector creates an NFSI-Certified “high traction” surface that can help prevent slips and falls. What’s more, you get a long-lasting, glossy, natural-looking floor that is less susceptible to scuffs, black marks, stains and scratches.

- ▶ No stripping or deep scrubbing required, eliminating operator exposure to and environmental release of potentially hazardous stripping chemicals
- ▶ Easy to spot repair damaged areas
- ▶ Unique hybrid technology that densifies, increases hardness and improves wear

Country	3M Order Code	Product Number	Product Detail	Packout
AU	70071683356		3.785L	2 bags/case
NZ	75040031660		3.785L	2 bags/case



Scotchgard™ Resilient Floor Protector, 3.8 L Bag

High Performance floor coating for vinyl and vinyl composition substrates which offers a good and clean appearance over time, with benefits of labor savings, and elimination of stripping versus conventional acrylic finishes.

Water based formula penetrates and protects resilient flooring surfaces such as vinyl, vinyl composition, and solid vinyl tile.

cleaningthe

Country	3M Order Code	Product Number	Product Detail	Packout
NZ	70071659240		3.785L	2 bags/case



3M™ Concrete Floor Cleaner & Densifier

Daily floor cleaner concentrate with excellent cleaning ability and a densifier to provide improved shine and durtability on uncoated concrete. Works in tandem with the Scotch-Brite Diamond Floor Brush to maximise floor appearance.

946mls Dose

.5

Country	3M Order Code	Product Number	Product Detail	Packout
ANZ	70001206534		3.785L Bottle	4 bottles/case



3M™ TroubleShooter™ Baseboard Stripper, 600 gms Aerosol

Non-ammoniated formula strips floors without lengthy downtime. No rinsing or neutralizing needed

Country	3M Order Code	Product Number	Product Detail	Packout
ANZ	61500061314		Aearosol spray can 600g	12 cans/case





Floor Pads

Every 3M Floor Pad is made to high quality standards. Ongoing innovation and advancements in technology make 3M Floor Pads more effective than ever. Each floor pad in 3M’s full line is engineered specifically for a particular maintenance task.

Floor Pads

For over 50 years, high performing 3M™ Floor Pads have been an industry leader. High performance aligns well with sustainability.

When compared to the nearest competitor, 3M floor pads:

- ▶ Remove deep scuff marks 7 times faster*
- ▶ Provide nearly 40% more aggressive floor stripping*
- ▶ Have 25% better cut on Schiefer test*
- ▶ Have 50% better burnishing durability*

*Applies to specific 3M floor pads.
Contact 3M for supporting test data.

Every 3M™ Floor Pad is made to high quality standards. And ongoing innovation and advancements in technology make 3M floor pads more effective than ever.







It's no wonder we are the #1 supplier worldwide.

- ▶ Each floor pad in 3M's full line is engineered specifically for a particular maintenance task.
- ▶ 3M floor pad uniformity and quality helps produce: less machine wobble and vibration, less operator fatigue, prolonged useful life of the pad and better results on your floors.
- ▶ Uniform coating throughout every 3M floor pad helps produce a long, useful life, resulting in less pad usage.



All floor pads are not created equally.

The differences between floor pads may seem small. But when added up, they can make a big difference to your bottom line in terms of productivity and labour costs. Consider the following attributes of 3M floor pads that help set them apart from the competition:

- ▶ Uniform distribution of mineral abrasives throughout pad—not just on the surface—offers impressive performance and a long, useful life.
- ▶ Individually separated and coated fibers help produce more consistent, high-quality results.
- ▶ The combination of highly conformable fibers help to provide maximum pad-to-floor contact.



3M™ Floor Pads		Other Floor Pads	
			
OUTSIDE	INSIDE	OUTSIDE	INSIDE
			
<ul style="list-style-type: none">▶ Fibres uniformly coated with resin and mineral throughout entire pad, producing more consistent results▶ Combination of highly conformable fibres help to maximise the pad-to-floor contact		<ul style="list-style-type: none">▶ Fibres randomly coated with resin and mineral, which can produce inconsistent results▶ Larger fibres are less conformable, providing fewer contact points with the floor	

Floor Stripping: Aggressiveness




*Pads worn via 50 passes over 3M Safety-Walk Slip-Resistant Treads 610 (swing machine)

Deep Scrubbing: Aggressiveness, Floor Finish & Deep Scuff Removal



*Worn pad average




*Pads worn via 25 passes over 3M Safety-Walk Slip-Resistant Treads 610 (swing machine)

Burnishing: Durability

3M™ Sky Blue Hi-Performance Burnish Pad 3050




After burnishing 350,000 square feet of flooring, pad weight loss was less than 15% versus 32% and 33% with competitive pads*



*Based on lab testing with battery burnisher




Choosing the Right Pad for the Right Job

Stripping		
	3M™ High Productivity Pad 7300 Pad Most aggressive stripping pad. Resists loading and clogging. For fast removal of finish.	
		3M™ Black Stripper Pad 7200 Standard of the industry. Consistent proven performance. Long pad life.
		
		3M™ Brown Stripper Pad 7100 Conformable for uneven floors. Heavy duty scrubbing for 2-4 coat removal. Strips prior to refinishing.

Scrubbing		
	Scotch-Brite™ Surface Prep Pad Plus For heavy-duty scrubbing & for 2-4 coat removal prior to recoating.	
		3M™ Blue Cleaner Pad 5300 For heavy-duty scrubbing for 1-2 coats prior to recoating.
		
		3M™ Extra Duty Floor Brush 73 For heavy-duty scrubbing or stripping of most floor surfaces. Unique wedge design provides multiple cleaning edges that get uneven, rough floors cleaner, faster.

Cleaning and Buffing		
	3M™ Topline Autoscrubber Pad 5000 Scrubs and cleans without dulling the finish. Ideal for use on an Autoscrubber.	
		3M™ Red Buffer Pad 5100 For everyday cleaning and light scrubbing. Removes light soil scuff marks and black heel marks.
		
		3M™ White Super Polish Pad 4100 For light cleaning to help remove soil and scuff marks with minimal dulling of finish.

Cleaning and Gloss Recovery	
	Scotch-Brite™ Clean & Shine Pad Not only provides a deep clean but improves gloss levels over time. Ideal for use on an Autoscrubber.

*See price pages for list of floor pad sizes & codes

Choosing the Right Pad for the Right Job

Burnishing



3M™ Eraser Burnish Pad 3600

For harder finishes and high traffic areas.

Removes black marks and returns gloss in fewer passes.



3M™ Natural Blend Tan Pad 3500

Use on harder finishes and high traffic conditions.

Removes marks and scuffs while polishing.

Blend of natural and synthetic fibres.

Best Gloss




3M™ Natural Blend White Pad 3300

Excellent results on a wide variety of finishes.

Provides consistent high gloss white minimising swirl marks.

Blend of natural and synthetic fibres.


Soft Finish



3M™ Sky Blue Hi-Performance Burnish Pad 3050

Restores gloss to dull floors.

For frequent burnishing with less dust, point build-up and burning.





3M™ Aqua Burnish Pad 3100



Produces good gloss improvement.

Exceptional durability and life. The soft finish problem solver.

*See price pages for list of floor pad sizes & codes

Choosing the Right Pad for the Right Job

Diamond Coated Floor Pads	
 <p>Scotch-Brite™ Sienna Diamond Floor Pad</p> <p>Sienna Diamond: For worn and dull floors in poor initial condition. Cleans, conditions and polishes to a medium shine.</p> <p>Made of high quality synthetic fibre, with abrasive particles, including high quality synthetic diamonds for cleaning and conditioning Marble, Terrazzo, Slate and Polished concrete flooring.</p>	 <p>Scotch-Brite™ Purple Diamond Floor Pad Plus</p> <p>Purple Diamond: For floors with medium shine in good initial condition. Cleans and polishes floors to a brilliant gloss finish.</p> <p>Made of high quality synthetic fibre, with abrasive particles, including high quality synthetic diamonds for cleaning and conditioning Marble, Terrazzo, Slate and Polished concrete flooring.</p>

Uncoated Concrete Floor Brush	
 <p>Scotch-Brite™ Diamond Floor Brush 1000</p> <p>1000 Diamond brush: For dull floors where a low to medium gloss/DOI is desired</p> <p>3M's proprietary floor bristle brush uses flexible bristles that conform to uneven floors or floor irregularities including low spots in floor.</p>	 <p>Scotch-Brite™ Diamond Floor Brush 3000</p> <p>3000 Diamond brush: For polished floors where a medium to high gloss/DOI is desired</p> <p>3M's proprietary floor bristle brush uses flexible bristles that conform to uneven floors or floor irregularities including low spots in floor.</p>

Why you should choose 3M™ Floor Pads

Uniform coating throughout every 3M floor pad helps produce a long, useful life, resulting in less pad usage.

3M™ Floor Pads

- Remove deep scuff marks 7 times faster*
- Provide 40% more aggressive floor stripping*
- Offer 50% better burnishing durability*

*When compared to closest competitor. Test done in USA laboratory

*See price pages for list of floor pad sizes & codes

Maintenance Operation

Equipment Speed

First Choice

Stripping

To remove finish, sealer and contaminants from the floor surface.

Rotary or Automatic

Low Speed
175–600 RPM



3M™ High Productivity Pad 7300
Our most aggressive stripping pad. Unique open construction resists loading and clogging. For fast removal of finish and proven consistent stripping.

Scrubbing

To provide a fresh new surface for finishing.

Rotary or Automatic

Low Speed
175–600 RPM



Scotch-Brite™ Surface Preparation Pad Plus
Heavy-duty scrubbing for 2–4 coat removal prior to recoating.

Cleaning

To remove light soil and other contaminants.

Rotary or Automatic

Low Speed
175–600 RPM



Scotch-Brite™ Clean & Shine Pad
Use the two-sided Scotch-Brite™ Clean & Shine Pad for daily cleaning and dustless polishing.

Buffing

To remove scuffs and black heel marks and enhance floor appearance.

Rotary

Low Speed
175–600 RPM



3M™ White Super Polish Pad 4100
Ideal for removing soil and scuff marks with minimal dulling. Also used to polish wood floors.

Burnishing

To remove scuffs and marks, repair finish and improve gloss and image clarity.

Electric, Battery,
Propane

Ultra High Speed
1500 RPM & Above



3M™ Eraser Burnish Pad 3600
Removes black marks and returns gloss in fewer passes than other pads while producing less dust. Ideal for harder finishes and high traffic areas. Excellent durability and minimal finish removal.

Best Gloss

Electric, Battery,
Propane

Ultra High Speed
1500 RPM & Above



3M™ Natural Blend White Pad 3300
Blend of natural and synthetic fibers. Excellent results on a wide variety of finishes and traffic conditions. Consistent high gloss with minimal swirl marks.

Soft Finish

Electric, Battery,
Propane

Ultra High Speed
1500 RPM & Above



3M™ Sky Blue Hi-Performance Burnish Pad 3050
Restores gloss to dull floors. Designed for frequent burnishing with less dust, point buildup and burning.

Stone Floor Conditioning

To clean and condition worn and dull stone floors.

Rotary, Automatic,
Electric, Battery or
Propane

Low to Ultra High
Speed 175–1500 RPM
& Above



Scotch-Brite Sienna Diamond Floor Pad Plus
Diamond-coated floor pads clean and condition worn and dull marble, terrazzo, slate and polished concrete, bringing it to a medium gloss.

Stone Floor Polishing

To clean and polish stone floors with medium shine in good condition.


Rotary, Automatic,
Electric, Battery or
Propane


Low to Ultra High
Speed 175–1500 RPM
& Above





Scotch-Brite Purple Diamond Floor Pad Plus
Diamond-coated floor pads further enhance the appearance of terrazzo, slate and polished concrete.


Alternate Choices


- 

3M™ Black Stripper Pad 7200
Standard of the industry. Consistent proven performance. Long pad life.
- 


3M™ Blue Cleaner Pad 5300
Heavy-duty scrubbing for 1–2 coat removal prior to recoating.
- 


3M™ TopLine Autoscrubber Pad 5000
Scrubs and cleans. Open construction resists clogging. Ideal for autoscrubbers.
- 

3M™ Red Buffer Pad 5100
Designed for everyday cleaning and light scrubbing to remove light soil, scuff marks and black heel marks.
- 

3M™ Natural Blend Tan Pad 3500
Blend of natural and synthetic fibers. Ideal for harder finishes and high traffic conditions. Removes marks and scuffs while polishing.
- 

3M™ Aqua Burnish Pad 3100
Good gloss improvement with exceptional durability and life. The soft finish problem solver.

- 

3M™ Brown Stripper Pad 7100
Conformable stripping pad for uneven floors. Super heavy-duty scrubbing for 2–4 coat removal.
- 

3M™ Red Buffer Pad 5100
Designed for everyday cleaning and light scrubbing to remove light soil, scuff marks and black heel marks.

Choose the right floor pad for the job.

No two floor maintenance jobs are exactly alike. That's why 3M, the inventor of floor pad technology and the world's number one floor pad supplier, manufactures a wide range of products designed for specific types of equipment and maintenance tasks. Use this chart to help you choose the pads you need or contact your 3M representative for help.



Green Seal

The Green Seal Environmental Innovation program recognizes products that significantly reduce environmental impact through product innovation. 3M™ Floor Pads* are certified by Green Seal® for Environmental Innovation based on a design for significantly improved performance, durability, or both, extending the useful life of the floor pad and reducing solid waste generation.

*3M™ and Scotch-Brite™ Brand Floor Pad families include: 7300, 7200, 5300, 3050, SPP Plus, SPP, Purple Diamond, and Clean & Shine Niagara™ Brand floor pad families include: 7400N, 7200N, 5300N, and Deep Scrubbing Pad



Greener Solutions

Greener Solutions is a 3M program for 3M™ Floor Pads* that are made with at least 50% post-consumer recycled materials and water-based latex resins. Plus, our packaging is 100% recyclable and made with 50–100% recycled content.

The polyester fiber used to make a range of floor pads* contains a minimum of 50% post-consumer recycled content. The recycled polyester fiber used is third-party certified for post-consumer recycled content. *3M™ Brand Floor Pad families include: 3200, 3300, 3400, 3500, 3600, 5000, 5100, Sienna and Purple Diamond Pad. Niagara™ Brand Floor Pad families include: 3300N, 3400N, 3500N, 3700N, 5100N, 5400N and 7200N.

Floor Pads

3M™ Trizact™ Diamond TZ Discs

Give marble, terrazzo, polished concrete and other porous stone floors new life with 3M™ Trizact™ Diamond TZ Discs featuring proprietary 3M technologies and manufacturing techniques, these advanced abrasives leave exceptionally consistent scratch patterns, maximizing efficiency and reducing the number of steps in the restoration process.

- ▶ Uniform cutting surface stays sharp and effective through the life of the discs
- ▶ Wet process does not create dust
- ▶ Compatible with standard floor cleaning equipment (low speed rotary and automatic scrubber)
- ▶ Can also be used with the 3M™ Electric Variable Speed Polisher to easily access stairs, corners and other tight areas
- ▶ Fast material removal rates
- ▶ Use on your existing flat grinding and finishing equipment - both single and double-sided lapping machines
- ▶ Cleaner operation - reduces machine wear
- ▶ Designed to work with aqueous coolants to reduce clean-up and toxic waste disposal issues associated with abrasive slurries
- ▶ Minimizes sub-surface damage
- ▶ Designed for speed, consistency and control needed for flat finishing, grinding and lapping of technical ceramics, glass and exotic metals

3M™ Trizact™ Diamond TZ Discs, Gold

Diamond disc system for more aggressive refurbishing of stone floors with apparent wear or damage from scratching or pitting.


3M™ Trizact™ Diamond TZ Discs, Red

Diamond disc system for refurbishing and initial finishing of worn and damaged stone floors using low-speed rotary or automatic equipment.

3M™ Trizact™ Diamond TZ Discs, Blue

For intermediate finishing and pre-polishing stone floors using low-speed rotary or automatic equipment.

Country	3M Order Code	Product Detail	Packout
ANZ	70071660743	Gold Trizact Disc	4 pads/box, 4 boxes/case
ANZ	70071660750	Red Trizact Disc	4 pads/box, 4 boxes/case
ANZ	70071660768	Blue Trizact Disc	4 pads/box, 4 boxes/case



Floor Pads

Scotch-Brite™ Clean & Shine Pad

The Scotch-Brite™ Clean & Shine Pad shines the floor as you clean with it. With repeated use, your floors gradually achieve burnish-quality results without the extra step of actually burnishing. Using a low-speed auto scrubber with just plain water or neutral cleaner, it effectively removes scuff marks faster than traditional floor pads and lasts significantly longer. So you can maintain a shining reflection with less time, effort and equipment.

Use the two-sided Scotch-Brite™ Clean & Shine Pad for daily cleaning and dustless polishing.

- ▶ **Less time to clean** — removes black marks 3 times faster than traditional cleaning pads.
- ▶ **Reduce burnishing** — shine increases with each use to reduce or even eliminate the need for burnishing.
- ▶ **Less equipment** — clean and shine in the same step using only a low-speed scrubber.
- ▶ **Fewer chemicals** — effective with just water.
- ▶ **Replace less often** — lasts longer than traditional cleaning pads.
- ▶ **Versatile** — can be used on most coated and uncoated floors including VCT, vinyl, stone, terrazzo, concrete, marble, granite and rubber.



Country	3M Order Code	Product Detail	Packout
ANZ	XE006001079	Clean & Shine 11inch	5 pads/case
ANZ	XE006001087	Clean & Shine 12inch	5 pads/case
ANZ	XE006001095	Clean & Shine 13 inch	5 pads/case
ANZ	XE006001103	Clean & Shine 14inch	5 pads/case
ANZ	XE006001111	Clean & Shine 15inch	5 pads/case
ANZ	XE006001129	Clean & Shine 16inch	5 pads/case
ANZ	XE006001137	Clean & Shine 17inch	5 pads/case
ANZ	XE006001145	Clean & Shine 18inch	5 pads/case
ANZ	XE006001152	Clean & Shine 19inch	5 pads/case
ANZ	XE006001160	Clean & Shine 20 inch	5 pads/case
ANZ	XE006001178	Clean & Shine 21inch	5 pads/case
ANZ	XE006001186	Clean & Shine 22inch	5 pads/case
ANZ	XE006001194	Clean & Shine 23 inch	5 pads/case
ANZ	XE006001202	Clean & Shine 24 inch	5 pads/case
ANZ	XE006001210	Clean & Shine 12 in x 18 inch	5 pads/case
ANZ	XE006001228	Clean & Shine 20 in x 14 inch	5 pads/case
ANZ	XE006001236	Clean & Shine 28 in x 14 inch	5 pads/case
ANZ	XE006001244	Clean & Shine 32 in x 14 inch	5 pads/case



Floor Safety

3M offers a full range of functional, slip-resistant tapes and treads suitable for industrial or residential applications in dry, wet or oily conditions. 3M also manufactures temporary peelable slip resistance coatings for high risk areas.

Floor Safety

Scotchgard™ Anti-Slip & Surface Protection Film

Scotchgard™ Anti-Slip & Surface Protection Film is designed to protect stone and vinyl flooring as well as bathroom surfaces from the everyday challenges they are subjected to. It can be applied to vinyl, sealed concrete, marble, ceramic tile, terrazzo and more.

Typical uses:

- ▶ Building entrances
- ▶ Airports
- ▶ Underneath chairs and furniture
- ▶ Rolling beds
- ▶ Cafeteria lines and dining areas
- ▶ Retail aisles
- ▶ Bathroom surfaces and floors
- ▶ Classroom chairs and more



This protective film reduces the number of stripping and recoating events a surface requires – which saves you time, labour and money. No special tools or techniques are required to install and remove Scotchgard™ Anti-Slip & Surface Protection Film. The product can also be easily removed prior to floor stripping or refinishing. Scotchgard™ Anti-Slip & Surface Protection Film is compatible with standard floor cleaning procedures such as the use of auto scrubbers as well as as floor disinfectants, cleaners and coatings. In addition, it has been certified to a P4 slip rating making this a high traction product.

Sizes 1.2M x15m, 80mm x 15m



Floor Safety

Scotchgard™ Surface Protection Film 2200

Scotchgard™ Surface Protection Film is designed to protect surfaces from the everyday challenges they are subjected to. It can be applied to waxed vinyl, sealed concrete, marble, ceramic tile, terrazzo and more. P2 Slip rating.

Sizes 2" x 2" Sheets

Country	3M Order Code	Product Number	Product Detail	Packout
AU	70071659612	2200	2ft x 2ft (610mm x 610mm)	10 sheets/case



Floor Safety

Protection that Shines

As a leading global manufacturer of slip-resistant products, 3M offers a full range of functional, slip-resistant materials designed for the safety of people in the workplace. These mineral and non-mineral coated products are suitable for industrial or residential applications in dry, wet or oily conditions. 3M™ Safety-Walk™ Slip-Resistant Tapes and Treads adhere to clean, dry surfaces without wrinkling, curling, tearing, shrinking or lifting and offer proven durability for long life. Pressure sensitive adhesive backing makes it easy to apply tapes and treads without the use of anchoring.

3M™ Safety-Walk™ Tapes and Treads meet or exceed the standards and recommended guidelines for slip resistance in accordance with AS/NZS requirements. Standard rolls and pre-cut treads are available in a variety of sizes, colours and textures ranging from fine resilient, medium resilient and general purpose to coarse and conformable material types. Custom sizes, pieces and die-cut shapes are available through an extensive national network of 3M authorized converters.



Floor Safety

3M™ Safety-Walk™ Slip-Resistant Fine Resilient Tapes and Treads - 200 Series

A fine-textured, slip-resistant surface with a pressure-sensitive adhesive backing provides enhanced safety and comfort in light and barefoot traffic areas.

- ▶ For wet, barefoot-traffic areas
- ▶ Non-mineral, fine-textured, slip-resistant vinyl surface
- ▶ High performance, water-resistant, acrylate adhesive is ideal for wet conditions
- ▶ Applications: showers, tubs, surfboards, around hot tubs and pools
- ▶ Standard sizes:
 - 25mm x 18.2m
 - 50mm x 18.2m
 - 100mm x 18.2m
 - 150mm x 18.2m
 - 300mm x 18.2m
 - Custom shapes and sizes are also available

Colours : White & Clear



3M™ Safety-Walk™ Slip-Resistant Medium Resilient Tapes and Treads - 300 Series

A soft textured, non-mineral, medium resilient surface bonded to a pressure-sensitive adhesive backed plastic film.

- ▶ For barefoot or shoe-traffic areas
- ▶ Non-mineral, medium textured, slip-resistant polyolefin surface
- ▶ Textured resilient high friction surface and durable adhesive provide long-lasting performance
- ▶ Applications: locker rooms, around hot tubs and pools, boats, personal watercraft, water skis, exercise equipment, conveyers
- ▶ Standard sizes:
 - 25mm x 18.2m
 - 50mm x 18.2m
 - 100mm x 18.2m
 - 150mm x 18.2m
 - 300mm x 18.2m
 - 600mm x 18.2m
 - 914mm x 18.2m
 - Custom shapes and sizes are also available

Colours : Black, Grey



*See price pages for list of Safety-Walk sizes, colours & codes

Floor Safety

3M™ Safety-Walk™ Slip-Resistant Conformable Tapes and Treads - 500 Series

A high-friction, slip-resistant material that has a special pressure-sensitive adhesive backed aluminum film that conforms around corners and adheres to irregular surfaces.

- ▶ For irregular or contoured surfaces in light to heavy shoe-traffic areas
- ▶ Mineral-coated, high friction slip-resistant surface
- ▶ Aluminum backing conforms to corners, curves, and irregular surfaces
- ▶ Aggressive, high performance adhesive forms an excellent bond for a secure hold
- ▶ Applications: stairs, ladders, loading ramps, platforms, irregular surfaces like diamond plating or flat surfaces with rivets or screw heads
- ▶ Safety yellow colour for high visibility and easy identification of hazard areas
- ▶ Standard sizes:
 - 25mm x 18.2m
 - 50mm x 18.2m
 - 100mm x 18.2m
 - 150mm x 18.2m
 - 300mm x 18.2m
 - 600mm x 18.2m
 - 914mm x 18.2m
 - Custom shapes and sizes are also available

Colours : Black & Yellow



*See price pages for list of Safety-Walk sizes, colours & codes

Floor Safety

3M™ Safety-Walk™ Slip-Resistant General Purpose Tapes and Treads - 600 Series

A mineral-coated, slip-resistant material adhered by a durable resin to a pressure-sensitive adhesive backed plastic film.

- ▶ For light to heavy shoe-traffic areas
- ▶ Mineral-coated, high friction slip-resistant surface
- ▶ Highly durable surface withstands the rigors of equipment traffic
- ▶ Low-profile design helps reduce trip hazard
- ▶ High performance pressure-sensitive adhesive for easy application
- ▶ Applications: flat surfaces, steps, stairways, entrances, ramps, ladders, lawn equipment, snowmobiles, scooters, construction machinery and vehicles
- ▶ Standard sizes:
 - 25mm x 18.2m
 - 50mm x 18.2m
 - 100mm x 18.2m
 - 150mm x 18.2m
 - 300mm x 18.2m
 - 600mm x 18.2m
 - 914mm x 18.2m
 - Custom shapes and sizes are also available

Colours : Black, Yellow, Clear, Black & Yellow



*See price pages for list of Safety-Walk sizes, colours & codes

Floor Safety

3M™ Safety-Walk™ Coarse Tapes and Treads - 700 Series

Extra-large mineral particles and durable construction provide additional slip resistance in extreme conditions.

- ▶ For extreme, heavy traffic areas
- ▶ Extra-large abrasive mineral particles help provide a stable slip-resistant surface even in the presence of water or oil
- ▶ High performance adhesive creates excellent bond to most surfaces
- ▶ An open abrasive pattern resists clogging and reduces clean up time
- ▶ Applications: construction vehicles, ship and plane decks, trains, semi-trailers, oily wet areas, platforms and ramps, machine shops, agriculture and forestry equipment, recreational vehicles
- ▶ Standard sizes:
 - 100mm x 18.2m
 - 150mm x 18.2m
 - 600mm x 18.2m
 - 1.2m x 100m
 - Custom shapes and sizes are also available

Colours : Black, Grey




*See price pages for list of Safety-Walk sizes, colours & codes

Floor Safety

OEM Custom Converting and Die Cutting

3M's national network of authorized converters can expertly match 3M technologies to customer requirements with the form, fit and functionality for application success. When a specific product design or architect drawing calls for a non-slip surface or an equipment part needs a slip-resistant component added, 3M™ Safety-Walk™ Materials can be easily die cut to meet your specific requirements. 3M™ Safety-Walk™ Slip-Resistant Products help provide traction on slippery surfaces and help meet AS/NZS standards. In addition, 3M™ Safety-Walk™ Coarse Tapes and Treads 700 Series meets, and is on the qualified products list associated with Military Specification MIL-PRF-24667C Type XI Comp PS covering non-skid systems.



Floor Safety

3M™ Safety-Walk™ Primer 901

► Solvent based adhesive prepares rough or porous surfaces before application of slip resistant tapes & treads.

Country	3M Order Code	Product Number	Product Detail	Packout
NZ	62214165508		946ml can	12 cans/case




3M™ Safety-Walk Edge Sealing Compound

► 3M™ Safety-Walk Edge Sealing Compound is a liquid, solvent-based sealer that protects exposed edges of slip-resistant tapes and treads from excessive moisture or liquids.
One 147 ml tube with convenient tube applicator seals approximately 22 to 30 linear metres.

Country	3M Order Code	Product Number	Product Detail	Packout
ANZ	62556926608		147.8mL	12 tubes/case





Matting

Over 30 years ago, 3M scientists developed a product which would help effectively protect building entrances from dirt. The first Nomad™ matting product with its revolutionary vinyl 'coiled loops' was developed to help remove moisture as well as dirt and debris. Incorporating carpet fiber technology, 3M expanded its entrance matting offering. Today, thanks to continuous innovation and proven expertise, 3M offers a complete line of entrance matting as well as Safety-Walk™ branded wet area and anti-fatigue work area matting.

Matting



Recessed Wells, Foyers



Work Areas



Drinking Fountains & Wet Areas



Food Service Areas



Entrances



Pool & Locker Room Areas

Matting


3M™ Safety-Walk Grip Economy Matting

- ▶ Ergonomic design.
- ▶ No substances of concern.
- ▶ Offers safety and comfort.
- ▶ Made from tough and durable natural rubber.

Colour: Black

Sizes: 600mm x 900mm & 900mm x 1500mm

Country	3M Order Code	Product Number	Product Detail	Packout
AU	AN019413747	ECGRIPS	Black 600mm x 900mm x 14mm	1 each




3M™ Safety-Walk Economy Dome Matting

- ▶ Anti-fatigue mat with a bubble surface that offers both safety and comfort.
- ▶ Made from tough and durable natural rubber with no substances of concern.

Colour: Black

Sizes: 600mm x 900mm & 900mm x 1200mm

Country	3M Order Code	Product Number	Product Detail	Packout
AU	AN019413762	ECDOMES	Black 600mm x 900mm x 14mm	1 each
AU	AN019413770	ECDOMEL	Black 900mm x 1200mm x 14mm	1 each




3M™ Safety-Walk Economy Open Hole Matting

- ▶ Slender mat that provides comfort and reduces fatigue.
- ▶ Raised surface edges provides safe footing and slip resistance.
- ▶ Light-weight and easy to clean.
- ▶ Available in Black and Terracotta colours.

Colour: Black

Size: 910mm x 1520mm

Country	3M Order Code	Product Number	Product Detail	Packout
AU	AN019413788	EC1000B	Black 910mm x 1520mm x 13mm	1 each




3M™ Safety-Walk Economy Ute Liner Matting

- ▶ Economy ute liner matting.
- ▶ Great for protection and safety

Colour: Black

Sizes: 1830mm x 1230mm

Country	3M Order Code	Product Number	Product Detail	Packout
AU	AN019413705	ECUTE	Black 1830mm x 1200mm	1 each



Matting

3M™ Safety-Walk™ Cushion Matting 5270


Textured, solid top surface, anti-fatigue cushion mat.

- ▶ Spring-coiled vinyl compresses uniformly and continually, helping provide greater comfort and less fatigue.
- ▶ Solid top allows debris to stay on top of the mat for easy cleaning.
- ▶ Special grease and oil-resistant coating keeps mat resilient over time, providing continuous comfort.
- ▶ Ideal for the workplace where people stand for extended periods of time.
- ▶ Designed for light to medium industrial use.

Colour: Black

Sizes: 914mm x 1.5m

Country	3M Order Code	Product Number	Product Detail	Packout
AU	70008400452	5270E	Black 900mm x 3m	1 each
AU	70008400445	5270E	Black 900mm x 1.5m	1 each



3M™ Safety-Walk™ Safety Cushion Mat 1200 Black/Red

Unbacked open hole construction mat for wet/greasy areas.

- ▶ Provides comfort and reduces fatigue.
- ▶ Raised surface edges provide safe footing and slip resistance.
- ▶ Safety bevel for smooth traffic and easy cart access.
- ▶ Open hole construction to allow debris and liquids to fall through.
- ▶ Grease resistant terracotta red for oil/greasy kitchen applications.
- ▶ Standard black mat recommended for non-greasy areas.
- ▶ Easy to clean, pick up and hose off.

Colour: Red & Black

Sizes: 910mm x 1.52m

Country	3M Order Code	Product Number	Product Detail	Packout
AU	AN019305943	1200	Black 910mm x 1520mm	1 each
AU	AN019305950	1200	Terracotta 910mm x 1520mm	1 each



Matting

3M™ Safety-Walk™ Cushion Matting 5100

Unbacked, vinyl z web cushion mat.

- ▶ Rigid vinyl Z-web construction provides firm support and allows cart traffic.
- ▶ Extended ridge design provides increased traction in wet areas, helping reduce slips and falls.
- ▶ Open Z-web design allows liquids and small debris to fall through enhancing the security of footing.
- ▶ Ideal for the workplace where people stand for extended periods of time.
- ▶ Designed for light industrial and light to medium commercial applications.


Colour: Red & Black

Sizes: 914mm x 1.5m & 914mm X 6m

Country	3M Order Code	Product Number	Product Detail	Packout
AU	75040057772	5100	Quarry Tile Red 914mm x 1.5m	1 each
AU	70008400551	5100	Quarry Tile Red 914mm x 6m	1 each
AU	70008400569	5100	Black 914mm x 1.5m	1 each



Black



Quarry Tile Red



3M™ Safety-Walk™ Wet Area Matting 1500


Unbacked, cushioned, vinyl loop mat for wet areas.

- ▶ Cushioned vinyl loops provide comfortable surface for barefoot traffic.
- ▶ Coiled vinyl loops reduce impact of dropped items that may otherwise shatter and be a danger to barefoot traffic.
- ▶ Open construction allows water to drain through, helping keep surfaces drier.
- ▶ Improves slip resistance, helping reduce falls.
- ▶ Antimicrobial coating provides resistance to mildew, fungus and odours in the mat.

Colour:Green

Sizes: 914mm x 6m

Country	3M Order Code	Product Number	Product Detail	Packout
AU	61500104692	1500	Green 914mm x 6m	1 each



Green

3M™ Nomad™ Medium Traffic Scraper Matting 6050


Backed, vinyl-loop matting for outdoor or indoor applications.

Designed for medium traffic conditions.


- ▶ Vinyl loops scrape, trap and hide dirt and moisture, minimising re-tracking into the building.
- ▶ Cushioned vinyl backing protects floors from removed soil and will not stain flooring.
- ▶ Durable vinyl construction performs in temperatures from -10°F to 150°F (-23°C to 65°C).
- ▶ Fade resistant.

Colour: Multiple


Sizes: 1.2m x 12m



Black



Gray



Green

*See price pages for list of Nomad™ sizes, colours & codes

Matting

3M™ Clean-Walk™ Mats

3M™ Clean-Walk™ are a multi-sheet adhesive system that captures dirt on contact from shoes, wheel and other passing objects. The top sheet easily peels away when soiled, instantly exposing a fresh, ready-to-use adhesive sheet.

- ▶ This mat system is suitable for every environment - from office, manufacturing, laboratory to warehouse
- ▶ Ideal for Clean Room environments as they contain antimicrobial properties that inhibit fungal growth in the mat
- ▶ Available in framed (60 sheets) or unframed (30 or 60 sheet options)

Sizes:

- 457mm x 1168mm
- 630mm x 1140mm
- 640mm x 800mm Framed

Country	3M Order Code	Product Number	Product Detail	Packout
AU	70006716925	5830	457mm x 1168mm- 30 sheets	1
ANZ	70006716917	5830	63cm x 114cm- 30 sheets	4
ANZ	70006716958	5836	63cm x 114cm- 60 sheets	4
AU	70006716933	5840	64cm x 80cm- Framed 60 sheets	1





Spill Management

3M pioneered the development of synthetic sorbents while leveraging one of our core technologies. Our sorbents contain no abrasive granules that can damage expensive equipment. Instead, they are made from microfiber materials, which contain millions of tiny pockets that absorb and hold liquids. Choose from petroleum (oil-only), maintenance (for non-aggressive liquids), and chemical (for most aggressive and non-aggressive liquids) formats.

Spill Management

Now more options

3M™ Sorbents are available in high capacity, medium capacity and traditional absorbency so you can select the right product for the size of your potential spill. These pads and rolls can be wrung out and reused many times with virtually no loss in absorbency. We complement our rolls and pads with booms, mini-booms, pillows, drum covers, spill kits and response packs for use with many types of spills and tasks.

Sustainability

Our high and medium capacity sorbents are lightweight to reduce the volume of waste going into landfill. 3M™ Sorbents may be incinerated with very low ash residue. High capacity sorbents contain at least 25 percent recycled content by weight. Medium capacity sorbents contain at least 50 percent recycled content by weight.

Additional benefits

- ▶ 3M's microbundle technology employs millions of tiny voids to absorb liquid - effectively doubling the capacity of the material
- ▶ 3M™ Sorbents absorb more so you don't have to use as much, and create less waste
- ▶ 3M™ Sorbents are made from inert polypropylene and polyester fibers that trap liquid in the voids
- ▶ 3M™ Sorbents are lightweight, non-abrasive and come in many shapes and sizes to perfectly fit your application
- ▶ 3M™ Petroleum Sorbents can be reused; 90 percent of the oil can be wrung out and reclaimed
- ▶ 3M™ High and Medium Capacity Sorbents are made with scrim on one or two sides to help eliminate linting



Spill Management

Cost Benefits of 3M™ Sorbents


Because of 3M™ Sorbents’ superior absorbency properties, they offer significant cost benefits associated with materials, labour and disposal.

Sorbing a 94 Litre Spill

Number of pads required

77 Pads
3M HP-156
Petroleum Sorbent

146 Pads
Competitive Multi-Layer,
Heavy Oil Only Sorbent



Kilograms (kg) of Sorbent going into Disposal

3kg
3M HP-156
Petroleum Sorbent

11kg
Competitive Multi-Layer,
Heavy Oil Only Sorbent




Cost Comparison: 3M™ Sorbents vs. Clay Granules

Materials estimated for cleaning up 94 Litres of fluid

0.77 Case
3M M-PD1520DD
Sorbent Pads (66 pads)

5.70 Bags
(20kg/BAG)
Clay Granules




Labour to sorb 82kg of oil

32 Minutes
Worker Clean-up
Time
3M Sorbent

2.7kg/min

234 Minutes
Worker Clean-up
Time,
Plus Breaks
Clay Granules


0.9kg/min



Drums & Disposal

0.5 Drum
3M Sorbent & Fluid

1.6 Drums
Clay Granules & Fluid



Spill Management

Different Types of Sorbents



3M™ Oil & Petroleum Sorbents

- ▶ For control and clean-up of petroleum-based fluids
- ▶ Repels water and floats
- ▶ For use on land or water



3M™ Chemical Sorbents

- ▶ For control and clean-up of most hazardous liquids
- ▶ Resists reactions with most hazardous chemicals, including acids
- ▶ Absorbs petroleum-based and aqueous-based solutions



3M™ Maintenance Sorbents

- ▶ For control and clean-up of non-aggressive liquids
- ▶ Helps maintain a clean and safe working environment
- ▶ Absorbs petroleum-based liquids and aqueous-based liquids

Spill Management

Chemical Sorbent Pads

3M™ Chemical Sorbent Pad C-PD914DD

Barcode: 50051138290967

SKU: 70070408235

Size: 23 x 36cm, 590ml per pad

Quantity: 25 pads/box, 6 boxes/case



3M™ Chemical Sorbent Folded C-FL550DD/P-F2001

Barcode: 50051138464962

SKU: 70070708030

Size: 45cm x 15m, 40L/box
3 box/case

Quantity: 3 boxes/case



Chemical Sorbent Rolls

3M™ Chemical Sorbent Roll C-RL15150DD*

Barcode: 50051138290979

SKU: 70070408243

Size: 38cm x 45m, 117L/roll

Quantity: 1 roll/case



Chemical Sorbent Booms


3M™ Chemical Sorbent Mini-Boom P-200

Barcode: 50051138175967

SKU: 70070189314

Size: 7.5cm x 1.2m, 3.8L/boom

Quantity: 12 booms/case



Chemical Sorbent Pillows


3M™ Chemical Sorbent Pillow P-300

Barcode: 50051138175974

SKU: 70070189322

Size: 23cm x 38cm, 2L/pillow

Quantity: 16 pillows/case



Chemical Sorbent Spill Kits

3M™ Chemical Sorbent Spill Kit SPK10L**

SKU: XH000766192

Size: 10L

Contains: 1/4 3M™ Chemical Folded Sorbent C-FL550DD,
1 x 3M™ Respirator 3M 4277 (A1B1E1P2),
1 x Safety Goggles,
1 x Pair Oil Resistant Gloves,
1 x Contaminated Waste Bag,
1 x Spill Response Procedures,
1 x Plastic bucket with lid



3M™ Chemical Sorbent Spill Response Kit SRP-Chem*

SKU: AT010797341

Size: 17L/kit

Quantity: 2/Case

Contains: 10 x 3M™ Chemical Sorbent Pads C-PD914DD,
3 x 3M™ Chemical Sorbent Mini Booms P200,
1 x Contaminated Waste Bag



*Not available in New Zealand.

Spill Management

Chemical Sorbent Spill Kits

3M™ Chemical Sorbent Cab Bag Spill Kit CSRB-Chem*

Barcode: 05931006301158

SKU: AT010580648

Size: 25L

Quantity: 1 Kit



Contains: 20 x 3M™ Chemical Sorbent Pads C-PD914DD, 3 x 3M™ Chemical Mini Booms P200, 2 x 3M™ Chemical Pillows P300, 1 x 3M™ Respirator 4277 (A1B1E1P2), 1 x 3M™ Fahrenheit™ Safety Goggles, 1 x 3M™ 4510 Protective Coveralls XL, 1 x Pair Oil Resistant Gloves, 1 x Cabin Bag, 1 x Contaminated Waste Bag, 1 x Spill Response Procedures

3M™ Chemical Sorbent Spill Response Pack CSRK-180*

SKU: AT010575218

Size: 180L

Quantity: 1 Kit



Contains: 12 x 3M™ Chemical Mini Booms - P200, 8 x 3M™ Chemical Pillows - P300, 3 x 3M™ Folded Chemical Sorbent Rolls C-F1550DD, 2 x 3M™ Respirator 3M 4277 (A1B1E1P2), 2 x 3M™ Fahrenheit™ Safety Goggles, 2 x 3M™ 4510 Protective Coveralls XL, 2 x Pair Oil Resistant Gloves, 1 x 240L Wheelie Bin, 5 x Containment Waste Bag, 1 x Spill Response Procedures

3M™ Chemical Sorbent Spill Kit CSRK-35*

SKU: AT010575200

Size: 35L

Quantity: 1 Kit



Contains: 20 x 3M™ Chemical Pads C-PD914DD, 6 x 3M™ Chemical Sorbent Mini Booms P200, 2 x 3M™ Chemical Pillows P300, 1 x 3M™ Respirator 3M 4277 (A1B1E1P2), 1 x 3M™ Fahrenheit™ Safety Goggles, 1 x 3M™ 4510 Protective Coveralls XL, 1 x Pair Oil Resistant Gloves, 1 x 60 Litre Drum, 1 x Contaminated Waste Bag, 1 x Spill Response Procedures

General Purpose Sorbent Pads

3M™ General Purpose Sorbent Pad M-PD1520DD

Barcode: 50051131071648

SKU: 70070408755

Size: 40cm x 52cm, 1.4L / pad

Quantity: 100 pads/case



3M™ General Purpose Sorbent Folded M-FL550DD

Barcode: 50051131071723

SKU: 70070408771

Size: 45cm x 15M, 40L/box

Quantity: 3 boxes/case



*Not available in New Zealand. **Not available in Australia

Spill Management

General Purpose Sorbent Rolls

3M™ General Purpose Sorbent Roll M-RL38150DD

Barcode: 50051131071679

SKU: 70070408730

Size: 96cm x 96cm 45cm
287L/roll

Quantity: 1 roll/case



General Purpose Sorbent Booms

3M™ General Purpose Sorbent Mini-Boom M-MB308

Barcode: 50051138215274

SKU: 70070313567

Size: 7.6cm x 2.4m/boom
7.5L/boom, 45L/case

Quantity: 6 booms/case



General Purpose Particulate Sorbent

3M™ Floorsweep Sorbent FLS-10*

Barcode: AT010583766

SKU: 9310063046510

Size: 10Kg per bag
60 bags per pallet

Quantity: 100 pads/case



*Not available in New Zealand.

General Purpose Spill Kits

3M™ General Purpose Spill Kit Cabin Bag SRCB-Gen*

Barcode: AT010579988

Size: 35L

Quantity: 1 Kit

Contains: 20 × 3M™ General Purpose Sorbent Pad,
1 × 3M™ General Purpose Sorbent Boom,
1 × Weather Proof Zippered Cabin Bag,
1 × Pair of Solvent & Oil Resistant Gloves,
1 × Contaminated Waste Bag,
1 × Spill Response Procedures



3M™ General Purpose Spill Kit Wheelie Bin MSRK-130*

Barcode: AT010565805

Size: 130L

Quantity: 1 Kit

Contains: 25 × 3M™ General Purpose Sorbent Pad,
2 × 3M™ General Purpose Sorbent Boom,
1 × 3M™ General Purpose Folded Sorbent,
1 × 3M™ Floorsweep,
1 × 3M™ 4510 Protective Coveralls XL,
1 × 120L Wheelie Bin,
1 × Pair of Solvent and Oil Resistant Gloves,
1 × Contaminated Waste Bag,
1 × Spill Response Procedures,
5 × Tamper Seals



3M™ General Purpose Spill Kit Wheelie Bin MSRK-210*

Barcode: AT010579970

Size: 210L

43cm x 48cm x 0.5cm
1.4L/pad, 86cm x 96cm
6L/pad

Quantity: 1 Kit

Contain: 50 × 3M™ General Purpose Sorbent Pad,
3 × 3M™ General Purpose Sorbent Boom,
2 × 3M™ General Purpose Folded Sorbent,
1 × 3M™ Floorsweep,
1 × 3M™ 4510 Protective Coveralls XL,
1 × 240L Wheelie Bin,
2 × Pair of Solvent and Oil Resistant Gloves,
5 × Contaminated Waste Bag,
1 × Spill Response Procedures,
5 × Tamper Seals



Spill Management

Petroleum Sorbent Pads

3M™ Petroleum Sorbent Pad HP-156

Barcode: 50051138289916
Sku: 70070405785
Size: 43cm x 48cm x 0.5cm
1.4L/pad
Quantity: 100 pads/case



3M™ Petroleum Sorbent Pad HP-255*

Barcode: 50051138289923
Sku: 70070405793
Size: 43cm x 48cm x 2.5L/pad
50 pad/bale
Quantity: 50 pads/case



3M™ Petroleum Sorbent Pad HP-157

Barcode: 00051138291167
Sku: 70070408557
Size: 86cm x 96cm, 6L/pad
Quantity: 50 pads/case



3M™ Petroleum Sorbent Folded P-FL550DD

Barcode: 5005131071730
Sku: 70070708063
Size: 45cm x 15m, 40L/box
3 box/case
Quantity: 3 boxes/case



Petroleum Sorbent Rolls

3M™ Petroleum Sorbent Roll HP-100

Barcode: 00051138289904
Sku: 70070405777
Size: 97cm x 44m x 0.5cm, 277L/roll
Quantity: 1 roll/case



Petroleum Sorbent Booms

3M™ Petroleum Sorbent Single Boom T-270

Barcode: 50021200160542
Sku: 98071106334
Size: 20cm x 3m, 76L/boom
Quantity: 4 booms/case



3M™ Petroleum Sorbent Double Boom T-280*

Barcode: 00021200160851
Sku: 98071108074
Size: 23cm x 10cm x 3m, 38L/boom
Quantity: 4 booms/case



3M™ Petroleum Sorbent Mini-Boom T-4

Barcode: 50051138213546
Sku: 70070221364
Size: 7.5cm x 1.2m, 3.8L/boom
Quantity: 12 booms/case



*Not available in New Zealand.

**Not available in Australia.

Spill Management

Petroleum Sorbent Pillows

3M™ Petroleum Sorbent Pillow T-240

Barcode: 00021200160530

SKU: 98071101996

Size: 36cm x 63cm, 13L/pillow

Quantity: 10 pillows/case



Petroleum Sorbent High Performance Spill Response Kits with PPE

3M™ Oil & Petroleum Sorbent Spill Kit Cabin Bag SRCB-Gen*

Barcode: 5931006301158

SKU: AT010575002

Size: 45L

Quantity: 1 Cab Bag Spill Kit

Contains: 10 x 3M™ Oil Sorbent Pads - HP156,
4 x 3M™ Oil Sorbent Mini Booms T4,
1 x 3M™ Respirator 3M 4251 (A1P2),
1 x 3M™ Fahrenheit™ Safety Goggles,
1 x 3M™ 4530+ Protective Coveralls XL,
1 x Pair Oil Resistant Gloves,
1 x Cabin Bag,
1 x Contaminated Waste Bag,
1 x Spill Response Procedures



3M™ Oil & Petroleum Sorbent Spill Kit Drum OSRK-45*

Barcode: 59310063011537

SKU: AT010575010

Size: 45L

Quantity: 1 Spill Kit Drum

Contains: 17 x 3M™ Oil Sorbent Pads - HP156,
6 x 3M™ Oil Sorbent Mini Booms T4,
1 x 3M™ Respirator 3M 4251 (A1P2),
1 x 3M™ Fahrenheit™ Safety Goggles,
1 x 3M™ 4530+ Protective Coveralls XL,
1 x Pair Oil Resistant Gloves,
1 x 60 Litre Drum,
1 x Contaminated Waste Bag,
1 x Spill Response Procedures



Petroleum Sorbent High Performance Spill Response Kits with PPE (Cont'd)

3M™ Oil & Petroleum Sorbent Spill Kit Wheelie Bin OSRK-190*

Barcode: 5931006301158

SKU: AT010575143

Size: 190L

Quantity: 1 Spill Kit Wheelie Bin

Contains: 25 x 3M™ Oil Sorbent Pads - HP156,
2 x 3M™ Double Booms T280,
2 x 3M™ Folded Petroleum Rolls - PFL550DD,
2 x 3M™ Respirator 3M 4251 (A1P2),
2 x 3M™ Fahrenheit™ Safety Goggles,
1 x 3M™ 4530+ Protective Coveralls XL,
2 x Pair Oil Resistant Gloves,
1 x 240 Litre Wheelie Bin,
5 x Contaminated Waste Bag,
1 x Spill Response Procedures



Oil High Performance Workshop Spill Kits - without PPE

3M™ Oil HP Workshop Spill Kit OPWSK-300*

Barcode: 9310063054652

SKU: AT010597980

Size: 300L

Quantity: 1 300L Spill Kit

Contains: 125 x HP-156 Oil Pads;
8 x HP Oil T4 Mini booms;
2 x Oil HP PFL550DD Folded sorbent;
1 x FLS-10 Floorsweep;
2 x Gloves;
8 x Waste Bags;
1 x Spill Procedures;
1 x 240L wheelie bin



*Not available in New Zealand.

For more information about Cleaning & Workplace Safety Supplies please contact us:

Australia

TechAssist Helpline 1800 024 464
TechAssist Email techassist@mmm.com
Customer Service 1300 363 565

New Zealand

TechAssist Helpline 0800 364 357
Customer Service 0800 252 627



3M Commercial Solutions

3M Australia Pty Limited
Building A, 1 Rivett Road
North Ryde NSW 2113
TechAssist Helpline: 1800 024 464
TechAssist Email: techassist@mmm.com
Customer Service: 1300 363 565
Website: 3m.com/au/facilities

3M New Zealand Limited
94 Apollo Drive, Rosedale
Auckland 0632
TechAssist Helpline: 0800 364 357
Customer Service: 0800 252 627

3M is a trademark of 3M Company.
© 3M 2023. All rights reserved.