


Properties	Round, Jacketed Flat Cable
	
Part Number	3759-XX
Application	Protected Input/Output interconnections
Conductor spacing (mm)	1.27
Conductor type	Stranded
Conductor size	28 AWG
Insulation material	PVC
Colour	Black jacket Grey cable
First conductor marking	Red
Insulation resistance ( / 3m)	> 1 x 10 <sup>10</sup>
Conductor quantity	9, 10, 14, 15, 16, 20, 25, 26, 30, 34, 37, 40, 50, 64
Length (m)	30.48/91.44
Impedance ( ) unbalanced	90
Capacitance (pF/m) unbalanced	54.8
Inductance (µH/m) unbalanced	0.46
Propagation delay (ns/m) unbalanced	4.92
Voltage rating (v)	NEC 725, CL2 CSA 300
Temperature rating (°C)	-20 +80
APPROVALS	UL E118773 CL2 (AWM Style 20267) CSA LL53649