


Welding, cutting, grinding and finishing



Hazards



Exposure to arc radiation



Welding fumes



Foreign body eye injuries



Exposure to noise



Falling objects

3M Safety Solutions



3M™ Speedglas™ 9100 XXi Welding Helmet

► Part # [06-0100-30iSW](#)

Improved optics deliver more natural color and contrast.



3M™ Speedglas™ 9100 Hard Hat Adapter

► Part # [06-0014-00NR](#)

If Hard Hat required, add Loop Adapter.



3M™ Particulate Respirator 8515

► Part # [8515](#)

Cool Flow™ valve technology for comfort while welding.



3M™ Reusable Respirator 6502QL

► Part # [6502QL \(Med\)](#)

Rugged comfort and low-profile fit for use under most welding helmets.

3M™ Particulate Filter 2097

► Part # [2097](#)



3M™ Solus, 1000-Series, S1101SGAF-KT

► Part # [S1101SGAF-KT](#)

Resists fogging in hot, humid environments.



3M™ Clear Polycarbonate Faceshield WP96

► Part # [82701-00000](#)

3M™ Universal Headgear For Hard Hat H24M

► Part # [82520-10000](#)



Hearing Products: 3M™ E-A-R™ Push-Ins™ Corded Earplugs

► Part # [318-1001](#)



3M™ PELTOR™ Welding Earmuffs H505B

► Part # [H505B](#)

Designed to fit under welding helmets, particularly under the 3M™ Speedglas™ 9100.



3M™ Hard Hat H-701R

► Part # [H-701R](#)

Easy adjust ratchet suspension for secure fit and lightweight comfort.



3M™ DBI-SALA® Fall Protection for Tools Utility Pouch

► Part # [1500130](#)

Helps prevent falling hazards – keeps tools and parts securely attached.

3M™ DBI-SALA® Fall Protection for Tools Adjustable Radio Holster

► Part # [1500089](#)

Keeps radios handy but securely attached.

3M™ Integrated Safety Solutions



3M™ Speedglas 9100 FX-Air Welding Helmet with Adflo

► Part # [36-1101-30SW](#)

Designed for welders working in higher altitude locations. Blower unit adjusts for changes in air density. The welding helmet can help provide overhead protection and increased peripheral vision. Auto-Darkening Filter not included.

