



3M Science.
Applied to Life.™

Leave no trace.

NEW! 3M™ Film Disc 371L
Available in grades 80 to
400 for use on aluminum
and other metals

Low-loading – without the use
of anti-loading coatings that can
contaminate paint finishes.



3M™ Film Disc 371L

Take a load off!

A low-loading, stearate-free solution for “body in white” and paint preparation.

Now, 3M introduces an advanced new film disc construction, especially designed for metal finishing and paint preparation of aluminum, steel and other metals used in automotive applications.

New 3M™ Film Disc 371L is engineered to be low-loading, without the use of stearate-based anti-loading coatings. And its durable, flexible film backing handles sharp edges with less risk of tearing.

- Durable, tear-resistant film construction
- Premium abrasive, for a fast cut
- Flexible, smooth film backing conforms to contours and rounded edges
- Flat film backing produces a uniform and consistent finish
- Easy-to-use 3M™ Hookit™ Attachment System allows quick disc changes, for improved productivity



Ordering information

UPC 076308-	Size	Grade	Max RPM	Case Quantity
66161-8	5" X NH	P80	12,000	250
66162-5	5" X NH	P100	12,000	250
66163-2	5" X NH	P120	12,000	250
66164-9	5" X NH	P150	12,000	250
66165-6	5" X NH	P180	12,000	250
66166-3	5" X NH	P220	12,000	250
66155-7	5" X NH	P240	12,000	250
66157-1	5" X NH	P320	12,000	250
66159-5	5" X NH	P400	12,000	250
66167-0	6" X NH	P80	12,000	250
66168-7	6" X NH	P100	12,000	250
66169-4	6" X NH	P120	12,000	250
66170-0	6" X NH	P150	12,000	250
66171-7	6" X NH	P180	12,000	250
66172-4	6" X NH	P220	12,000	250
66156-4	6" X NH	P240	12,000	250
66158-8	6" X NH	P320	12,000	250
66160-1	6" X NH	P400	12,000	250

Warranty, Limited Remedy, and Disclaimer: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. User is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application. Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



Abrasive Systems Division
3M Center, Building 223-6S-03
St. Paul, MN 55144-1000
1-866-279-1235
www.3M.com/abrasives

Please recycle. Printed in USA.
© 3M 2016. All rights reserved.
Issued: 8/16 11684HB
61-5002-8421-3

3M and Hookit are trademarks of 3M Company.
Used under license by 3M subsidiaries and affiliates.