

3M Science.
Applied to Life.™

3M Attachment Solutions

**Fast and secure document
attachments for the
toughest journey.**



More choices than ever for document control and protection.

3M™ Packing List Envelopes

A wide variety of choices for document control and protection.

3M™ Packing List Envelopes are an ideal way to save time and increase your productivity in the mailroom, on the shipping dock and around the office. Packing List Envelopes offer you convenient peel-off liners and a reliable pressure sensitive adhesive.

- Wide variety of standard sizes to fit your document control requirements
- Non-printed and printed envelopes with standard messages
- Custom sizes and/or custom printed messages

| T (Top Printed) | | | |
|---|--|--|--|
| PLE-T1 PACKING LIST/ INVOICE ENCLOSED 4.5" x 5.5" 1,000/case | | PLE-T1 INV INVOICE ENCLOSED 4.5" x 5.5" 1,000/case | |
| PLE-T1 PACKING LIST/ INVOICE ENCLOSED 4.5" x 5.5" | | PLE-T2 PACKING LIST/ INVOICE ENCLOSED 4.5" x 6" 1,000/case | |
| PLE-T3 PACKING LIST/ INVOICE ENCLOSED 7" x 5.5" 1,000/case | | PLE-T4 PACKING LIST/ INVOICE ENCLOSED 5.5" x 10" 1,000/case | |

| NP (Non-Printed) | |
|--|--|
| NP1 NO PRINT (CLEAR) 4.5" x 5.5" 1,000/case | |
| NP2 NO PRINT (CLEAR) 4.5" x 6" 1,000/case | |
| NP3 NO PRINT (CLEAR) 5.5" x 7" 1,000/case | |
| NP4 NO PRINT (CLEAR) 5.5" x 10" 1,000/case | |
| NP5 NO PRINT (CLEAR) 7" x 10" 1,000/case | |
| NP6 NO PRINT (CLEAR) 9.5" x 12" 1,000/case | |
| NP9 NO PRINT (CLEAR) 7" x 6" 1,000/case | |
| FED1 NO PRINT (PERFED) 6.75" x 10.75" 500/case | |

| F (Full Face Printed) | |
|---|--|
| F1 PACKING LIST/ INVOICE ENCLOSED 4.5" x 5.5" 1,000/case | |

| Custom Packing List Envelopes |
|---|
| PLE-C (CUSTOM PRINTED) Available in all standard sizes. 1,000/case |

| Zipper Closure Envelope | |
|--|--|
| NPZ-L NO PRINT (CLEAR) 8.5" x 11.5" 500/case | |
| NPZ-XL NO PRINT (CLEAR) 10" x 12.5" 500/case | |

document control and protection.

Scotch® RCT Pouch Tapes

A fast and easy way to attach shipping documents while reducing waste—now that's smart.




Scotch® Pouch Tapes have a sticky border with a non-tack center for attaching shipping documents, brochures or even product samples to shipping containers.

Stickier than other solutions

We've eliminated the liner

Durable, yet conformable film handles curves and bumps

- **Proprietary adhesive** designed specifically to stick to recycled corrugate cartons
- Won't rub or pop off, reducing delayed or lost packages
- No slippery, tricky liners to remove for faster application and reduced clutter in work areas
- Low profile design reduces label shear off in transit
- Moisture- and abrasion-resistant barrier to withstand the rigors of shipping






On a roll for the fastest time savings
 Improve throughput by up to 40% by pairing Scotch® Pouch Tape 824RCT with companion dispensers M797 or M727.

Scotch® Adjustable Tape Dispenser M797
 Easily adjusts to all Scotch® Pouch Tape sizes. Extra high platform for easy dispensing.

Scotch® Adjustable Tape Dispenser M797
 For use with Scotch® Pouch Tapes up to 5' wide.

On a pad for portability and pre-cut convenience
 Take the Scotch™ Pouch Tape Sheets 830RCT anywhere you go—no cutting—no cutting, minimal waste.



| 3M ID | Description | Sizes | Printed message (custom print available) |
|--------|-------------------------------------|---------------------------|---|
| 824RCT | Roll format | 5" x 6", 5" x 8", 6" x 8" | DOCUMENTS ENCLOSED DOCUMENTOS ADJUNTOS |
| 830RCT | Padded sheets | 5" x 8" and 8" x 10" | DOCUMENTS ENCLOSED DOCUMENTOS ADJUNTOS |
| M727 | Dispenses Pouch Tapes up to 5" wide | | |
| M797 | Adjustable for any Pouch Tape width | | |

Well-defined cutting area for fast and easy application.
 Preprinted bilingual message, or custom print with brand/marketing message.



See for yourself: Time Savings
3m.com/ScotchPouchTapeEraserDemo



3M™ Tape Pads

No dispenser? No problem.

- Portable “peel and stick” convenience, 25 sheets per pad
- Adheres to bags, boxes, plastic film, powder coats, metals and glass
- Removable tab for easy handling
- Stores easily in pockets, drawers, tool boxes and part carts
- Used to repair, patch, seal, protect, reinforce, close and trap



3M™ Packaging Tape Pad 3750P



3M™ Tape Sheets 822

| Product | Sheet size(s) | Color | Tape material | Total thickness mil (mm) | Tensile strength lb/in (N/100mm) | Adhesive type | Adhesion strength oz/in (N/100mm) | Elongation (%) | Tab |
|---------|---------------------------------|--------------------------|---------------|--------------------------|----------------------------------|------------------|-----------------------------------|----------------|------------------------|
| 809G | Custom size | Transparent, Red, Yellow | Polypropylene | 3.1 (0.079) | 35 (613) | Synthetic rubber | 55(60) | 160 | Removable or permanent |
| 809S | Custom size w/ custom backsheet | Transparent | | | | | | | |
| 822 | 4" x 6" | Transparent | | | | | | | Removable |
| 3750P | 2" x 6" | | | | | | | | |

Note: This technical information and data should be considered representative or typical only and should not be used for specification purposes.

Product use: All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M’s control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user’s knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user’s method of application.

Warranty and Limited Remedy: Unless stated otherwise in 3M’s product literature, packaging inserts or product packaging for individual products, 3M warrants that each 3M product meets the applicable specifications at the time 3M ships the product. Individual products may have additional or different warranties as stated on product literature, package inserts or product packages. 3M MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user’s application. If the 3M product is defective within the warranty period, your exclusive remedy and 3M’s and seller’s sole obligation will be, at 3M’s option, to replace the product or refund the purchase price.

Limitation of Liability: Except where prohibited by law, 3M and seller will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



Closure and Masking Systems Division

3M Center, Building 225-3S-06
 St. Paul, MN 55144-1000
 800-362-3550
 877-369-2923 (Fax)

3M and 3M Science. Applied to Life. are trademarks of 3M Company. Please recycle. Printed in USA.
 © 3M 2023. All rights reserved.