



Bondo® Filler Comparison Chart

       								
PRODUCT	 ORIGINAL All purpose solution for repairing dents, dings, and scratches in your home or on your car	 FAST DRY Premium formula for repairing dents, dings, and scratches around your home or on your car faster and easier	 SHORT STRAND FIBERGLASS REINFORCED Ideal for small hole repair and rust-out repairs on cars and boats	 LONG STRAND FIBERGLASS REINFORCED Ideal for large hole repair, rust out areas, rebuilding missing pieces, shattered fiberglass, and more	 EXTREME METAL REINFORCED Exceptionally strong formula can be drilled, anchored, or tapped to repair or rebuild cosmetic damage	 WOOD Quick, durable repairs to restore damaged, missing and dented wood	 LIQUID RESIN FOR FIBERGLASS Waterproof formula for repairing chips and cracks or rebuilding surfaces on fiberglass, metal, wood, and masonry	 GLAZING & SPOT PUTTY Versatile formula ideal for covering minor scratches, rock chips, road rash, pinholes, holes, and nicks
TOP APPLICATION								
SUMMARY	Bondo® Original Filler is a lightweight formula for general purpose automotive dent repairs and home restoration needs.	Bondo® Fast Dry Filler is designed to help you get all the same jobs done as our Bondo Original filler, faster and easier. It's the fastest drying Bondo product, and can be sanded in just 15 minutes.	Bondo® Short Strand Fiberglass Reinforced Filler contains short strands of fiberglass and spreads easily, repairing holes up to 1/2 inch in diameter without the need for a backup screen or body patch. Can be used on your car, boat, or home restoration jobs.	Bondo® Long Strand Fiberglass Reinforced Filler features strands of chopped fiberglass up to 1 inch long for extra strength on your toughest repairs. Tackle filling large rust holes and restoring shattered fiberglass. Can be used on your car, boat, or home restoration jobs.	Bondo® Extreme Metal Reinforced Filler is the strongest Bondo filler for repairing small areas that need to be drilled, tapped, or anchored. Ideal for a wide range of cosmetic and non-structural car or home repairs.	Bondo® Wood Filler can be used to make highly durable, same day repairs to damaged and rotted wood. Quickly fix doors, windows, fences, wood trim, and more.	Bondo® Liquid Resin for Fiberglass is an industry standard for restoration and repair of cars, boats and homes. The high strength polyester resin features a waterproof formula, is highly durable, and provides long-lasting repairs.	Bondo® Glazing and Spot Putty smooths and repairs pin holes, scratches, nicks, minor dents, stone chips, and other surface imperfections in auto bodies and paint.
PROJECT IDEAS	Automotive restoration and dent repair, smoothing out fiberglass repairs.	Automotive restoration and dent repair, smoothing out fiberglass repairs.	Repairing small rust out areas and holes up to 1/2 inch diameter in metal and fiberglass.	Repairing rust out areas and holes up to 1 inch diameter in metal and fiberglass.	Repairing non-structural cosmetic damage to alloy vehicle wheels, repairing furniture fixtures and hinges, parts that need to be drilled and tapped.	For use on wood cabinets, furniture, floors, decks, window sills, exterior trim, fences, siding, doors, and baseboards.	Repairing damage in fiberglass substrates. Useful on fiberglass boats, showers, hot tubs, and vehicle parts. Can be used as a concrete and wood sealer.	Can be applied as a top coat to Bondo Fillers to eliminate pin holes and imperfections during final finishing.
SURFACES	IDEAL FOR metal, aluminum, wood ALSO WORKS WITH concrete, masonry surfaces	IDEAL FOR metal, aluminum, wood ALSO WORKS WITH concrete, masonry surfaces	IDEAL FOR metal, fiberglass, ceramic ALSO WORKS WITH wood, concrete, masonry surfaces	IDEAL FOR metal, fiberglass, ceramic ALSO WORKS WITH wood, concrete, masonry surfaces	IDEAL FOR concrete, masonry surfaces, metal ALSO WORKS WITH wood, fiberglass	IDEAL FOR wood-based trim, siding, window sills, decks, doors, and furniture	IDEAL FOR fiberglass ALSO WORKS WITH metal, wood, rigid plastics	IDEAL FOR metal, fiberglass and wood as well as sanded and primed or painted surfaces
CURE/SAND TIME	20 minutes	15 minutes	30 minutes	30 minutes	20 minutes	15 minutes	2 hours	20 minutes
WATERPROOF	No	No	Yes	Yes	No	No	Yes	No
STAINABLE	No	No	No	No	No	Yes	No	No
PAINTABLE	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes
HARDENER	Blue Cream Hardener included	Blue Cream Hardener included	Blue Cream Hardener included	Blue Cream Hardener included	Clear Liquid Hardener included	Blue Cream Hardener included	Clear Liquid Hardener included	None required
COLOR WHEN CURED	Light Blue	Light Blue	Dark Green	Dark Green	Gray	Golden Yellow	Translucent Light Brown	Maroon