

3M™ Power Tools for Body Repair

3M™ Pistol Grip Disc Sander

The 3M™ Pistol Grip Disc Sander is a light-weight tool with the power to grind welds and the size to access small and hard-to-reach areas. Perfect for grinding and sanding applications with our 3M™ Cubitron™ II Fibre Roloc™ Discs.

- Maximize cut speed with 3M™ Cubitron™ II Fibre Roloc™ Discs
- Suitable for both 2 inch and 3 inch discs
- Variable speed adjustment for optimal finish



3M™ Cut-Off Wheel Tools

The 3M™ Cut-Off Wheel Tools deliver the performance you need when working with tough automotive substrates. When paired with 3M™ Cubitron™ II Cut-Off Wheels, technicians can slice through even high-strength steel and aluminum with clean, straight lines and minimal effort.

- Power with a 3M™ Cubitron™ II Cut-Off Wheel for a cleaner cut that runs cooler
- Compact design with built-in safety features for easy handling
- Featuring a light-weight composite body for greater user comfort
- Available in 3 inch and 4 inch sizes



3M™ Mini File Belt Sander and File Belt Sander

The 3M™ File Belt Sanders allow technicians to access hard-to-reach areas and are great for spot weld removal, deburring, cleaning, and finishing.

- Remove spot welds cleanly and quickly with 3M™ Cubitron™ II File Belts — replacing the need for expensive drills and bits
- Adjustable arm for user comfort and multiple applications
- Available in 13 inch and 18 inch sizes



3M™ Pistol Grip Disc Sander

Part No.	Max RPM	Thread Size	Weight lb (kg)	Height in. (mm)	Length in. (mm)	Motor hp (W)
Use with 2 in. (50mm) and 3 in. (75mm) discs*						
33577	18,000	1/4 in. – 20	1.76 (0.8)	2.05 (52)	7.50 (189)	0.45 (336)

*Tool includes a 2 in. (50mm) and 3 in. (75mm) 3M™ Roloc™ Disc Pad.



PN 33577

3M™ Cut-Off Wheel Tools

Part No.	Wheel Size in. (mm)	Max RPM	Thread Size	Weight lb (kg)	Height in. (mm)	Length in. (mm)	Motor hp (W)
ALWAYS USE WITH GUARD							
33579	3 (75)	20,000	1/4 in. – 28	1.91 (0.87)	3.14 (79.6)	7.73 (196)	0.70 (522)
33581	4 (100)	20,000	1/4 in. – 28	2.00 (0.91)	3.42 (86.9)	7.73 (196)	0.70 (522)



PN 33579

3M™ Mini File Belt Sander and File Belt Sander

Part No.	Belt Size in. (mm)	Max RPM	Weight lb (kg)	Height in. (mm)	Length in. (mm)	Motor hp (W)
Belt Speed: 4100 SFPM (1250 SMPM)						
33573	3/8 × 13 (10 × 330)	17,000	2.07 (0.94)	2.87 (73)	12.50 (320)	0.65 (485)
33575	1/2 × 18 (13 × 457)	17,000	2.16 (0.98)	2.87 (73)	15.15 (385)	0.65 (485)



PN 33573

Replacement Parts — in. (mm)	
33583 Replacement Contact Wheel, 3/8 (10)	33585 File Belt Replacement Arm, 3/8 × 13 (10 × 330)
33584 Replacement Contact Wheel, 1/2 (13)	33588 File Belt Replacement Arm, 1/2 × 18 (13 × 457)

Learn more about our complete system of body repair solutions at **3MCollision.com**



For videos and more scan code



Automotive Aftermarket Division
3M Center, Building 223-6N-01
St. Paul, MN 55144 USA

Phone 1-877-666-2277
Web 3MCollision.com

For Professional Use Only.

Warranty and Limited Remedy: 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER EXPRESS OR IMPLIED WARRANTIES OR CONDITIONS, INCLUDING ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If the 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted.

3M and Cubitron are trademarks of 3M. Please recycle. Printed in USA. © 3M 2016. All rights reserved. 60-4402-7939-0