



Choose your Headlight Kit

DO YOU HAVE A CAR?



Do you live in the 1800s?

No

Do you have headlights?

No

You are on a car website... why are you here?!?

Yes



(awesome)

No



Relax and wax on

Yes

Are they yellow?

Yes

Do say... how yellow are they?



Improve brightness by up to **200%**

Light



Restore your headlights in seconds

Medium



Restore your headlights in minutes

Heavy



Some serious TLC. Easier, faster HD restoration!

ALL IN THE WORLD IS GOOD!



3M Headlight Kits Feature Exclusive Trizact™ technology

Quick & convenient

2 step process for light haziness and yellowing. Hand applied.

Moderate restoration

4 step process for moderate haziness and yellowing. Easier and faster.

Heavy duty restoration

4 step process for heavy haziness and yellowing. Drill use saves time.

Shop owner

Have a shop do the service for you. For heavy haziness and yellowing. Bulk buy for the professional.

