

DUAL-RING CABLE TIE-OFF ADAPTER

**COMPATIBLE.
SECURE.
SAFE.**

**REPLACE
YOUR MATERIAL
HANDLING
SLINGS WITH
A FALL ARREST
RATED ANCHOR.**



TRUSTED, QUALITY FALL PROTECTION



PRODUCT SHEET

DUAL-RING DESIGN

EASILY SLIDE OR REPOSITION WITHOUT DISCONNECTING

Performance, Value and Safety


The Protecta® dual-ring cable tie-off adapter is a lightweight and extremely durable anchor designed to provide an alternative to "choker" style anchors, and is a safe replacement for material handling slings being used for fall protection.

- Reposition without disconnecting or loosening—simply slide
- Portable and reusable design provides added versatility
- Durable ¼" (6.35 mm) galvanized construction for longevity
- Meets the latest OSHA and ANSI standards

The dual-ring design provides a safe, compatible connection that is fall arrest rated for personnel; replacing incompatible "basket" type configurations such as used with some slings, or slings requiring multiple hooks into a single connecting element or connecting combinations of hooks or carabiners together.


NOT RECOMMENDED:

Attaching more than one hook into a single connecting element (ref: OSHA & ANSI)




NOT RECOMMENDED:

Connecting combinations of hooks or carabiners together (ref: OSHA & ANSI)



RECOMMENDED: Protecta® offers a wide variety of safe, secure and compatible anchors including the dual-ring tie-off adapter and various cable and web choker/pass-thru tie-off adapters.



Fall Arrest Rated

For personnel use and peace-of-mind—5,000 lb. (22kN)

Extremely Durable

Galvanized steel construction

Easily Repositioned

Slide anchor—no need to disconnect or loosen

Built-In Saflok™ Carabiner

Self-closing, self-locking one-handed operation

2190100

Dual-Ring Design

Provides safe and compatible tie-off point

Models Available:

2190100—Dual-ring cable tie-off adapter x 3 ft.

2190101—Dual-ring cable tie-off adapter x 4 ft.

2190102—Dual-ring cable tie-off adapter x 6 ft.

NOTE: In Canada, add a "C" to the end of the part number.

Specifications:

Hardware: Zinc-plated forged alloy steel D-rings and carabiner

Wire Rope: ¼" diameter 7x19 galvanized wire rope

Minimum Breaking Strength: 5,000 lbs (22 kN)

Capacity: 310 lbs. (141 kg) (one person)

Standards: Meets ANSI Z359.1 and OSHA requirements

Weight: 1.6 lbs. (0.73 kg) for 3 ft. model



Capital Safety - USA: 800 328 6146

Canada: 800 387 7484 | Latin America: +1 651 385 4301

Asia: +65 65587758 | Germany: +49 (0)30 92 03 83 87 00

New Zealand: 0800 212 505 | Australia: 1800 245 002

Europe, Middle East, Africa: +33 (0)4 97 10 00 10

Northern Europe: +44(0)1527 548000

www.capitalsafety.com | info@capitalsafety.com