



Science.
Applied to Life.™



Protect your body.
Prepare to paint.

3M™ Automotive Aftermarket Division
3M Masking Solutions Products



3M™ Masking Solutions.

Masking tape is used in all types of applications throughout the repair process. 3M offers a range of products to help increase productivity and improve profitability, by reducing repair process times and eliminating rework costs.

3M is one of the world's largest manufacturers of tapes. Through intensive research and development in laboratories throughout the world, we have created a range of new and innovative products that provide fast and effective solutions for every masking situation. From fine line painting and detailing to general protection, 3M masking systems are able to meet all demands.

Aperture masking for smooth blend lines.

3M Soft Edge Masking Foam Tape

An effective solution for time-consuming masking of vehicles prior to painting. The tape is used to mask vehicle apertures such as door, bonnet, boot and filler cap. As well as achieving the required 'soft edge', this tape ensures that the interior of the vehicle is kept free of paint and dust.



3M Soft Edge Masking Foam Tape.

3M Soft Edge Masking Foam Tape PLUS

utilises a tubular design that will deform to expand or compress to fill a range of aperture sizes. This allows painters to easily mask both wide and narrow openings in one simple step, whilst the offset adhesive bead allows the product to be placed away from the paint edge to optimise the soft edge.



3M Soft Edge Masking Foam Tape PLUS.


Accurately masking difficult contours and areas.

3M Trim Masking Tape eliminates visible paint edges and reduces the cost of removing and installing new mouldings and glass. It allows paint coverage under the moulding, saving time and labour on removing paint lines on existing mouldings.




3M Trim Masking Tape.

3M Trim Lifting Cord eases the problems when painting up to a rubber moulding such as around a windscreen. A flexible 6mm diameter foam cord is slid under the moulding using a clever applicator tool. Quick to apply, the cord ensures no edge build-up and no visible evidence of repair work, thus eliminating the need to remove the glass. An applicator tool is supplied free with each box.



3M Trim Lifting Cord.

3M Smooth Transition Tape is a fast and simple way to create smooth transitions whilst painting base and clear coat finishes. Our tape provides a flawless appearance when masking and painting parts such as door apertures, quarter edge panels and swage lines. It can be used in conjunction with 3M Soft Edge Foam Masking Tape PLUS for primer repairs so it is great for SMART repairs.



3M Smooth Transition Tape.

Premium range prevents rework and saves money on time and materials.



3M Purple Premium PLUS Clear Masking Film prevents moisture imprinting and ghosting on painted vehicle surfaces. The film is a premium high density plastic sheeting which withstands temperatures of up to 120°C for an hour. Masking tape can easily be removed and repositioned on the film.




3M Purple Premium PLUS Clear Masking Film.

3M Taped Masking Film is used for localised masking and SMART repairs. Our pre-applied tape makes this film easy to use, and our micro replication technology means that you can tear in clean, straight lines without a blade. It protects against paint spray and prevents paint running off the plastic film.



3M Taped Masking Film.

3M Scotch® High Performance Masking Tape (Blue) 3434 is suitable for a wide variety of applications in auto refinishing. Use in environments up to 110°C and in conditions of high water resistance. Our high performance blue crepe paper masking tape has excellent solvent and water resistance properties.



3M Scotch® Premium Auto Refinish Masking Tape (Green) 3030 gives you clean paint lines and less build-up. Our green-coloured, smooth creped masking tape is a specially formulated cross-linked rubber/resin adhesive and suits a wide variety of bodyshop applications.



3M Scotch® Masking Tape.

Part No.	Item	Dimensions	Configuration	Units per box	Boxes per case
3M™ Soft Edge Foam Masking Tape					
50421	3M Soft Edge Masking Foam Tape PLUS	7 x 21mm x 7m		1	1
09678	3M Soft Edge Masking Foam Tape	10 x 13mm x 5m		1	1
09973		7 x 19mm x 5m			
3M Specialist Masking					
06345	3M Trim Masking Tape	50.8mm x 10m	5mm strips	1	6
06347			7mm strips		
06349			10mm strips		
06348			15mm strips		
06342	Starter Kit		Mixed		1
09529	3M Trim Lifting Cord	6mm x 40m		1	1
06800	3M Smooth Transition Tape	0.25" x 30'		5	12
3M Large Area Masking					
50988	3M Purple Premium PLUS Clear Masking Film	4m x 150m		1	1
50989		5m x 120m			
05967	3M Taped Masking Film	40cm x 25m		1	30
05968		60cm x 25m			24
05969		90cm x 25m			
05970		110cm x 25m			
05971		180cm x 25m			
3M Premium Masking					
07897	3M Scotch® High Performance Masking Tape Blue 3434	24mm x 50m		36	1
07898		36mm x 50m		24	
07899		48mm x 50m		20	
50978	3M Premium Auto Refinish Masking Tape Green 3030	24mm x 50m		36	1
50980		36mm x 50m		24	
50981		48mm x 50m			

For more information visit: www.3M.co.uk/bodyshop



Automotive Aftermarket Division

3M United Kingdom PLC
Tel: 0845 603 9714
aadenquiries@mmm.com
www.3M.co.uk/bodyshop

Automotive Aftermarket Division

3M Ireland
Tel: (00) 353 1 216 0301
Fax: (00) 353 1 280 3509

Please recycle. Printed in the United Kingdom.
© 3M 2016. All rights reserved.
AB093