

## Product Description

3M™ Bathroom Cleaner Concentrate 44A is a concentrated product to be diluted and dispensed using the 3M™ Flow Control System Wall Mount Dispenser or the 3M™ Flow Control System Portable Dispenser.

3M™ Bathroom Cleaner Concentrate 44L is a concentrated product to be diluted and dispensed using only the 3M™ Twist 'n Fill™ Cleaning Chemical Management System. Improper use or dilution may result in altered product performance and may increase the risk of health effects.

Use for daily cleaning of toilet bowls, urinals, and other hard surface areas.

## Special Features

- Automatic dispensing eliminates measuring and mixing and helps ensure accurate dilutions
- Green Seal™ GS-37 Certification
- Pleasant fragrance
- Hard water tolerant
- Cleaner
- Scale remover
- Soap scum remover

## Applications

- Concrete
- Marble
- Terazzo
- Porcelain fixtures
- Stainless steel
- Tile and grout
- Vinyl

## Packaging

3M Bathroom Cleaner Concentrate 44A:

- 0.5 gallon bottle
- 4 bottles per case

Each 0.5-gallon bottle typically yields 25 ready-to-use gallons 1:50 dilution ratio

3M Bathroom Cleaner Concentrate 44L:

- 0.528 gallon bottle
- 6 bottles per case

Each 2 liter bottle typically yields 27 ready-to-use gallons 1:50 dilution ratio

### Quick Links

- [Resource Library](#)
- [Safety Data Sheets \(SDS\)](#)
- [Video Library](#)

Some of these links lead to web-based resources that are not product-specific.

## General Use Directions

Dispense 3M™ Bathroom Cleaner Concentrate 44A with cold water using the 3M™ Flow Control System Dispenser into a properly labeled container.

Apply ready-to-use solution with a cloth, mop, or sponge to thoroughly wet the surface. Wipe dry with a cloth, sponge, mop or allow to air dry.

**Note:** For spray applications, use a coarse spray. Spray 6-8 inches from surface; rub with brush, sponge or cloth. Do not breathe spray.

**Toilet Bowl and Urinal/Cleaner Directions:** Empty toilet bowl or urinal and apply ready-to-use product to exposed surfaces and under the rim with a cloth, mop, sponge or mechanical spray. Brush or swab thoroughly, especially under the rim. For best scale removal, allow to stand for 10 minutes and flush.

## Precautionary Summary

**Personal Protective Equipment (PPE) Recommendation:** Refer to SDS for specific PPE guidance.

**Waste Disposal Method:** Incinerate in an industrial or commercial facility in the presence of a combustible material. As a disposal alternative, dispose of waste product in a facility permitted to accept chemical waste. Rinse empty container with water and recycle.

**Note:** Refer to product Safety Data Sheet for specific physical properties, health hazard, first aid and precautionary information.

- 22-4730-2 (Concentrate)
- 22-4877-1 (RTU)



This product meets the Green Seal™ standard for industrial and institutional cleaners based on its reduced human and environmental toxicity and reduced volatile organic compound content, with skin and eye irritation and acute toxicity met at the as-used dilution.



# 3M™ Bathroom Cleaner Concentrate 44A and 44L

## Health and Safety

When handling any chemical products, read the manufacturers' container labels and the Safety Data Sheets (SDS) for important health, safety and environmental information. To obtain SDS sheets for 3M products go to [3M.com/SDS](http://3M.com/SDS), or by mail or in case of an emergency, call 1-888-364-3577 or 1-651-737-6501.

When using any equipment, always follow the manufacturers' instructions for safe operation.

## Technical Information

Technical information and data, recommendations, and other statements provided by 3M are based on information, tests, or experience which 3M believes to be reliable, but the accuracy or completeness of such information is not guaranteed. Such technical information and data are intended for persons with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. The typical values shown should not be used for the purpose of specification limits. If you have questions about this Product, contact the **Customer Service Department at 1-800-852-9722**.

## Product Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

## Warranty

3M warrants that each 3M product will be free from defects in material and manufacture for 90 days from the date of purchase from 3M's authorized distributor. 3M MAKES NO OTHER EXPRESS OR IMPLIED WARRANTIES, INCLUDING ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.

### Limited Remedy

If a 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

### No Extension of Warranty

In the case of an approved warranty claim, the replacement Product will carry only the remaining term of the original warranty period.

### Limitation of Liability

Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted.

### Commercial Solutions Division

3M Center, Building 220-12E-04  
St. Paul, MN 55144

1-800-328-0033  
[3M.com/Facility](http://3M.com/Facility)

© 3M 2018. All rights reserved.  
3M is a trademark of 3M. Used under license in Canada.  
All other trademarks are property of their respective owners.  
Revision B, April 2018. Please recycle.

