

Increasing Efficiency, Improving Productivity.

3M™ Sealer Range

- ▶ Hybrid polymer technology products allow 'wet-on-wet' paintability for faster throughput.
- ▶ A variety of applicators to suit your individual application.
- ▶ Various finishes to match OEM appearance.
- ▶ Polyurethane seam sealer range approved for 'Direct to Metal' applications.




3M™ Polyurethane and Hybrid Sealer Range

Increasing Efficiency, Improving Productivity



3M™ Multi-Purpose Sealer

- Creates a variety of seam sealing finishes including sprayed, extruded and brushed seams
- Can be used as a stonechip coating to match a variety of finishes found on today's vehicles
- Overpaint almost immediately with water based paint systems*
- Efficient process time and productivity gains
- Isocyanate-free
- This sealer is available in 310ml cartridge




3M™ Polyurethane Sealer Range

- Comprehensive range with a variety of packaging options and colours, including the new colour beige
- Cost effective seam sealing method for all non wet-on-wet applications
- For all interior and exterior seams
- Suitable for primed and painted surfaces as well as direct to metal applications
- Can be used as weld-through sealer (RSTW)
- Overpaint product once the skin is fully formed; usually after 20–45 mins (depending on working conditions)
- This range is available in 310ml cartridge, 310ml sachet and 600ml sachet



3M™ Hybrid Range

- 3M hybrid technology for excellent wet-on-wet processes*
- Offering productivity gains and process efficiency
- White version is available for wet-on-wet, easy to see caulkable seams
- Grey version is available for sprayable application
- Isocyanate-free
- This range is available in 290ml cartridge



* If left for more than 24 hrs, abrade the product lightly with 3M™ Scotch-Brite™ to guarantee paint adhesion.

3M™ Seam Sealer Range

3M™ Multi-Purpose Sealer

Part No.	Description	Colour	Type	Unit/Carton	Size
50740	3M™ Multi-Purpose Seam Sealer	Beige	Cartridge	9	310 ml









3M™ Hybrid Range

Part No.	Description	Colour	Type	Unit/Carton	Size
08851	3M™ Hybrid Seam Sealer Sprayable	Grey	Cartridge	12	290 ml
08855	3M™ Hybrid Seam Sealer Caulkable	White			

3M™ Polyurethane Range

Part No.	Description	Colour	Type	Unit/Carton	Size
08694	3M™ Polyurethane Seam Sealer	Black	Cartridge	12	310 ml
08684	3M™ Polyurethane Seam Sealer	Grey			
08689	3M™ Polyurethane Seam Sealer	White			
08365	3M™ Polyurethane Seam Sealer	Beige			
08789	3M™ Polyurethane Seam Sealer	Black	Sachet	12	310 ml
08782	3M™ Polyurethane Seam Sealer	Grey			
08787	3M™ Polyurethane Seam Sealer	White			
08793	3M™ Polyurethane Seam Sealer	Black	Sachet	12	600 ml
08783	3M™ Polyurethane Seam Sealer	Grey			
08788	3M™ Polyurethane Seam Sealer	White			

3M™ Applicators

	290/310 ml cartridge 	310 ml sachet 	600 ml sachet 
Universal	 08993 pneumatic universal applicator ▶ extrudable applications ▶ sprayable application (cart. only)		
Premium Pneumatic	 08012 extrudable	 08006 extrudable	 08007 extrudable
Basic – Manual	 08013 manual applicator extrudable		

For more information contact your local 3M distributor or visit: www.3M.co.uk/bodyshop

Automotive Aftermarket Division

3M United Kingdom PLC
Tel: 08456039714
aadenquiries.uk@mmm.com
www.3M.co.uk/bodyshop

Automotive Aftermarket Division

3M Ireland
Tel: (01) 280 3555

Please recycle. Printed in UK.
© 3M 2016. 3M is a trademark
of the 3M company All rights
reserved. AB087 // J343472

