

**3M** Science.  
Applied to Life.™



# Delivering a world of comfort to you.

The 3M™ Versaflo™ Powered Air Turbo TR-603E-ASB, combined with the 3M™ Full Face Mask 7900PF can be used in asbestos/abatement environments bringing all the protection, comfort and simplicity you need.

## Easy cleaning and decontamination

- ▶ Smooth shape
- ▶ Suitable for shower decontamination (IP54) & temporary submersion (IP67)
- ▶ Easy clean belt – submersible belt with smooth surfaces allows easy, thorough cleaning

## Comfortable Airflow

- ▶ TR-600 delivers constant 180lpm steady airflow as battery discharges or filter loads with particulates

## Ease of Use

- ▶ Display shows battery charge status and particulate filter loading status during use
- ▶ Charge status is also indicated by a useful LED display on the battery
- ▶ No user calibration of turbo required
- ▶ Electronic audible, visual and vibratory alarm
- ▶ Intelligent fast-charging single station battery charger

## System Protection, Traceability & Security

- ▶ Approved to EN 12942 Class TM3
- ▶ Unique serial numbers applied on the turbo, face mask and battery
- ▶ Maintenance certificate delivered with each starter kit

## Full Face Mask 7900PF

- ▶ Double faceséal for a reliable fit
- ▶ Large polycarbonate lens with wide field of view
- ▶ Quick-release buckles
- ▶ Six-strap harness
- ▶ Soft and pliable silicone



## 3M™ Versaflo™ Powered Air Turbo TR-603E-ASB

(includes airflow indicator TR-972, spark arrestor TR-662 x2)



## 3M™ Versaflo™ P Starter Kit TR-615E-ASB

This Versaflo™ Starter Kit includes the TR-603E-ASB Turbo, P filter, filter cover, spark arrestor (x2), easy clean belt, high capacity battery, single station battery charger kit, BT-50 tight fitting breathing tube, BT cover, airflow indicator, full face mask, BT retainer and cleaning & storage kit.

## 3M™ Versaflo™ A1P Starter Kit TR-618E-ASB

This Versaflo™ Starter Kit includes the TR-603E-ASB Turbo, A1P filter, filter cover, spark arrestor (x2), easy clean belt, high capacity battery, single station battery charger kit, BT-50 tight fitting breathing tube, BT cover, airflow indicator, full face mask, BT retainer and cleaning & storage kit.



## Spares & Accessories

Part No.	Description
TR-6710E	P Filter
TR-6110E	A1P Filter
TR-6700FC	Filter Cover
TR-6100FC	Filter Cover
TR-6600	Pre-filter
TR-662	Spark Arrestor
TR-632	High Capacity Battery
TR-641E	Single Station Battery Charger Kit
TR-644E	4-Station Battery Charger Kit

Part No.	Description
TR-627	Easy Clean Belt
TR-972	Airflow Indicator
TR-653	Cleaning & Storage Kit
TR-651	Filter Latch Assembly
BT-50	Breathing Tube
BT-922	Disposable Breathing Tube Cover
RTN-01	Breathing Tube Retainer
7900PF	Full Face Mask
7893	Six-Strap Harness

Part No.	Description
7927	Lens
7992	Lens Covers
7991	Nose Cup Assembly
7925	Spectacle Kit
7283	Exhalation Valve
7895	Speaking Diaphragm Kit
7883	Neck Strap Assembly
7989	Green Head Harness Buttons
STC-01	Professional Carry Case