

3M™ Auto Glass One-Part Urethanes (Sausage/Flex-packs)

**Now in 600ML.
FLEX PACKS**



- Job size
- Less waste
- Easy-to-use
- Most economical


3M™ Fast Cure Auto Glass Urethane

- Fastest curing 3M one-part urethane
- Carlite by Visteon™ approved
- Officially licensed by NASCAR™
- High Viscosity
- Meets OEM strength requirements
- Meets FMVSS 212 & 216
- Reaches 150 psi (OLS) in 1 hour at 90°F @ 80% RH

3M™ Auto Glass Urethane Windshield Adhesive (Medium/High Viscosities)

- Meets OEM strength requirements
- Meets FMVSS 212 & 216

3M™ Auto Glass One-Part Urethanes



Ordering Information:

Part No.	Size	QTY./CASE
3M™ Fast Cure Auto Glass Windshield Adhesive		
08689	450 ml Flex Pack	12
08566	600 ml/ Flex Pack	12
3M™ Auto Glass Urethane Windshield Adhesive-(Medium)		
08695	450 ml/ Flex Pack	12
08564	600 ml/ Flex Pack	12
3M™ Auto Glass Urethane Windshield Adhesive-(High)		
08698	450 ml/ Flex Pack	12
08565	600 ml/ Flex Pack	12



Automotive Aftermarket Division

3M Center, Building 223-6N-01
St. Paul, MN 55144-1000
www.3M.com/automotive



Recycled Paper
50% - Pre-consumer
10% - Post-consumer