

3M™ Ultra Clear Double Coated Tapes UCT-50 and UCT-30 bring products to light.

When products are backlit or require light transmission, the right adhesive is essential. These ultra-clear, ultra-thin, double-sided tapes are produced on a clean room coater, so your finished design will stay free of dirt, dust and debris. They also offer excellent initial tack, good adhesion and dimensional stability.

- Ultra clear for exceptional appearance
- ▶ 90% light transmission and 1.1% haze
- ▶ 2 mil double-sided tape
- Easy die-cutting and laminating

Your design will look amazing in any light.

Sometimes, it's what you don't see that counts. 3M™ Ultra Clear Double Coated Tapes UCT-50 and UCT-30 feature a polyester film for dimensional stability and improved handling + their high-tack adhesive provides good shear holding power — yet they're so clear, they practically disappear.







Shed more light on medical screen displays. Let drivers see how fast they're going.





Hold touchscreen control panels securely.



Power up elevator button clarity.



Show travelers the way with brighter backlit graphics.

3M™ Ultra Clear Double Coated Tapes UCT-50 and UCT-30

Product Number	Adhesive	Color	Liner	Tape Thickness (without liner)	PET Carrier Thickness	Standard Roll Length	Working Temperature
UCT-30	Acrylic	Clear	PET Liner	1.0 mils (.030mm)	0.16 mils (.004mm)	200 Meters	-10 to 150°C
UCT-50	Acrylic	Clear	PET Liner	2.0 mils (.050mm)	0.48 mils (.012mm)	100 Meters	-10 to 150°C

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.



Industrial Adhesives and Tapes Division 3M Center, Building 225-3S-06 St. Paul, MN 55144

Phone 800-362-3550 Web 3M.com/converter