



PELTOR™



3M™ PELTOR™ CH-5 High Attenuation Headset
**Communication headset with
highest attenuation on the market***

You have two great reasons to protect your hearing – your only two ears. The CH-5 Headset employs the latest technology to help provide protection against hazardous levels of noise including impact sounds. The robust headset is designed to be used in extreme and rough environments with high noise.

3M™ PELTOR™ CH-5 High Attenuation Headset



Hearing protection for communicating with external communication devices.

*As of October 2016

Hearing protection and communication

The 3M™ PELTOR™ CH-5 High Attenuation Headsets offers an SNR value of 37dB and helps provide very good impact sound protection. The CH-5 High Attenuation Headsets offers a newly developed watertight boom microphone with improved noise cancellation as well as compatibility with existing 3M™ PELTOR™ Adapters. Smart construction enables easy and fast maintenance even out in the field.

Attachments

To fit most users needs, the headset is available in both headband and helmet attachment. All in black colour.

Stainless Steel Wire Headband

Wire headband offers comfortable and consistent pressure.

Hearing Protection

Noise attenuating ear cups help provide hearing protection in environments with potentially hazardous noise.

Replaceable cushions and foam liners (hygiene kit)

Microphone

Dynamic watertight boom microphone (IP 68).



Standard Models

Article number	Description	3M ID	SAP ID
MT73H450A-77 GB	Hearing protector, flex, headband	UU008027557	7100099844
MT73H450P3E-77 GB	Hearing protector, flex, helmet attachment	UU008027573	7100099881
MT73H450A GB	Hearing protector, J11, headband	UU008117143	7100106703
MT73H450P3E GB	Hearing protector, J11, helmet attachment	UU008117184	7100106867

Accessories

Article number	Description	3M ID	SAP ID
HY45	Hygiene kit	UU008117135	7100107408
M171/2	Wind protector, 2 pcs	UU008159483	7100112112
HY100A	Clean – Single-Use Protectors	XH001651351	7100064410
HYM1000	Mic tape, 5m	XH001651328	7100064281
MT73/1	Dynamic watertight boom microphone (IP 68)	UU008163634	7100112094

Please contact your 3M dealer for more information about compatible 3M™ PELTOR™ Flex cables and apaters.

Attenuation

MT73H450A-77 GB
SNR=37 dB H=37 dB M=36 dB L=28 dB



MT73H450P3E-77 GB
SNR=36 dB H=35 dB M=35 dB L=28 dB



3M Personal Safety Division

3M Svenska AB, Box 2341
SE-331 02 Värnamo
Sweden
Tel. +46 370 69 42 00
Internet: www.3M.com/PELTOR

Please recycle. Printed in Sweden.

© 3M 2016. All rights reserved.

3M is a trademark of 3M Company, used under license in Canada. PELTOR is a trademark of 3M Svenska AB, used under license in Canada.