



Noise

Noise-induced hearing loss can be prevented.



Examples of Workers Affected

Electricians and plumbers

Metal and iron workers

Carpenters and drywallers

Masons and painters

Laborers

3M Safety Solutions



3M™ E-A-R™ Push-Ins™ Corded Earplugs

► [Part # 318-1001](#)



3M™ PELTOR™ Lite-Com Pro II, Two-Way Radio Headset

► [Part # MT7H7P3E4010-NA-50](#)

Lets construction workers communicate freely without removing their hearing protection.



3M™ E-A-Rfit™ Dual-Ear Validation System

► [Part # 393-1100](#)

Helps determine whether workers' hearing protection provides adequate protection. Measures across seven standard frequencies in under 5 seconds.



3M™ PELTOR™ Cap-Mount Earmuffs X4P3E

► [Part # X4P3E](#)

Hearing protection with all-day comfort.

[Click on part numbers to learn more.](#)