



Polyester Films/Data Page

FOD # 0065

Scotch™ 8038 Performance-Engineered Polyester Film

Product Construction

<u>Product</u>	<u>Facestock</u>
8038	2.0 mil (50 microns) Clear Gloss Polyester

Features

- Top coated for excellent graphic ink anchorage.
- Clear film facestock allows sub-surface graphics printing.
- A variety of laminating adhesives can be applied to the film to provide a wide range of performance characteristics.

Applications

- Identification labels for automotive, electronics and other durable goods.

Recommended Scotch Laminating Adhesives

<u>Product</u>	<u>Caliper</u>	<u>Adhesive Type</u>	<u>Liner</u>
965	2.0 mil	#100	3.2 mil 55# Densified Kraft
992	2.0 mil	#300	3.2 mil 55# Densified Kraft
9442	2.0 mil	#350	3.2 mil 55# Densified Kraft
9445	5.0 mil	#350	3.2 mil 55# Densified Kraft
9447	1.0 mil	#320	3.2 mil 55# Densified Kraft
9457	1.0 mil	#400	3.2 mil 55# Densified Kraft
9458	1.0 mil	#300	3.2 mil 55# Densified Kraft
9462	2.0 mil	#100	3.2 mil 55# Densified Kraft
9522	2.0 mil	#220	3.2 mil 55# Densified Kraft
9525	5.0 mil	#220	3.2 mil 55# Densified Kraft

Processing

- Care should be taken during die-cutting, since adhesive ooze around the finished labels may lead to label blocking. Be sure to thoroughly evaluate the product construction in actual end-use applications to make sure customer requirements are satisfied.

1/28/93

Terms and Conditions of Sale for products sold by 3M Identification and Converter Systems Division can be found in the ICSD Price Book and in other appropriate schedules.

Technical Data: All physical properties, statements, and recommendations are either based on tests we believe to be reliable or our experience, but they are not guaranteed. 3M recommends each user determine the suitability of the products for the intended use.

Warranty and Limited Remedy: THE FOLLOWING WARRANTY IS MADE IN LIEU OF ALL OTHER WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTY OF MERCHANTABILITY, THE IMPLIED WARRANTY OF FITNESS FOR A PARTICULAR PURPOSE AND ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING, A CUSTOM OR USAGE OF TRADE: 3M warrants its product will be free from all defects.

If a product is proved to be defective, then the exclusive remedy 3M's and seller's sole obligation shall be, at 3M's option, to replace the quantity of the product which is proved to be defective or to refund the purchase price.

Limitation of Liability: 3M and seller shall not be liable for direct, indirect, special, incidental or consequential damages based breach of warranty, breach of contract, negligence, strict liability or any other legal theory.

The foregoing Warranty and Limited Remedy and Limitation of Liability may be changed only by a written agreement signed by authorized officers of 3M and seller.

Scotch, ScotchMark, ScotchCap, and Stamark are trademarks of 3M.



Identification and Converter Systems Division

3M Center, Building 220-7W-03
St. Paul, MN 55144-1000
USA
1 800 223 7427
1 800 258 7511 FAX
e-mail idconvert@mmm.com

3M Canada Inc.

PO Box 5757
London, Ontario
Canada N6A 4T1
1 800 265 1840
519 452 6090 FAX

3M Mexico, S.A. de C.V.

Apartado Postal 14-139
Mexico, D.F. 07070
Mexico
52 5 728 2289
52 5 728 2299 FAX

3M Puerto Rico, Inc.

Puerto Rico Industrial Park
PO Box 100
Carolina, PR 00986-0100
809 750 3000
809 750 3035 FAX