

Styleitaliano – excellent aesthetics, made easy!

featuring



With 3M and Styleitaliano it's easy for you to create high-end, natural-looking restorations while saving valuable time. Optimise your outcomes by simplifying your technique.

3M™ Scotchbond™ Bond Universal Adhesive

Versatile. High bond strength. For use on any dental surface, with any etching technique and virtually no post-operative sensitivity.

3M™ Filtek™ Supreme XTE Universal Restorative


Beautiful for anterior restorations, but also strong enough for posterior restorations. Unsurpassed aesthetics, excellent polish retention, and exceptional handling.

3M™ Elipar™ DeepCure-S LED Curing Light

Predictable, reliable cure. Excellent depth of cure even when light positioning is difficult. Optimised light guide is more comfortable for patients.

3M™ Sof-Lex™ Diamond Polishing System

Imparts a gorgeous paste-like gloss with the convenience of a rubberised system. Fast and easy to use. Multi-use, can be sterilised and reused.



Ordering Information



Recommended Recipes

A shade recipes:

- A0 ▶ Dentine W + Enamel A2
- A1 ▶ Dentine A1 + Enamel A3
- A2 ▶ Dentine A2+ Enamel A3
- A3 ▶ Dentine A3+ Enamel A3
- A3.5 ▶ Dentine A4+ Enamel A3
- A4 ▶ Dentine A4+ Body A4

B shade recipes:

- B1 ▶ Dentine A1 + Enamel B2
- B2 ▶ Dentine A2+ Enamel B2
- B3 ▶ Dentine A3+ Enamel B2

Bleach recipes:

- OM2 ▶ Dentine W + Body XW
- OM3 ▶ Dentine W + Body W
- A0 ▶ Dentine W + Enamel A2

3M™ Filtek™ Supreme XTE Universal Restorative

Dentine shade refills

Refill shade	Item # syringe	Item # capsule
A1D	5914A1D	5915A1D
A2D	5914A2D	5915A2D
A3D	5914A3D	5915A3D
A4D	5914A4D	5915A4D
B3D	5914B3D	5915B3D
C4D	5914C4D	5915C4D
White	5914WD	5915WD

Syringe shade refills:

Include 1 – 4g syringe;
Instructions for Use

Capsule shade refills:

Dentine, Enamel and Translucent Shade Refills include 10 – 0.2g capsules; Body Shade Refills include 20 – 0.2g capsules; Instructions for Use

Body shade refills

Refill shade	Item # syringe	Item # capsule
A1B	5914A1B	5915A1B
A2B	5914A2B	5915A2B
A3B	5914A3B	5915A3B
A3.5B	5914A3.5B	5915A3.5B
B1B	5914B1B	5915B1B
B2B	5914B2B	5915B2B
C1B	5914C1B	5915C1B
C2B	5914C2B	5915C2B
A4B	5914A4B	5914A4B
A6B	5914A6B	5915A6B
B3B	5914B3B	5915B3B
B5B	5914B5B	5915B5B
C3B	5914C3B	5915C3B
D2B	5914D2B	5915D2B
D3B	5914D3B	5915D3B
White	5914WB	5915WB
Extra White	5914XWB	5915XWB

Enamel shade refills

Refill shade	Item # syringe	Item # capsule
A1E	5914A1E	5915A1E
A2E	5914A2E	5915A2E
A3E	5914A3E	5915A3E
B1E	5914B1E	5915B1E
B2E	5914B2E	5915B2E
D2E	5914D2E	5915D2E
White	5914WE	5915WE
Extra White	5914XWE	5915XWE

Translucent shade refills

Refill shade	Item # syringe	Item # capsule
Clear	5914CT	5915CT
Blue	5914BT	5915BT
Grey	5914GT	5915GT
Amber	5914AT	5915AT

Average enamel thickness 0.5mm



3M™ Scotchbond™ Bond Universal Adhesive

Item # Product Information

41254	3M™ Scotchbond™ Universal Adhesive Intro Kit: Vial Includes: 1 – 5ml adhesive vial; 50 disposable mixing wells; 50 disposable microbrushes; 1 – 3ml etchant syringe; 25 dispensing tips
41258	3M™ Scotchbond™ Universal Adhesive Refill Includes: 1 – 5ml adhesive vial
41255	3M™ Scotchbond™ Universal Adhesive Intro Kit—Unit Dose 40 Includes: 40 unit dose; 1 – 3ml etchant syringe
41256	3M™ Scotchbond™ Universal Adhesive Unit Dose 100 Includes: 100 unit dose; 1 – 3ml etchant syringe
41264	3M™ Scotchbond™ Universal DCA Dual Cure Activator Includes: 1 – 5ml vial
41263	3M™ Scotchbond™ Universal Etchant Etching Gel Includes: 2 – 3ml syringes; 50 dispensing tips



3M™ Elipar™ DeepCure-S LED Curing Light

Item # Product Information

76978	Elipar™ DeepCure-S LED Curing Light: Contains: Handpiece (Cordless), Charging Base (230V); Li-ion Battery; 10mm Light Guide; Eye Shield
76981	Elipar™ DeepCure-S Light Guide, 10mm
76984	Elipar™ DeepCure Eye Shield
76985	Elipar™ DeepCure-S Rechargeable Li-ion Battery



3M™ Sof-Lex™ Diamond Polishing System

Item # Product Information

5092-IM	Sof-Lex™ Diamond Polishing System – Introductory Kit: Kit includes: 5 Sof-Lex™ Pre-Polishing Spirals (Beige); 5 Sof-Lex™ Diamond Polishing Spirals (Pink); Instructions for Use; Technique Card
5090	Sof-Lex™ Pre-Polishing Spirals – Refill Includes: 15 Sof-Lex™ Pre-Polishing Spirals (Beige)
5091	Sof-Lex™ Diamond Polishing Spirals – Refill Includes: 15 Sof-Lex™ Diamond Polishing Spirals (Pink)



3M Oral Care
3M Australia Pty Ltd
Building A, 1 Rivett Rd
North Ryde NSW 2113
Ph: 1300 363 454
www.3M.com.au

3M New Zealand Limited
94 Apollo Drive
Rosedale, Auckland 0632
Ph: 0800 80 81 82
www.3M.co.nz

www.3M.com.au/Dental
www.3M.co.nz/Dental

3M, 3M Science. Applied to Life, Elipar, Filtek, Scotchbond and Sof-Lex are trademarks of 3M. Claims are supported by 3M internal data on file. Please recycle. © 3M 2017. All rights reserved.