



New! 3M™ Accuspray™ Pressurised
HGP Spray Gun and Pressure Cup!

3M™ Accuspray™ Pressurised HGP Spray Gun Faster, cleaner and efficient.

- ▶ Quick and easy matching of textured coatings
- ▶ Adjustable & versatile spray gun
- ▶ Improved productivity
- ▶ Reduced overspray
- ▶ Pressure cups for highly viscous materials



3M™ Accuspray™ Pressurised HGP Spray Gun.

The Perfect System For The Perfect Results.

The new 3M™ Accuspray™ Pressurised HGP Spray Gun and PPS™ Pressure Cups are designed for high viscosity coatings.

You can now apply virtually any sprayable coating such as underbody protection, high build primers and stonechip.

For applying highly viscous materials:

- ▶ 3M™ Accuspray™ Pressurised HGP Spray Gun
- ▶ Easy cleaning
- ▶ Processing hard to reach places
- ▶ Diverse adjustment and nozzle options
- ▶ Many textures can be reproduced
- ▶ Less material consumption
- ▶ Ideal for use with 3M™ Body Gard™ Coatings



1.4 mm nozzle



1.8 mm nozzle



2.0 mm nozzle

3M™ Body Gard™ Coatings for textured, flat or smooth finishes.

- ▶ Excellent stone chip resistance
- ▶ High solids
- ▶ Coating becomes tack free in 10-25 minutes
- ▶ Fast drying

Using the Accuspray™ Pressurised HGP Spray Gun with 3M™ Body Gard™ Coatings you can quickly and easily achieve most OEM stonechip finishes.



Fast cleaning, fast material change!

Creates like new gun performance



Reduced sanding & cleaning time



Improves transfer efficiency



Reduced overspray



3M™ Accuspray™ System

3M™ Accuspray™ Spray Gun HG14 provides exceptional results though excellent atomisation resulting in higher transfer efficiency and lower overspray.

3M™ Accuspray™ Spray Gun HG14

Saving you time, money and material. Using the 1.4mm, 1.8mm or 2.0mm atomising heads / nozzles to achieve the desired results.

- ▶ 1.4mm nozzles are perfect for wet-on-wet primer applications
- ▶ 1.8mm nozzle is still the first choice for high build primer
- ▶ 2.0mm nozzle for sprayable polyester primer



Colour change in no time!

- 1** Pull the trigger guard and remove the nozzle by the two release latch.
- 2** Clean the needle with a solvent cross linked cloth.
- 3** Simply put on the new nozzle and you're done.



3M™ Accuspray™ System: Everything under control, everything in sight.

Item Image	Product Number	Description	Contents	Quantity per Pack	Shipping Unit
	16577	3M™ Accuspray™ Spray Gun HG14	HG14 Spray Gun with 1.4mm atomising heads	1	1
	16587	3M™ Accuspray™ Model HGP Pressurised Gun Kit	HGP Spray Gun with 1.8mm and 2.0mm atomising heads and air control valve	1	1
	16121	3M™ PPS™ Type H/O Pressure Cups – Mini	Mini 177ml	1	4
	16124	3M™ PPS™ Type H/O Pressure Cups – Large	Large 828ml	1	2
	16114	3M™ PPS™ Mini Lids & Liners	Mini Lids & Liners – 200 micron filter	50	1
	16000	3M™ PPS™ Standard Lids & Liners	Standard Lids & Liners – 200 micron filter	50	1
	16612	3M™ Accuspray™ Atomising Head / Nozzle	Orange – 1.4mm	4	6
	16611	3M™ Accuspray™ Atomising Head / Nozzle	Clear – 1.8mm	4	6
	16609	3M™ Accuspray™ Atomising Head / Nozzle	Red – 2.0mm	4	6
	16236	3M™ Accuspray™ Storage System		1	1

Accuspray™ HGP Pressurised Spray Gun to be used with the 3M™ PPS™ Mini & Standard Lids and Liners.
Accuspray™ HG14 can be used with all 3M™ PPS™ Lid & Liners sizes: Large, Standard, Midi and Mini.

Please visit our website for more information: www.3M.co.uk/BodyShop

Automotive Aftermarket Division

3M United Kingdom plc, 3M Centre
Cain Road, Bracknell, Berkshire RG12 8HT
Tel: 0845 603 9714
Fax: 0800 378127
aadenquiries@mmm.com

3M Automotive Aftermarket Division

3M Ireland Limited
Tel: (00) 353 1 2160301
Fax: (00) 353 1 2803509

Please recycle. Printed in UK.
© 3M 2016. All rights reserved.
3M, PPS and Accuspray are all
trademarks of the 3M Company.
J327338. AB077

