

## for Wall Graphics Eligible for the 3M™ MCS™ Warranty

### Quick Links

[3M Graphics Warranties](#)  
[Technical Information Selector](#)  
[Safety Data Sheets \(SDS\)](#)  
[Videos](#)

Some of these links lead to web-based resources that are not product-specific.

### Overview

The results of the 3M Wall Film Adhesion Tests will help determine which film is most suitable for the job. In some cases, one job may require using more than one film, depending on the adhesion that can be achieved on each different wall. Wall graphics created with [3M™ Print Wrap Film IJ180mC](#) and [3M™ Envision™ Print Wrap Film LX480mC/SV480mC](#) are eligible for the 3M™ MCS™ Warranty.

### Additional Information

- See [3M Instruction Bulletin Clean](#) for full details on preparing painted wallboard for enhanced adhesion of adhesive-backed film
- See [3M Instruction Bulletin 5.37](#) for full details on testing 3M wall film adhesion using the 3M Adhesion Test Kit.
- See [FAQ Wall Application](#) for Frequently Asked Questions related to Smooth, Indoor Wall Applications including what is required to be eligible for the 3M™ MCS™ Warranty and recommended paints for the best adhesion.

## Smooth Wall Application Checklist

Fill-in the information below before applying finished graphics to smooth, indoor walls.

Installation Site Information	
Business Name	
Address	
City/State/Zip	
Customer Information	
Contact Name	
Business Name	
Address	
City/State/Zip	
Phone Number	
Graphics Manufacturer	
Business Name	
Phone Number	
Installer Information	
Name	
Phone Number	
Date of Installation	

### Adhesion Test

This test is designed to show initial adhesion capability measured in grams, of the wall film you plan to use when the wall is cleaned according to 3M's recommendations and the film is applied to a fairly smooth indoor wall surface. An adhesion value of 1000g/15min is required in order for the wall graphic to be eligible for the 3M™ MCS™ Warranty and to ensure proper adhesion.

