

March 6, 2017  
Issue Number: 948

**End of Life Notice: 3M™ Ground Plane Cables, Various Series**

To Our Valued Customers:

3M is obsoleting several series of Ground Plane Cables on .050” (1.27mm) pitch:

<b>3M Part Number</b>	<b>Description</b>	<b>Tech Sheet</b>
3353/xx	3M™ Ground Plane Cable, 3353 Series	TS-0078
3469/xx	3M™ Ground Plane Cable, 3469 Series	TS-0077
3476/xx	3M™ Ground Plane Cable, 3476 Series	TS-0071

Canadian Certified versions (prefixed ‘C’) are also impacted.

3M has made the decision to exit the market for flat ribbon, ground plane cables because of low sales.

**Last Time Buy**

For the parts impacted by this EOL 3M is offering a last time buy. Orders will be accepted until March 26, 2017.

If you have any questions, please contact your 3M representative for this product.

Thank you for your understanding and continued partnership with 3M.

Yours faithfully,

**Lindsay Powell**  
Marketing Manager  
3M Interconnect Products

**End of Life: 3M™ Ground Plane Cables, Various - February 2017**

3M SKU	Description	Tech Sheet
80001216540	80001216540 3353/26-100 =26/CAB/RC/GRPL/28AWG/STR/2 DRN/.050"/100'	TS-0078
80001216557	80001216557 3353/34-100 =34/CAB/RC/GRPL/28AWG/STR/2 DRN/.050"/100'	TS-0078
80001216565	80001216565 3353/40-100 =40/CAB/RC/GRPL/28AWG/STR/2 DRN/.050"/100'	TS-0078
80001216573	80001216573 3353/50-100 =50/CAB/RC/GRPL/28AWG/STR/2 DRN/.050"/100'	TS-0078
80001216581	80001216581 3353/60-100 =60/CAB/RC/GRPL/28AWG/STR/2 DRN/.050"/100'	TS-0078
80001216599	80001216599 3353/64-100 =64/CAB/RC/GRPL/28AWG/STR/2 DRN/.050"/100'	TS-0078
80001216607	80001216607 3469/10-100 =10/CAB/RC/GRPL/28AWG/STR/0 DRN/.050"/100'	TS-0077
80001216615	80001216615 3469/14-100 =14/CAB/RC/GRPL/28AWG/STR/0 DRN/.050"/100'	TS-0077
80001216623	80001216623 3469/15-100 =15/CAB/RC/GRPL/28AWG/STR/0 DRN/.050"/100'	TS-0077
80001216631	80001216631 3469/16-100 =16/CAB/RC/GRPL/28AWG/STR/0 DRN/.050"/100'	TS-0077
80001216649	80001216649 3469/18-100 =18/CAB/RC/GRPL/28AWG/STR/0 DRN/.050"/100'	TS-0077
80001216656	80001216656 3469/20-100 =20/CAB/RC/GRPL/28AWG/STR/0 DRN/.050"/100'	TS-0077
80001216664	80001216664 3469/25-100 =25/CAB/RC/GRPL/28AWG/STR/0 DRN/.050"/100'	TS-0077
80001216672	80001216672 3469/26-100 =26/CAB/RC/GRPL/28AWG/STR/0 DRN/.050"/100'	TS-0077
80001216680	80001216680 3469/34-100 =34/CAB/RC/GRPL/28AWG/STR/0 DRN/.050"/100'	TS-0077
80001216698	80001216698 3469/36-100 =36/CAB/RC/GRPL/28AWG/STR/0 DRN/.050"/100'	TS-0077
80001216706	80001216706 3469/37-100 =37/CAB/RC/GRPL/28AWG/STR/0 DRN/.050"/100'	TS-0077
80001216714	80001216714 3469/40-100 =40/CAB/RC/GRPL/28AWG/STR/0 DRN/.050"/100'	TS-0077
80001216722	80001216722 3469/50-100 =50/CAB/RC/GRPL/28AWG/STR/0 DRN/.050"/100'	TS-0077
80001216730	80001216730 3469/60-100 =60/CAB/RC/GRPL/28AWG/STR/0 DRN/.050"/100'	TS-0077
80001216748	80001216748 3469/64-100 =64/CAB/RC/GRPL/28AWG/STR/0 DRN/.050"/100'	TS-0077
80001216755	80001216755 3476/10-100 =10/CAB/RC/GRPL/28AWG/STR/1 DRN/.050"/100'	TS-0071
80001387333	80001387333 3476/10 =10/CAB/RC/GRPL/28AWG/STR/1 DRN/.050"/300'	TS-0071
80001387341	80001387341 3476/10SF =10/CAB/RC/GRPL/28AWG/STR/1 DRN/.050"/300'SF	TS-0071
80001216763	80001216763 3476/14-100 =14/CAB/RC/GRPL/28AWG/STR/1 DRN/.050"/100'	TS-0071
80001216771	80001216771 3476/15-100 =15/CAB/RC/GRPL/28AWG/STR/1 DRN/.050"/100'	TS-0071
80001216789	80001216789 3476/16-100 =16/CAB/RC/GRPL/28AWG/STR/1 DRN/.050"/100'	TS-0071
80001391160	80001391160 3476/16 =16/CAB/GRPL/28AWG/STR/1 DRN/.050"/300'	TS-0071
80001216797	80001216797 3476/20-100 =20/CAB/RC/GRPL/28AWG/STR/1 DRN/.050"/100'	TS-0071
80001216805	80001216805 3476/20-300 =20/CAB/RC/GRPL/28AWG/STR/1 DRN/.050"/300'	TS-0071
80001216813	80001216813 3476/24-100 =24/CAB/RC/GRPL/28AWG/STR/1 DRN/.050"/100'	TS-0071
80001216821	80001216821 3476/25-100 =25/CAB/RC/GRPL/28AWG/STR/1 DRN/.050"/100'	TS-0071
80001216839	80001216839 3476/26-100 =26/CAB/RC/GRPL/28AWG/STR/1 DRN/.050"/100'	TS-0071
80001216847	80001216847 3476/26-300 =26/CAB/RC/GRPL/28AWG/STR/1 DRN/.050"/300'	TS-0071
80001216854	80001216854 3476/26-100SF =26/CAB/RC/GRPL/28AWG/STR/1 DRN/.050"/100'SF	TS-0071
80001216862	80001216862 3476/26-300SF =26/CAB/RC/GRPL/28AWG/STR/1 DRN/.050"/300'SF	TS-0071
80001216870	80001216870 3476/34-100 =34/CAB/RC/GRPL/28AWG/STR/1 DRN/.050"/100'	TS-0071
80001216888	80001216888 3476/37-100 =37/CAB/RC/GRPL/28AWG/STR/1 DRN/.050"/100'	TS-0071
80001216896	80001216896 3476/37-300 =37/CAB/RC/GRPL/28AWG/STR/1 DRN/.050"/300'	TS-0071
80001216904	80001216904 3476/40-100 =40/CAB/RC/GRPL/28AWG/STR/1 DRN/.050"/100'	TS-0071
80001216912	80001216912 3476/40-100SF =40/CAB/RC/GRPL/28AWG/STR/1 DRN/.050"/100' SF	TS-0071
80001216920	80001216920 3476/50-100 =50/CAB/RC/GRPL/28AWG/STR/1 DRN/.050"/100'	TS-0071
80001216938	80001216938 3476/50-300 =50/CAB/RC/GRPL/28AWG/STR/1 DRN/.050"/300'	TS-0071
80001216946	80001216946 3476/50-100SF =50/CAB/RC/GRPL/28AWG/STR/1 DRN/.050"/100'SF	TS-0071
80001216953	80001216953 3476/60-100 =60/CAB/RC/GRPL/28AWG/STR/1 DRN/.050"/100'	TS-0071
80001216961	80001216961 3476/64-100 =64/CAB/RC/GRPL/28AWG/STR/1 DRN/.050"/100'	TS-0071
80610718795	80610718795 C3469/37-100'=37/CAB/GRPL/28AWG/STR/0 DRN/.050"/CSA/100'	TS-0077
80001216979	80001216979 C3476/10-100 =10/CAB/RC/GRPL/28AWG/STR/1 DRN/.050"/CSA/100'	TS-0071
80001388372	80001388372 C3476/34=34/CAB/GRPL/28AWG/STR/1 DRN/.050"/CSA/300'	TS-0071
80001388414	80001388414 C3476/34=34/CAB/GRPL/28AWG/STR/1 DRN/.050"/CSA/100'	TS-0071
80001216987	80001216987 C3476/40-100 =40/CAB/RC/GRPL/28AWG/STR/1 DRN/.050"/CSA/100'	TS-0071
80001216995	80001216995 C3476/40-300SF =40/CAB/RC/GRPL/28AWG/STR/1DRN/.050"/CSA/300'SF	TS-0071
80610601439	80610601439 C3476/50= 50/CAB/GRPL/28AWG/STR/1 DRN/.050"/CSA/100'	TS-0071