



3M™ Specialty Tape Solutions

3M™ Aluminum Foil Tape 425

3M™ Aluminum Foil Tape 425 is the go-to foil tape for numerous applications across a broad range of industries. Comprised of a dead soft aluminum foil backing and coated with a highly engineered pressure sensitive acrylic adhesive, it is ideal for heat shielding, heat reflecting, chemical masking, light enhancement, chemical milling, seaming, sealing and de-paint operations.

Key Characteristics

- High thermal conductivity enhances heating or cooling efficiency
- High heat reflectivity and flame resistance protects temperature-sensitive materials against heat and flame damage and hot spots
- Reflect light
- Seal and protect against moisture, solvents and dust
- Resist outdoor weathering and UV degradation for long term performance

Use For

- Heat shielding of delicate parts
- Aircraft chemical paint strip masking
- Refrigerator and freezer copper coil attachment
- Reflective layer for lighting
- Sealing out air and moisture



Technical Parameters

Adhesive	Acrylic
Backing	Aluminum Foil
Backing Thickness	2.8 mils (0.07mm)
Total Thickness	4.6 mils (0.12mm)
Temperature Use Range	-65°F to 300°F (-54°C to 149°C)

Specialty Six

Bringing better ideas to the surface with a wide variety of tape solutions.

3M™ Specialty Tape Solutions meeting application challenges for appliances, aerospace, automotive, construction, MRO, electronics, commercial transport, marine and more.

	3M™ Aluminum Foil Tape 425		3M™ Polyester Tape 850
	3M™ Vinyl Tape 471		3M™ PTFE Film Tape 5490
	3M™ Glass Cloth Tape 361		3M™ UHMW-PE Tape 5423

For more information, call 1-800-362-3550 or visit 3M.com/IATD



3M Industrial Adhesives and Tapes Division
3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
Phone 800-362-3550
Fax 877-369-2923
Web 3M.com/IATD

Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application. **Warranty, Limited Remedy and Disclaimer:** Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. **Limitation of Liability:** Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

3M is a trademark of 3M. © 3M 2017. All rights reserved. Please recycle. Printed in USA. 70-0716-9834-7 3/2017