



3M Science.
Applied to Life.™

Get comfortable with choices.

**Protective eyewear that self-adjusts to individual
wearer, helping to provide comfort all day.**

When it comes to protective eyewear, comfort matters. That's what sets the 3M™ SecureFit™ Protective Eyewear product family apart. The proprietary 3M™ Pressure Diffusion Temple Technology helps provide a secure, snug fit, while not compromising comfort. Factor in durable lightweight design, lens colors, coating options and other comfort features, and you'll see protective eyewear in a whole new light.

3M™ SecureFit™ Protective Eyewear 600 Series

The quality, durability and versatility of the 3M™ SecureFit™ Protective Eyewear 600 Series bring higher performance to workplace needs, with a variety of features that include lens coating options such as 3M™ Scotchgard™ Anti-fog Coating, multiple lens colors, readers and polarized lens options.

Secure, comfortable fit with 3M™ Pressure Diffusion Temple (PDT) Technology

Durable polycarbonate lenses absorb 99.9% of UVA and UVB rays and meet the requirements of ANSI Z87.1-2015 Standard as an Impact Rated spectacle

Rugged anti-scratch (RAS) coating helps extend the life of the lens

Optional removable foam-lined gasket helps keep debris out of your eyes while providing comfort and cushioning

Long-lasting clarity Scotchgard™ Anti-fog Coating retains its effectiveness for at least 25 washings with water*

Stylish yet sturdy frame that nearly anyone can wear

Multiple lens color options including photochromic and polarized lenses

Optional readers with 3M™ Scotchgard™ Anti-fog Coating and a range of diopters

+1.5
+2.0
+2.5

Lens
Anti-fog Coating

* Based on 3M internal testing per EN168 test method when compared with traditional anti-fog coatings.

Other lens color and shade options



The science behind Scotchgard™ Anti-fog Technology.

Uncoated

In hot and humid environments, tiny droplets form on the lens and scatter incoming light, making it more difficult for you to see clearly.

LENS

Scotchgard™ coated

Scotchgard™ Anti-fog Lens Coating causes these droplets to flatten out and form a thin film, reducing the scattering of light.

LENS ANTI-FOG COATING

SCOTCHGARD™ 3M

3M™ SecureFit™ Protective Eyewear 400 Series

Greater comfort is achieved through advancements in science. The 400 Series features 3M™ Pressure Diffusion Temple Technology, soft one-piece nose bridge, dual-injected temples and optional foam-lined gasket.

Benefits and Features



Dual-injected, padded temple touchpoints for added comfort over the ears

Motion-inspired, contoured piping in a bold, modern color palette for an infusion of style

Polycarbonate lenses absorb 99.9% of UVA and UVB rays and meet the requirements of ANSI Z87.1-2015 Standard as an Impact Rated spectacle

Optional readers with a range of diopters 1.5+, 2.0+, 2.5+

Secure, comfortable fit with 3M™ Pressure Diffusion Temple (PDT) Technology

Optional removable foam-lined gasket helps keep debris out of your eyes while providing comfort and cushioning

Soft one-piece nose bridge

Other lens color options

- Clear
- Grey
- Indoor/Outdoor Mirror Lens

3M™ SecureFit™ Protective Eyewear 200 Series

The right fit changes everything. Temples automatically self-adjust to help provide a secure, comfortable fit each time.

Benefits and Features



Contemporary and lightweight, weighs less than 1 ounce

Polycarbonate lenses absorb 99.9% of UVA and UVB rays and meet the requirements of ANSI Z87.1-2015 Standard as an Impact Rated spectacle

Anti-fog or anti-scratch lens coating

Molded nose bridge

Secure, comfortable fit with 3M™ Pressure Diffusion Temple (PDT) Technology

Other lens color options

- Clear
- Grey
- Amber

3M™ SecureFit™ Protective Eyewear 400 Series

PRODUCT NO.	3M ID NO.	LENS	COATING	DESCRIPTION	UPC NO.
SF401AF	70-0716-5095-9	 Clear	Anti-fog	Anti-fog coating helps keep lenses free of moisture in hot and humid conditions.	100-78371-66211-7
SF402AF	70-0716-5096-7	 Grey		Grey lenses perform best in outdoor daytime work environments, similar to lenses worn in non-work settings.	100-78371-66212-4
SF410AS	70-0716-5097-5	 Indoor/ Outdoor Mirror	Anti-scratch	Indoor/Outdoor Mirror lenses help reduce brightness and glare when working both indoors and outdoors.	100-78371-66213-1
SF401AF-FM	70-0716-7533-7	 Clear	Anti-fog	Removable foam-lined gasket helps keep debris out of your workers eyes while providing comfort and cushioning.	500-51131-27475-9
SF402AF-FM	70-0716-7660-8	 Grey		Anti-scratch coating helps protect lenses from scratches, nicks and scrapes that can become distractions.	500-51131-27565-7
SF410AS-FM	70-0716-7638-4	 Indoor/ Outdoor Mirror	Anti-scratch		500-51131-27545-9
SF-FOAM	70-0716-7534-5	 Replacement Foam Gasket	-		500-51131-27476-6
SF415AF	70-0716-5578-4	 Clear Reader +1.5	Anti-fog	Designed for workers who have difficulty reading small print or are engaged in detail work, magnifying +1.5, +2.0, +2.5 diopters combining eye protection with reading enhancement.	100-78371-66512-5
SF420AF	70-0716-5579-2	 Clear Reader +2.0			100-78371-66513-2
SF425AF	70-0716-5580-0	 Clear Reader +2.5			Grey lenses reduce brightness and glare from the sun and are mainly for outdoor daytime use.

3M™ SecureFit™ Protective Eyewear 200 Series

PRODUCT NO.	3M ID NO.	LENS	COATING	DESCRIPTION	UPC NO.
SF201AF	70-0716-4765-8	 Clear	Anti-fog	Anti-fog coating helps keep lenses free of moisture in hot and humid conditions.	100-78371-65717-5
SF202AF	70-0716-4766-6	 Grey		Grey lenses perform best in outdoor daytime work environments, similar to lenses worn in non-work settings.	100-78371-65718-2
SF203AF	70-0716-4767-4	 Amber		Amber lenses reduce interference from blue light to improve contrast and provide excellent UV protection. Popular for inspection tasks, and hazy, overcast or foggy days. Never use for night driving.	100-78371-65719-9
SF201AS	70-0716-4768-2	 Clear	Anti-scratch	Anti-scratch coating helps protect lenses from scratches, nicks and scrapes that can become distractions.	100-78371-65720-5
SF202AS	70-0716-4769-0	 Grey			100-78371-65721-2
SF203AS	70-0716-4770-8	 Amber			100-78371-65722-9

Early release
of 3 key SecureFit 600
products in February
2017. All will be
available May 2017.

3M™ SecureFit™ Protective Eyewear 600 Series

PRODUCT NO.	3M ID NO.	LENS	COATING	DESCRIPTION	UPC NO.	
 SF601SGAF	70071696069	 Clear	Scotchgard™ Anti-fog	Anti-fog coating helps workers see clearer, longer.	50051131273370	
 SF601SGAF-FM	70071696093	 Clear with Foam Gasket		Removable foam-lined gasket helps keep debris out of your workers eyes while providing comfort and cushioning.	50051131273400	
 SF602SGAF	70071696077	 Grey		Similar to typical sunglasses, grey lenses are popular in outdoor daytime work environments.	50051131273387	
SF602SGAF-FM	70071696101	 Grey with Foam Gasket		Removable foam-lined gasket helps keep debris out of your workers eyes while providing comfort and cushioning.	50051131273417	
SF603SGAF	70071696085	 Amber		Amber lenses reduce interference from blue light to improve contrast and provide excellent UV protection. Popular for inspection tasks, and hazy, overcast or foggy days. Never use for night driving.	50051131273394	
SF607SGAF	70071696119	 Indoor/ Outdoor Grey		Indoor/Outdoor Grey lenses help reduce brightness and glare when working both indoors and outdoors.	50051131273424	
SF615SGAF	70071696168			Clear Reader +1.5	Designed for workers who have difficulty reading small print or are engaged in detail work, magnifying +1.5, +2.0, +2.5 diopters and combining eye protection with reading enhancement.	50051131273479
SF620SGAF	70071696176			Clear Reader +2.0		50051131273486
SF625SGAF	70071696184			Clear Reader +2.5		50051131273493
SF615GSGAF	70071696192			Grey Reader +1.5	Grey lenses reduce brightness and glare from the sun and are mainly used for outdoor daytime applications.	50051131273509
SF620GSGAF	70071696200			Grey Reader +2.0		50051131273516
SF625GSGAF	70071696218			Grey Reader +2.5		50051131273523
SF601RAS	70071676897	 Clear		Rugged anti-scratch	Rugged anti-scratch coating helps extend the life of the lens.	50051131273356
SF602RAS	70071696051	 Grey	50051131273363			
SF617AS	70071696135	 Low IR	Anti-scratch	Provides good visual sight and acuity while absorbing UV and some IR. Popular for wearing with welding helmet.*	50051131273448	
SF630AS	70071696143	 Shade 3.0		Predominantly used with other PPE for cutting, brazing and soldering, metal making, furnace work, and open flame applications.*	50051131273455	
SF650AS	70071696150	 Shade 5.0		50051131273462		
SF611AS	70071696226	 Polarized	Polarized lenses reduce reflective glare; commonly used in outdoor applications.	50051131273530		
SF613AS	70071696234	 Photochromic	Lens darkens when exposed to UV light outdoors, and lightens when removed from UV exposure indoors.	50051131273547		
SF600FI	70071696242	 Replacement Foam Gasket	Replacement Foam Gasket	50051131273554		

* Additional personal protective equipment may be required.

3M™ SecureFit™ eyewear. Protection with options.

Choose features and lens options that best suit your workers and workplace needs. Options include a range of lens colors, readers, 3M™ Scotchgard™ Anti-fog Coating, anti-scratch coatings and more. All SecureFit protective eyewear features the proprietary self-adjusting 3M™ Pressure Diffusion Temple Technology that helps provide a secure, snug fit, while not compromising comfort.



Features	SecureFit™ 200	SecureFit™ 400	SecureFit™ 600
3M™ Pressure Diffusion Temple (PDT) Technology	●	●	●
3M™ Scotchgard™ Anti-fog Coating			●
RAS Coating			●
Anti-scratch/Anti-fog Coating*	●	●	●
Reader Option (+1.5, +2.0, +2.5)		●	●
Dual lens design			●
Clear, Amber, Grey tints	●	●	●
I/O Grey		●	●
Photochromic			●
IR-Tints – LOW IR, Shade 3.0, Shade 5.0			●
Polarized			●
Optional foam-lined gasket		●	●
Robust frame			●
Soft temple tips		●	
Soft nose bridge		●	●
Lightweight, less than 1 oz.	●	●	●

*Traditional anti-fog coatings provide both increased anti-scratch as well as anti-fog protection over uncoated polycarbonate lenses.



3M™ SecureFit™ 200



3M™ SecureFit™ 400



3M™ SecureFit™ 600

⚠ WARNING

These eye and face protection products help provide limited eye and face protection. **Misuse or failure to follow warnings and User Instructions may result in serious potential injury, including blindness or death.** For proper use, selection and applications against flying particles, optical radiation and/or splash, see supervisor, read *User Instructions* and warnings on the package or call 3M PSD Technical Service in the USA at 800-243-4630. In Canada, call Technical Service at 800-267-4114.



Personal Safety Division
3M Center, Building 235-2W-70
St. Paul, MN 55144-1000

For more information
Technical Service: 1-800-243-4630
Customer Service: 1-800-328-1667
3M.com/workersafety
3M.com/securefit

© 3M 2017. All rights reserved.
3M, SecureFit and Scotchgard are trademarks of 3M Company.
3M PSD products are occupational use only.
70-0716-2621-5