

3M™ PELTOR™ ProTac™ III Headset

Hearing protection and situational awareness

Sudden loud or sharp noises are attenuated instantly to help protect workers hearing from potentially harmful noise levels. The ProTac™ III Headset utilizes sound limiting environmental microphones to monitor the surrounding environment, and when hazardous noises are present, the electronic circuit in the headset limits the speaker volume to 82 dB. Use as a traditional hearing protector, or increase the ambient sound level to one of five volume steps to minimize over-protection and improve your ability to hear warning signals, alarms and other sounds in machines and processes.



Part Number	3M Material Number	Description	Qty
MT13H221A	7100088424	ProTac™ III Headset, black, headband (NRR 26 dB, CSA class A)	1 EA
MT13H221P3E	7100088423	ProTac™ III Headset, black, hard hat attached (NRR 23 dB, CSA class B)	1 EA
<i>Accessories</i>			
HY220	7100101874	Hygiene Kit	1 EA
FL8CE/1	7000108359	3.5 mm audio cable	1 EA
HY100A	7100084410	Clean hygiene pads (100 Pair per Carton)	1 CAR



Hearing protection with level-dependent function for environmental listening (limited to 82 dBA)



Hearing protection with external audio input (limited to 82 dBA)

also available in hard hat attached configuration



You know that wearing hearing protection in noisy environments is important for worker safety. But equally important is the ability to hear alarms, vehicles and effectively communicate with other workers. The 3M™ PELTOR™ ProTac™ III Headset utilizes level-dependent technology to block out potentially harmful noise when needed and still listen normally when not. Designed by 3M PELTOR for rugged work environments, the ProTac™ III Headset combines professional-grade durability with lightweight comfort for all-day wearability.