

**3M** Science.  
Applied to Life.™



## Airflow selection – delivering a world of comfort to you.

The new 3M™ Versaflo™ Powered Air Respirator System TR-600 provides protection against particles, gases or vapours, or against a combination of these depending on the type of filter used. The turbo has selectable multiple airflows through a simple, intuitive, easy to use two-button operation and the particulate filter and battery status indicators provide constant updates during use. The modern, low profile design keeps weight close to the back resulting in greater comfort.

# Introducing the new 3M™ Versaflo™ Powered Air Turbo TR-600

## Comfortable airflow

- Three user selectable flow rates to maximise comfort
- Controlled airflow delivers steady flow as battery discharges or filter loads with particulates

## Ease of use

- TR-600 display shows battery charge status and particulate filter loading status during use
- Charge status is also indicated by a useful LED display on the battery
- No user calibration of turbo required
- Electronic audible, visual and vibratory alarm in case of low battery and/or low air flow

## Multiple applications

- Easy clean belt – submersible belt with smooth surfaces allows easy, thorough cleaning
- High durability belt option for hot work or rugged environments provides greater durability and spark/flame resistance
- Suitable for shower decontamination and temporary submersion to aid cleaning

## Safety

- Approved to EN 12941 Class TH2 or TH3 dependent on headtop



## Typical industries and applications

- Pharmaceutical manufacturing
- Painting
- Chemical processing
- Agriculture
- Demolition
- Pulp and paper processing
- Medical & healthcare
- Foundries

### Versaflo Powered Air Turbo TR-602E

This turbo can be easily adapted to your type of environment – see options below. Includes Air Flow Indicator TR-971 and Spark Arrestor TR-662 (x2).



### Versaflo Powered Air Turbo Starter Kit TR-619E

This Versaflo™ Starter Kit includes the TR-602E Turbo, A2P filter, filter cover, prefilters (x10), spark arrestor (x2), easy clean belt, high capacity battery, single station battery charger kit, BT-30 length adjusting breathing tube and airflow indicator.



## Filters

Filters	Filter Covers
TR-6710E P	TR-6700FC
TR-6820E P + Nuisance Odour* Organic Vapour Filter and Acid Gas (Hydrogen Fluoride up to 10 x Workplace Exposure Limit)	TR-6800FC
TR-6110E A1P	TR-6100FC
TR-6130E ABE1P	TR-6300FC
TR-6310E A2P	TR-6300FC
TR-6580E ABE2K1HgP	TR-6500FC

\* "Nuisance Odour" refers to concentrations below the Workplace Exposure Limit

## Batteries

- TR-630 Standard Battery
- TR-632 High Capacity Battery

## Belts

- TR-626 High Durability Belt
- TR-627 Easy-Clean Belt

## Spares and Accessories

TR-6600 Pre-filter	TR-971 Air Flow Indicator
TR-662 Spark Arrestor	BPK-01 Backpack
TR-653 Cleaning & Storage Kit	TR-655 Backpack Adapter
TR-651 Filter Latch Assembly	TR-329 Braces

## Chargers

- TR-641E Single Station Battery Charger Kit
- TR-644E 4-Station Battery Charger Kit

Note: 3M does not accept responsibility or liability, direct or consequential, arising from reliance upon any information provided and the user should determine the suitability of the products for their intended use. Nothing in this statement will be deemed to exclude or restrict 3M's liability for death or personal injury arising from its negligence or fraudulent misrepresentation.



3M Personal Safety Division  
3M United Kingdom plc  
3M Centre, Cain Road  
Bracknell, Berkshire RG12 8HT  
Tel: 0870 60 800 60  
www.3M.co.uk/safety

3M Ireland Limited  
The Iveagh Building  
The Park, Carrickmines  
Dublin 18  
Tel: 1 800 320 500

Please recycle. Printed in the UK. © 2016 3M. 3M and Versaflo are trademarks of the 3M company. All rights reserved. 70-0716-7111-2. J336370