

**3M**

**Scotchlite™**  
Reflective Material



**Compromise  
nothing.**

**CARBON  
BLACK  
STRETCH**  
TRANSFER FILM  
— C/790 —



**Scotchlite™**  
Reflective Material

# CARBON BLACK STRETCH TRANSFER FILM

— C/790 —



**Carbon Black**

## Freedom of movement and design.

Introducing C790 Carbon Black Stretch Transfer Film from 3M™ Scotchlite™ Reflective Material. The deepest black and highest stretch reflective material we've ever made, with the brightness you've come to expect from Scotchlite reflective materials. Patented\* C790 using Carbon Black Technology, combines all the features that active pursuits and dynamic lifestyles demand. Blend in. Stand out. Stretch deep. Do it all. Compromise nothing.



**Reflective**



**Stretch**



**Brightness**



**Stain Resistance**



**Off-Angle Brightness**



**Wash Durability**



**LowTemp Bond**



**Patented**

Learn more at: [3M.com/CarbonBlackReflective](http://3M.com/CarbonBlackReflective)



Personal Safety Division  
3M Center, Building 235-2W-70  
St. Paul, MN 55144-1000  
800-328-7098  
Scotchlite.com

3M Canada  
P.O. Box 5757  
London, Ontario N6A 4T1  
800-267-4414 Technical Service  
800-364-3577 3M HELPS  
3M.ca/Scotchlite

\*Patent: 3m.com/patents  
© 3M 2017. All rights reserved.  
3M and Scotchlite are trademarks of  
3M Company, used under license  
in Canada.  
Please recycle. Printed in U.S.A.