Science.
Applied to Life.™ Fire-rating

critical circuitry

Fire Alarm - Fire Pump **Backup Generators Radio Communications ARCS/DAS** 



## 3M™ Interam™ **Endothermic Mat E-5A-4**

- Helps meet NFPA 72, which mandates all new buildings provide radio coverage for first responders
- Helps you meet the building code requirement to protect emergency electrical circuitry for fire pumps

Local building codes typically require distributed antenna systems and fire pumps within a building to be protected for 2 hours.

This ensures that all of these systems will maintain their integrity in the event of a fire.

3M™ Interam™ Endothermic Mat E-5A-4 (3M E-Mat) is a proven, trusted solution for meeting the IBC, NFPA and NEC codes.

These codes protect electrical systems that supply power for distributed antenna systems, fire pumps and other critical electrically powered assets.

3M E-Mat serves as a flexible alternative to gypsum shafts or concrete encasement. This low-profile material saves space and helps overcome design challenges created by other mechanical systems installed within close proximity.

Protect with the best. Call your 3M Fire Protection rep for an onsite demo!

A Distributed Antenna System (DAS) or Auxiliary Radio Communication System (ARCS) is a building communication system designed to provide adequate radio coverage for emergency personnel. The **National Fire Protection Association passed an** ordinance in 2007—revised in 2010 and again in 2013 (NFPA 72)—mandating that all new buildings are required to provide radio coverage for first responders.





Protect critical electrical circuitry that supplies power to communication systems, fire pumps and other critical assets that must remain operable during a fire. Utilize 3M™ Interam™ Endothermic Mat E-5A-4 ... the trusted name in firestopping. Proven for over 30 years.

- E-Mat is a flexible mat that uses endothermic technology, which, when exposed to high temperatures, releases chemically bound water to cool surrounding materials and slow heat transfer to help protect critical components from fire
- It's the most-installed product for the protection of electrical raceways in United States nuclear power plants per the United States Nuclear Regulatory Commission NUREG-1924
- Tested and listed to ASTM E 119 Cellulosic Fire, UL 1709 Hydrocarbon Pool Fire, ISO 22899 Jet Fire and NFPA 58, Annex H/NFPA 290 Torch Test and UL 1489 for fuel oil pipe
- Tested and listed to ASTM E 662, ASTM E 162, BSS 7239, EN ISO 11925, EN 13501-1 and UL 723/ASTM E 84
- Has Factory Mutual (FM), Lloyd's of London and DNV listings

- Passes UL environmental aging and exposure for humidity, salt spray, wet-freeze-dry, acid spray and solvent spray
- Tested for blast, radiation, seismic, acoustic and chemical analysis

## **Performance & Physical Properties**

Color	Silver exterior, white interior				
Mat Lamination	3 mil. aluminum/scrim				
Mat Thickness	0.408 in. (10.3 mm)				
Roll Dimensions	24.5 in. x 20 ft. (622 mm x 6.09 m)				
Roll Weight	76.6 lbs. (33.8 kg)				
Weight/Unit Area	1.83 lbs./ft.² (8.93 kg/m²)	s. (33.8 kg) s./ft.² (8.93 kg/m²) /ft.³ (865 kg/m³)			
Bulk Density	54 lbs./ft.3 (865 kg/m3)				
Mat Area/Roll	40.8 ft.² (3.79 m²)	THE REAL PROPERTY.			
Surface Burning (ASTME 84)	Flame Spread 0.7 Smoke Development 0 Fuel Combustion 0				

Product Number	Description		Unit	Size	Billing UPC Number	Qty.
3M™ Interam™ Endothermic	Mat E-5A-4 (Aluminum Scrim)					
E-5A-4  ELECTRICAL ORGANIS  STREE BARRIER  FIRE PLANCISCO  FOR PLA	Protective wrap for cable trays, conduits and more		Roll	24.5 in. x 20 ft. (.408in. thick)	000-51115-16571-9	1/Cs
3M™ Aluminum Foil Tape 425	5					
425	Seals cut edges of 3M™ Interam™ Endothermic Mat		Roll	4 in. x 60 yd. (4.6mm thick)	000-51125-85313-2	2/Cs
Scotch® Filament Tape 898						
898	For use with 3M™ Interam™ Endothermic Mats to temporarily hold mat pieces in place during installation		Roll	18 mm x 55 m 24 mm x 55 m	000-51131-06897-1 000-51131-06898-8	48/Cs 36/Cs
3M™ Fire Barrier Sealant CP	25WB+					
CP 25WB+	Up to 4-hr penetration firestop	Color	Tube	10.1 oz.	000-51115-11638-4	12/Cs
SMOKE SEAL BASHER BLASHER BE BARBER BARBER BE BARBER BARBER BE BARBER BE BARBER BE BARBER BE BARBER	Up to 4-hr penetration firestop	Color	Sausage	20 oz.	000-51115-11642-1	10/Cs
	Up to 4-hr penetration firestop	Color	Cartridge	27 oz.	000-51115-11641-4	6/Cs
3M™ VentureClad™ Insulatio	on Jacketing Tape 1577CW-E Em	bossed I	Natural Aluminum	(Optional)		
1577CW-E	For use as a vapor barrier cladding over 3M™ Interam™ E-5A-4 Endothermic Mat		Roll	4 in. x 50 yd. (100 mm x 50 m)	000-76308-98278-2	4/Cs

## Important Notice to User:

Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application. Warranty and Limited Remedy: 3M warrants that each 3M Fire Protection Product will be free from defects in material and manufacture for 90 days from the date of purchase from 3M's authorized distributor. 3M MAKES NO OTHER EXPRESS OR IMPLIED WARRANTIES, INCLUDING ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If a 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted.

**Technical Information:** The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

For technical information, listed systems, training information and more, call 1-800-328-1687 or visit www.3M.com/Firestop

3M Industrial Adhesives and Tapes Division 3M Center, Building 225-3S-06 St. Paul, MN 55144-1000 1-800-328-1687 www.3M.com/Firestop

3M and Interam are trademarks of 3M Company. Used under license in Canada. © 3M 2017. All rights reserved. UL is a registered trademark of Underwriters Laboratories, Inc. 78-9236-7298-0