

Reflective perfected.

3M[™]Scotchlite[™] Print Wrap Film 780mC-10R

Introducing a new way to stand out, shine bright and look great. Thanks to robust retroreflective technology, this print wrap film commands attention at wide angles for faster and better visibility. This reflective film provides a dramatic appearance—any way you look at it.

Boost your visibility at 3M.com/ReflectiveFilm.



Shows by day. Glows by night.

A bright idea for so many applications

- ► Vehicle wraps
- ► Textured walls
- ► Movable assets
- ▶ Motorcycles
- ► Roadside assets
- ▶ Parking structures

- Highly conformable and repositionable for efficient installs
- Heat recovery properties reduce or eliminate bruising using heat
- Wide retroreflective viewing angles for enhanced visibility and safety
- Removes cleanly and easily, unlike most ordinary reflective films





▲ Excellent reflectivity makes graphics stand out 24 hours a day.



Commercial Solutions 3M Center, Building 220-12E-04 St. Paul, MN 55144 USA

Phone 1-800-328-3908 Web 3M.com/Graphics Warranty and Limited Liability. The following is made in lieu of all other express or implied warranties, including any implied warranty of merchantability or fitness for a particular purpose. All 3M products are warranted to be free of defects in materials and manufacture at the time of shipment and to meet the specifications stated in the film or media's Product Bulletin. Also see 3M Graphics Warranties Bulletin, which gives the terms, additional limitations of the warranty, if any, and limitations of liability.

For warranty information, visit 3M.com/GraphicsWarranties.

© 3M 2017. All rights reserved. 3M and Scotchlite are trademarks of 3M. Used under license in Canada. Printed in USA. Please recycle. APR 2017. HB12214

