

3M Science.
Applied to Life.™



**Anti-Fog technology.
Applied to help workers
see clearly, longer.**

WATCH NOW



Scotchgard™ Anti-Fog Coating Technology brings higher performance to safety eyewear.



Clearly better anti-fog performance.

A fogged lens can be frustrating and dangerous. Removing eyewear to wipe away fog can expose eyes to potentially dangerous impact hazards and debris. The Scotchgard™ Anti-Fog Coating resists fogging longer than traditional anti-fog coatings, even after washing multiple times.

Help workers see clearly, longer.

Scotchgard™ Anti-Fog Coating is designed for working in challenging situations such as:

- Hot & humid conditions
- Indoor & outdoor work
- Physically demanding tasks
- Climate controlled areas

See what you've been missing with our fog resistant eyewear.

Try the Solus™ 1000 Series safety eyewear and Goggle Gear 500 Series splash goggle with Scotchgard™ Anti-Fog Coating and see clearly, longer.*


Scotchgard™ Anti-Fog Coating is now available on Solus™ 1000 Series safety eyewear in a range of lens colors (clear or grey). Other features include removable temple arms, soft nose bridge, optional elastic strap, padded temple arms for added comfort, and vented, removable foam gasket to help reduce eye exposure.

Scotchgard™ Anti-Fog Coating is also available on 3M™ Goggle Gear 500 Series splash goggle with a low-profile design and adjustable strap. All come with polycarbonate lenses, which absorb 99.9% of UV rays.

* Based on 3M internal testing per EN168 test method when compared with traditional anti-fog coatings.



The science behind Scotchgard™ Anti-Fog Technology.



The facts are clear:



- Scotchgard™ Anti-Fog Coating **lasts longer** than traditional anti-fog coatings,* helping to increase eyewear performance in wet and steamy environments
- Workers may enjoy reliable, clearer sight longer, because the coating, with its active ingredient, is bonded to the lens
- The coating **retains its effectiveness** for at least 25 washings, allowing workers to wear their eyewear longer
- The coating **can be disinfected** with diluted bleach soaking or alcohol wipes without losing its anti-fog performance
- Workers can **feel confident** wearing Scotchgard™ Anti-Fog coated eyewear because it meets the requirements of EN168 and AS/NZS 1337.1



* Based on 3M internal testing per EN168 test method when compared with traditional anti-fog coatings.

Get out of the fog with a new family of eyewear.

3M™ Solus™ 1000 Series Eyewear



Replacements



3M™ Goggle Gear 500 Series



Product No.	Product Description	Packaging	Impact Rating
S1201SGAF	3M™ Solus™ 1000 Series, Green/Black Eyewear with Clear Scotchgard™ Anti-Fog Lens	1 pair/bag, 20 bags/box	AS/NZS 1337.1 Medium Impact
S1202SGAF	3M™ Solus™ 1000 Series, Green/Black Eyewear with Grey Scotchgard™ Anti-Fog Lens	1 pair/bag, 20 bags/box	AS/NZS 1337.1 Medium Impact
70071694551	3M™ Solus™ 1000 Replacement Foam Gasket	1pair/bag, 10 bags/box	Not required
70071694569	3M™ Solus™-Strap Replacement Strap	1pair/bag, 10 bags/box	AS/NZS 1337.1 Medium Impact goggle
GG501SGAF	3M™ Goggle Gear, 500 Series Clear Scotchgard™ Anti-Fog Lens	1pair/bag, 10 bags/box	AS/NZS 1337.1 Medium Impact (Dustproof and Splashproof)

How to

Attach strap to Eyewear



Attach temple to Eyewear



Attach strap to Goggle Gear



Foam gasket has small vents to help reduce fogging



WARNING

These eye and face protection products help provide limited eye and face protection. **Misuse or failure to follow warnings and User Instructions may result in serious potential injury, including blindness or death.** For proper use, selection and applications against flying particles, optical radiation and/or splash, see supervisor, read *User Instructions* and warnings on the package or call 3M PSD TechAssist in Australia at 1800 024 464. In New Zealand, call Technical Service at 0800 364 357.

For more information

AUSTRALIA

TechAssist Helpline 1800 024 464
 TechAssist Email: techassist@mmm.com
 Customer Service 1300 363 656
 Website www.3m.com/au/PPESafety

NEW ZEALAND

TechAssist Helpline 0800 364 357
 Customer Service 0800 252 627
 Website www.3m.com/nz/PPESafety



Personal Safety Division
 3M Australia Pty Limited
 Building A, 1 Rivett Road
 North Ryde NSW 2123

3M New Zealand Limited
 94 Apollo Drive, Rosendale
 Auckland 0632

© 3M 2016. All rights reserved.
 3M, Solus and Scotchgard are trademarks of 3M Company.

PB7777.04.16