



Automotive Aftermarket Division

3M™ 443SA Trizact Fine Finishing Discs

1) Part Numbers

Part number	Item	Grade	Dimension	Units per pack	Units per case
51131	Fine finishing discs	6000	75mm	15	4
51130		6000	150mm		
50415		6000	75mm		
50414		6000	150mm		
50079		6000	32mm	100	10

2) Description and end uses

3M 443SA Trizact Blending Discs are revolutionary structured abrasives for keying paint for the preparation of paint prior to the blending process. The discs have pyramid or triangular block structures which contain multiple layers of fine grade abrasive mineral. As the abrasive wears, sharp mineral is continuously exposed. The result is a consistent smooth finish and exceptional life.

3) Physical Properties

150 mm, 75 mm and 32mm discs

Foam backed abrasive disc with Hookit facing in 150 mm, 75 mm and 32mm diameters.

Product highlights:

- 0.5 micron finish – 1/3 of the finish of Microfine 2000 Wetordry
- Very easy to compound
- Reduces compounding time by up to 80% and total refinish time by an average of 30%
- Less mess
- Much less heat build-up in the compounding stage



4) Directions for Use

- Use with a fine action D/A sander (5 or 3 mm orbit) fitted with a soft Hookit back-up pad
- Use direct on the back-up pad when sanding flat areas and for contoured surfaces add the soft interface pad (PN 05774)
- Remove defects as normal with 260L P1500/1200 or Microfine Wetordry grade 2000/1500 or 9 micron or 2000 Wetordry scalloped discs
- Wipe off the sanding debris then wet the area with a pump spray bottle, also wet the disc face. The disc should not be allowed to run dry
- Use water or soapy water only. Do not use solvent or water-based degreaser
- do not leave soaking in water bucket
- Using medium pressure sand over the area until flatting scratches are no longer visible. You can check this by cleaning the area with a rubber squeegee. A small amount of practise will be needed to judge how long to sand to remove the flatting scratches. This will be dependent on previous grade used, paint hardness, orbit of machine, etc.
- Compound with Fast Cut Plus Compound/Fine Compound or the Finesse-it system. Compounding will take only a few seconds
- Finally use 3M 09376 Perfect-it III Extra Fine Polish with the soft 050488 Polishing Pad to remove any bloom and leave a perfect 'just painted' finish
- Use 3M Perfect-it III High Performance cloths after the compounding and polishing stages to achieve an easy, scratch free clean up. A good tip for the absolute best finish is to use different coloured wipes for each stage to avoid cross-contamination

5) Storage

It is recommended that all Coated Abrasive Products should be stored at constant levels of temperature and humidity within the ranges of 18-22°C, 50-65% RH. They should be kept away from damp (or cold) walls, windows or floors to avoid possible moisture absorption. Equally, storage adjacent to heat sources, eg steam pipes, radiators, hot air ducts, ovens, etc., should be avoided.

Product is best stored in original packaging until ready for use Shelf life indefinite under these conditions.

6) Safety

Whenever possible, sanding should be carried out in a well-ventilated area and it is strongly recommended that suitable goggles, dust mask and gloves are worn.

Discs should be used only on machines with a suitable support pad designed for the purpose and maintained in good condition at all times.



Technical Data Sheet

Effective: 04/05/2017

Supersedes: 08/02/2010

The abrasive discs should extend symmetrically to no more than 2 mm beyond the outer rim of the support pad.

Damaged or misshapen abrasive discs or support pads should not be used.

Discs and pads should not be modified in any way. They should be used only in their original size and shape, as supplied.

It is recommended that discs be used only on support pads that are clearly marked with maximum permitted running speed. The speed stated should not be exceeded.

Machines should be operated with the disc making the shallowest angle possible with the work piece.

Care should be taken to ensure that discs without a centre hole are mounted centrally on the support pad.

When not in use disc sanding machine should be placed in a stand designed for the purpose or, alternatively, positioned on their backs. They must not be placed with the disc or pad face in contact with the floor or workbench.

3M™ 443SA Trizact Fine Finishing Discs is designed FOR PROFESSIONAL INDUSTRIAL USE ONLY.

7) Disclaimer

All statements, technical information and recommendations are based on tests we believe to be reliable but the accuracy or completeness thereof is not guaranteed. Please ensure before using our product that it is suitable for your intended use. All questions of reliability relating to this product are governed by the Terms of Sale subject, where applicable, to the prevailing law.



Effective: 04/05/2017

Technical Data Sheet

Supersedes: 08/02/2010

For Additional Health and Safety Information

Denmark

3M a/s
Automotive Aftermarket
Hannemanns Allé 53
2300 København S
Tel: 43 48 01 00
3mkundeservicedk@mmm.com
www.3MAuto.dk

Finland

Suomen 3M Oy
Automotive Aftermarket
Keilaranta 6
02150 Espoo
Tel: 09 5252 1
tilaukset@mmm.com
www.3M.fi/autotuotteet

Norway

3M Norge AS
Automotive Aftermarket
Kanalveien 2
2004 Lillestrøm
Telefon: 06384
www.3m.no/auto
kundeservice@mmm.com

Sweden

3M Svenska AB
Automotive Aftermarket
Bileftermarknad
19189 Sollentuna
Tel. 08-922100
kundeservice@mmm.com
3M.se/bileftermarknad