

Commercial Branding and Transportation

3M™ Prestige 70 Exterior Window Film

Solar Control Window Film

Product Bulletin

Product Description

3M™ Prestige 70 Exterior is a multilayer, metal free, spectrally selective, solar control film with a durable scratch-resistant surface and a weather stable acrylic adhesive.

Applications

3M™ Prestige 70 Exterior is intended for exterior application on flat glass substrates.

Typical Properties

The values displayed are the results of illustrative lab test measurements made according to the indicated external norm and shall not be considered as a commitment from 3M.

| Product construction | |
|----------------------|----------------------------|
| Material base | Multi-layered PET/PMMA |
| Adhesive | Pressure sensitive acrylic |
| Protective liner | Siliconized PET |

| Typical Performance Properties according to EN 410 | | | | | | | | | | |
|--|-----------|----------------------|----------------------|--------------|-----------------------------|----------------|----------------------------|----------|---------------------|-----------------|
| Glass type | Film Type | Visible Light | | | Total Solar Energy Rejected | G Value (SHGC) | LSG (Light to solar gain)* | UV Block | Heat Gain Reduction | Glare Reduction |
| | | Reflected (interior) | Reflected (exterior) | Transmission | | | | | | |
| Single Pane | | % | % | % | % | | | % | % | % |
| Clear | No Film | 9 | 8 | 89 | 19 | 0.81 | 1.1 | 40 | NA | NA |
| | PR 70 EX | 7 | 7 | 72 | 51 | 0.49 | 1.5 | 99.9 | 40 | 19 |
| Tinted | No Film | 6 | 5 | 53 | 39 | 0.61 | 0.9 | 82 | NA | NA |
| | PR 70 EX | 5 | 6 | 43 | 62 | 0.38 | 1.1 | 99.9 | 38 | 19 |
| Double Pane | | | | | | | | | | |
| Clear | No Film | 15 | 15 | 79 | 30 | 0.70 | 1.1 | 55 | NA | NA |
| | PR 70 EX | 14 | 12 | 64 | 59 | 0.41 | 1.6 | 99.9 | 41 | 19 |
| Tinted | No Film | 13 | 8 | 47 | 51 | 0.49 | 1.0 | 85 | NA | NA |
| | PR 70 EX | 13 | 7 | 38 | 71 | 0.29 | 1.3 | 99.9 | 41 | 19 |

*Transmission/G

User Information

Shelf Life & Storage (prior to application)

Shelf life is 5 years from the manufacturing date. Material should be stored in its original packaging, laying in a horizontal orientation, away from direct sunlight. Heavy objects should not be placed on top of it to avoid damaging the product. Recommended storage conditions are 21°C and 40 – 50% relative humidity. Avoid extreme temperature ranges in storage.

The shelf life as defined above remains an indicative and maximum data, subject to many external and non-controllable factors. It may never be interpreted as warranty.

Application

These are indicative values for 3M™ Window Film products.

| | |
|-------------------------|---|
| Recommended substrate | Glass (as described in EN 15755-1) |
| Recommended surface | Flat to simple curved |
| Application method | Suitable for wet application or dry semi-automatic lamination |
| Application temperature | From +8°C to +45°C |
| Application guidelines | Check the weather forecast when planning the application. Do not install during precipitation or if the exterior temperature should drop below 0°C within 15 days after installation. |
| Service temperature | From -40°C to +80° C (not for extended periods of time at the extremes) |
| Edge sealing | Recommended for horizontal applications. Not necessary for vertical applications except where moisture can accumulate for an extended time. |
| Drying Time | Final adhesion is reached after approximately 8 - 10 days at 18°C and dry conditions. |

Maintenance and Cleaning

Use a cleaning agent designed for high-quality glass surfaces. The cleaning agent must be wet and non-abrasive with a pH value between 6 and 8 (neither strongly acidic nor strongly alkaline).

Health and Safety



WARNING

To help reduce the risk of personal injury and/or property damage associated with glass breakage, when working on or near glass surfaces, always use appropriate personal protective equipment.

Tools and Equipment Usage

When using any equipment, always follow the manufacturer's instructions for safe operation.

Chemicals

When handling any chemical products, read the manufacturers' container labels and the Safety Data Sheets (SDS) for important health, safety, and environmental information.

[Follow this link to obtain SDS sheets for 3M products.](#)

[Follow this link to obtain information about substances of very high concern \(SVHC\) for EU products.](#)

Warranty Information

Technical Information

Technical information, guidance, and other statements provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license to any intellectual property rights is granted or implied with respect to this technical information.

Product Selection and Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment, reviewing all applicable regulations and standards, and reviewing the product label and use instructions. Failure to properly evaluate, select, and use a 3M product in accordance with instructions or to meet all applicable safety regulations may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer

Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. Please refer to the Warranty Bulletin for 3M™ Window Films (Flat Glass Applications) and 3M™ Impact Protection Attachment (IPA) Sealant for complete details on warranty coverage, which can be obtained by contacting your 3M Authorized Window Film Dealer or your local 3M sales representative. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability

Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

All questions of warranty and liability relating to this product are governed by the terms and conditions of the sale, subject, where applicable, to the prevailing law. 3M Commercial Branding and Transportation products are not tested against automotive manufacturer specifications!

3M is a trademark of 3M. All other trademarks are the property of their respective owners.

3M United Kingdom PLC

Commercial Branding and Transportation
Cain Road
Bracknell, RG12 8HT
UK

© 3M 2026. All rights reserved.