



Automotive Aftermarket Division

3M™ 08475 Seam Sealer Tape

1) Part Numbers

08475

2) Description and end uses

A light green rubber tape with a removable liner for application over factory lap weld and hem flange joints, where a paintable seam sealer tape is required to seal and provide a factory like repair.

3) Physical Properties

Backing: Light green rubber

Adhesive: Acrylic

Liner: Easy-release paper

Roll Length: 10 yards (9.1 cm)

Roll Format: Reverse wound (liner facing out)

		ASTM TEST METHOD
Adhesion to Liner:	2.3 oz./in. width (2.5 N/100mm)	D-3652
Total Thickness:	3.4 mils (0.9mm)	D-3759
Elongation at Break:	80%	D-3759
Adhesion to Steel:	22 oz./in. width (24N/100mm)	D-3652



Technical Data Sheet

Effective: 19/08/2020 Supersedes: 01/06/2000

FEATURES	ADVANTAGES	BENEFITS
Rubber backing	Highly conformable	Duplicates factory appearance Provide reliable seal
Solvent activated adhesive system	Allows re-positioning prior to paint application	Ease of use Reliable bond

4) Directions for Use

It is recommended that the surface temperature be at least 40°F (4°C) or above. The ability of the pressure sensitive adhesive to adhere depends on how warm, clean, and dry the surface is to which it is applied.

Do not use on or with self-etching primers, without properly sealing first.

Do not apply directly to bare metal surfaces.

Bond of seam sealer tape is completed by solvents present in the paint system.

5) Storage

Storage Conditions: Not recommended to exceed 18 months of storage under normal conditions:

- A. Store in a clean dry place
- B. Store at room temperature (70°F or 21°C)
- C. Store at 40-50% relative humidity
- D. Rotate your stock

3M™ 08475 Seam Sealer Tape is designed FOR PROFESSIONAL INDUSTRIAL USE ONLY.

6) Disclaimer

All statements, technical information and recommendations are based on tests we believe to be reliable as at the date of hereof, but the accuracy or completeness thereof is not guaranteed. Please ensure before using the product that it is suitable for your intended use. Since the conditions and methods of use of the product and of the information referred to herein are beyond our control, other than for fraudulent misrepresentation, 3M expressly disclaims any and all liability as to any results obtained or arising from any use of the product or reliance on such information.



Technical Data Sheet

Effective: 19/08/2020 Supersedes: 01/06/2000

For Additional Health and Safety Information

<p>3M United Kingdom plc Automotive Aftermarket 3M Centre, Cain Road, Bracknell, RG12 8HT Tel: +44 (0)161 237 6391 aadukenquiries@mmm.com www.3Mbodyshop.co.uk</p>	<p>3M Ireland Limited Automotive Aftermarket The Iveagh Building Carrickmines Park Carrickmines , Dublin 18 Tel: +353 12160301 aadukenquiries@mmm.com www.3Mbodyshop.co.uk</p>	<p>3M Denmark a/s Automotive Aftermarket Hannemanns Allé 53 2300 København S Tel: +45 43480100 aadukenquiries@mmm.com www.3MAuto.dk</p>
<p>3M Finland, Suomen 3M Oy Automotive Aftermarket Keilaranta 6 02150 Espoo Tel: 09 5252 1 aadukenquiries@mmm.com www.3M.fi/autotuotteet</p>	<p>3M Svenska AB Automotive Aftermarket Herrjärva torg 4 170 67 Solna Tel: 08-922100 aadukenquiries@mmm.com www.3M.se/bileftermarkad</p>	<p>3M Norge AS Automotive Aftermarket Kanalveien 2 2004 Lillestrøm Tel: 06384 aadukenquiries@mmm.com www.3m.no/auto</p>
<p>3M Latvija K.Ulmana 5 Riga, LV-1004 Tel: +371 67066120 aadukenquiries@mmm.com www.3m.lv</p>	<p>3M Eesti OU Pärnu mnt. 158 11317 Tallinn Tel: +372 6 115 902 aadukenquiries@mmm.com www.3m.ee</p>	<p>3M Lietuva A.Goštauto str. 40 A LT-01112 Vilnius Tel: +370 5 2160780 aadukenquiries@mmm.com www.3m.lt</p>

© 3M 2020. 3M is a trademark of the 3M company. All rights reserved