



Automotive Aftermarket Division

3M™ 08568 Body Caulking Sealer

1) Part Numbers

08568 : 300 mm x 6 mm (60 strips / box)

2) Description and end uses

3M™ 08568 is a thumbing compound in preformed strips for sealing all openings in the car body, gaps around cables, tail lights.

Main product features:

- Preformed strips
- Easily thumbed.
- Soft, non-hardening.
- Completely waterproof.
- Will not shrink.
- Good adhesion.
- No oil migration.
- Can be painted over.

3) Physical Properties

Base	Polybutene
Colour	Grey
Solvent	None
Consistency	Extended Putty
Solids content	100%
Service Temperature range	- 30°C to + 70°C
VOC	No solvent
Storage conditions	Cool dry place. Best results are obtained when material is stored and applied at room temperature, 15 to 30°C. Storage temperature must not exceed 50°C.
Shelf life	24 months from date of manufacture under normal storage conditions.



Technical Data Sheet

Effective: 18/08/2020 Supersedes: 20/01/1999

4) Directions for Use

For sealing trunk seams, remove old sealer using 3M™ 08984 General Purpose Adhesive Cleaner if necessary.

Make sure seam is clean and dry. Press strip firmly into place and smooth with finger or tool.

For large opening several strips or pieces may be rolled together.

5) Storage

Store at room temperature. Rotate stock on a “first-in-first-out” basis. When stored at the recommended conditions in original, unopened containers, this product has a shelf life of

12 months. Use in a well-ventilated area.

6) Safety

Please refer to the Material Safety Data Sheet or contact your local 3M™ Toxicology Department.

3M™ 08568 Body Caulking Sealer is designed FOR PROFESSIONAL INDUSTRIAL USE ONLY.

7) Disclaimer

All statements, technical information and recommendations are based on tests we believe to be reliable as at the date of hereof, but the accuracy or completeness thereof is not guaranteed. Please ensure before using the product that it is suitable for your intended use. Since the conditions and methods of use of the product and of the information referred to herein are beyond our control, other than for fraudulent misrepresentation, 3M expressly disclaims any and all liability as to any results obtained or arising from any use of the product or reliance on such information.



Technical Data Sheet

Effective: 18/08/2020 Supersedes: 20/01/1999

For Additional Health and Safety Information

<p>3M United Kingdom plc Automotive Aftermarket 3M Centre, Cain Road, Bracknell, RG12 8HT Tel: +44 (0)161 237 6391 aadukenquiries@mmm.com www.3Mbodyshop.co.uk</p>	<p>3M Ireland Limited Automotive Aftermarket The Iveagh Building Carrickmines Park Carrickmines , Dublin 18 Tel: +353 12160301 aadukenquiries@mmm.com www.3Mbodyshop.co.uk</p>	<p>3M Denmark a/s Automotive Aftermarket Hannemanns Allé 53 2300 København S Tel: +45 43480100 aadukenquiries@mmm.com www.3MAuto.dk</p>
<p>3M Finland, Suomen 3M Oy Automotive Aftermarket Keilaranta 6 02150 Espoo Tel: 09 5252 1 aadukenquiries@mmm.com www.3M.fi/autotuotteet</p>	<p>3M Svenska AB Automotive Aftermarket Herrjärva torg 4 170 67 Solna Tel: 08-922100 aadukenquiries@mmm.com www.3M.se/bileftermarkad</p>	<p>3M Norge AS Automotive Aftermarket Kanalveien 2 2004 Lillestrøm Tel: 06384 aadukenquiries@mmm.com www.3m.no/auto</p>
<p>3M Latvija K.Ulmana 5 Riga, LV-1004 Tel: +371 67066120 aadukenquiries@mmm.com www.3m.lv</p>	<p>3M Eesti OU Pärnu mnt. 158 11317 Tallinn Tel: +372 6 115 902 aadukenquiries@mmm.com www.3m.ee</p>	<p>3M Lietuva A.Goštauto str. 40 A LT-01112 Vilnius Tel: +370 5 2160780 aadukenquiries@mmm.com www.3m.lt</p>

© 3M 2020. 3M is a trademark of the 3M company. All rights reserved