



Automotive Aftermarket Division

3M™ 80349 Extra Fine Compound

1) Part Numbers

80349

2) Description and end uses

3M™ 80349 Extra Fine Compound has been developed specifically for modern scratch resistant paints to give a relative high cut and very high gloss. The product is equally useful on standard paints. For use on refinish on original paints to remove sanding scratches after rectifying paint defects such as dust nibs or orange peel. Can also be used as an alternative to 3M™ Machine Polish after using a coarser compound to restore finish.

3M™ 80349 is a fine automotive compound for use on refinish paints to remove sanding scratches after denibbing or flattening with 3M™ 260L P1500 abrasive discs on 3M™ Microfine 2000 grade Wetordry™ hand sanding paper or 3M™ 9 micron abrasive disc. Use the appropriate size of Trizact™ Fine Finishing Discs 50076 (150 mm), 50075 (75 mm) or 3M™ A5 Trizact™ discs 50079 (32 mm) after sanding to refine the scratches before compounding.

3M™ 80349 is recommended for use with an electric or air driven polisher (1500-2000 rpm) equipped with a 3M™ 01927 Perfect-it™ Wool Compounding Pad on a 3M™ 09552/3 Back-up Pad. The wool pad should be used to give more aggression for the initial compounding stage until the scratches are removed. The pad should then be swapped for a 09550 Foam Compounding Pad to go over the compounded areas to restore gloss. On typical hard scratch resistant paints the harder orange foam will achieve a perfect finish. On softer paints the use of the 3M™ 09738 (soft black) polishing pad is recommended.

3) Physical Properties

Container:	1 litre bottle
Quantity per box:	12 bottles
Flash point:	97.22°C closed cup
Colour:	White
Consistency:	Thick liquid



Technical Data Sheet

Effective: 18/08/2020 Supersedes: 06/06/2007

VOCs:	15% by weight SCAQ443
Viscosity:	12,000-22,000 cps
pH:	7-8.5
% volatile:	70-80% by weight

4) Directions for Use

1. Shaking the bottle before use is not necessary but may help in dispensing the product
2. Sand any defects with 3M™ 260L Hooking Finishing Film Discs P1500 or 3M™ Microfine Wetordry™ grade 2000. For denibbing 3M™ 9 micron discs can be used
3. Refine scratches with the corresponding size of Trizact™ Fine Finishing Discs. On hard scratch resistant paint it will be necessary to sand longer with the Trizact™ discs than on standard paints
4. Apply compound using a rotary polisher and a 01927 Wool Compounding Pad. Use sufficient compound and do not run dry on fresh paint
5. Check afterwards to see if all scratches have been removed by using 3M™ Glass Cleaner/3M™ Control Spray
6. If any scratches are remaining carry out step 4 again
7. If all scratches have been removed replace the 01927 pad with the 09550 Compounding Pad and apply compound. Buff to a high gloss using pressure at first then easing the pressure as the compound is drying out
8. Remove any residue with a 3M™ 60668 High Performance Cloth
9. Clean any spatter from adjacent panels and plastics/rubbers with a soft damp cloth

The above system for using 3M™ 80349 is ideal for removing individual dust nibs, especially as the scratch resistant paints are harder to refinish than standard paints. If, however, a large area rectification is needed then after the sanding and Trizact™ scratch refining stage use 80349 on a 200 mm 3M™ 05704 Superbuff™ III wool compounding pad before changing to the 150 mm 09550 foam compounding pad for the final stage. Alternatively use 3M™ 09374 Fast Cut Compound or 3M™ 50077 Trizact™ Compound on a 09550 Perfect-it™ Foam Compounding Pad then finish with 3M™ 80349 Extra Fine Compound on a clean 09550 foam pad.



Technical Data Sheet

Effective: 18/08/2020 Supersedes: 06/06/2007

5) Storage

Avoid frost
Store upright
Practical shelf life is 2 years

6) Safety

Skin contact: Avoid contact with skin
After contact with skin wash immediately with plenty of soap and water

Ingestion: If swallowed do not induce vomiting. Seek medical advice immediately and show the container or label

3M™ 80349 Extra Fine Compound is designed FOR PROFESSIONAL INDUSTRIAL USE ONLY.

7) Disclaimer

All statements, technical information and recommendations are based on tests we believe to be reliable as at the date of hereof, but the accuracy or completeness thereof is not guaranteed. Please ensure before using the product that it is suitable for your intended use. Since the conditions and methods of use of the product and of the information referred to herein are beyond our control, other than for fraudulent misrepresentation, 3M expressly disclaims any and all liability as to any results obtained or arising from any use of the product or reliance on such information.



Technical Data Sheet

Effective: 18/08/2020 Supersedes: 06/06/2007

For Additional Health and Safety Information

<p>3M United Kingdom plc Automotive Aftermarket 3M Centre, Cain Road, Bracknell, RG12 8HT Tel: +44 (0)161 237 6391 aadukenquiries@mmm.com www.3Mbodyshop.co.uk</p>	<p>3M Ireland Limited Automotive Aftermarket The Iveagh Building Carrickmines Park Carrickmines , Dublin 18 Tel: +353 12160301 aadukenquiries@mmm.com www.3Mbodyshop.co.uk</p>	<p>3M Denmark a/s Automotive Aftermarket Hannemanns Allé 53 2300 København S Tel: +45 43480100 aadukenquiries@mmm.com www.3MAuto.dk</p>
<p>3M Finland, Suomen 3M Oy Automotive Aftermarket Keilaranta 6 02150 Espoo Tel: 09 5252 1 aadukenquiries@mmm.com www.3M.fi/autotuotteet</p>	<p>3M Svenska AB Automotive Aftermarket Herrjärva torg 4 170 67 Solna Tel: 08-922100 aadukenquiries@mmm.com www.3M.se/bileftermarkad</p>	<p>3M Norge AS Automotive Aftermarket Kanalveien 2 2004 Lillestrøm Tel: 06384 aadukenquiries@mmm.com www.3m.no/auto</p>
<p>3M Latvija K.Ulmana 5 Riga, LV-1004 Tel: +371 67066120 aadukenquiries@mmm.com www.3m.lv</p>	<p>3M Eesti OU Pärnu mnt. 158 11317 Tallinn Tel: +372 6 115 902 aadukenquiries@mmm.com www.3m.ee</p>	<p>3M Lietuva A.Goštauto str. 40 A LT-01112 Vilnius Tel: +370 5 2160780 aadukenquiries@mmm.com www.3m.lt</p>

© 3M 2020. 3M, Superbuff, Wetordry, Trizact, Perfect-it and are all trademarks of the 3M company. All rights reserved