



Automotive Aftermarket Division

3M™ 08919 / 3M 08929 - Inner Cavity Wax, Transparent

1) Part Numbers

3M™ 08919 / 1 litre can
3M™ 08929 / 10 litre drum

2) Description and end uses

Transparent inner cavity wax designed to penetrate seams and coat surfaces. It gives a protective flexible coating after drying with excellent rust preventive properties.

3M™ 08919/29 inner cavity wax can be applied to internal cavities requiring rust proofing e.g. inside:

- Doors
- Boots
- Rear wing panels
- Sills
- Chassis legs

Major features:

- Easily applied using the 3M™ 08997/3M 08998 guns
- Good seeping properties: It seeps by capillarity into gaps and along joints
- Good adhesion properties
- Good coverage

3) Physical Properties

Colour :	Transparent
Base :	Wax
Flash point :	Approx. 23°C
Solids content (Typical) :	Approx. 40 %
Service T° range :	-20 to +90°C
Specific gravity :	0.82
Coverage :	8 - 10 m ² /litre
Tack free time :	Approx. 2 hours
Storage conditions :	+ 5°C to 35°C
Practical life :	2 years under normal storage conditions



Technical Data Sheet

Effective: 19/08/2020 Supersedes: 28/10/1994

4) Directions for Use

1. Preparation

* FOR 3M™ 08919: 1 litre can

- Ensure 3M™ 08997 applicator gun is clean and safety holes clear.
- Shake can well before use.
- Connect can via screw top to the 3M™ 08997 spray gun which is equipped with a flexible extension tube.

* FOR 3M™ 08929: 10 litre drum

- Use 3M™ 08998 refill gun.
- Check the pressure cap is filled and connected to the compressed air.
- Choose one of the 3 provided extension tubes (that give different spray patterns) and fix it to the gun.
- The top screw allow to adjust the air/product mixing ratio.

NOTE: The extension tube enables access to the internal parts and thereby, allows easy application in difficult to reach areas.

2. Application method

- Spray using a pressure of 4 to 6 bars (55 to 80 PSI)
- Apply generously while agitating the extension tube
- Clear the gun after use

CAUTION: Do not attempt to paint on top of 3M™ 08919/29.

5) Storage

Store at room temperature in flammables storage area. Rotate stock on a “first-in-first-out” basis. When stored at the recommended conditions in original, unopened containers, this product has a shelf life see container for details. Use in a well-ventilated area.

6) Safety

Please refer to the Material Safety Data Sheet or contact your local 3M™ toxicological department.

3M™ 08919 / 3M 08929 - Inner Cavity Wax, Transparent is designed FOR PROFESSIONAL INDUSTRIAL USE ONLY.



Technical Data Sheet

Effective: 19/08/2020 Supersedes: 28/10/1994

7) Disclaimer

All statements, technical information and recommendations are based on tests we believe to be reliable as at the date of hereof, but the accuracy or completeness thereof is not guaranteed. Please ensure before using the product that it is suitable for your intended use. Since the conditions and methods of use of the product and of the information referred to herein are beyond our control, other than for fraudulent misrepresentation, 3M expressly disclaims any and all liability as to any results obtained or arising from any use of the product or reliance on such information

For Additional Health and Safety Information

3M United Kingdom plc Automotive Aftermarket 3M Centre, Cain Road, Bracknell, RG12 8HT Tel: +44 (0)161 237 6391 aadukenquiries@mmm.com www.3Mbodyshop.co.uk	3M Ireland Limited Automotive Aftermarket The Iveagh Building Carrickmines Park Carrickmines , Dublin 18 Tel: +353 12160301 aadukenquiries@mmm.com www.3Mbodyshop.co.uk	3M Denmark a/s Automotive Aftermarket Hannemanns Allé 53 2300 København S Tel: +45 43480100 aadukenquiries@mmm.com www.3MAuto.dk
3M Finland, Suomen 3M Oy Automotive Aftermarket Keilaranta 6 02150 Espoo Tel: 09 5252 1 aadukenquiries@mmm.com www.3M.fi/autotuotteet	3M Svenska AB Automotive Aftermarket Herrjärva torg 4 170 67 Solna Tel: 08-922100 aadukenquiries@mmm.com www.3M.se/bileftermarkad	3M Norge AS Automotive Aftermarket Kanalveien 2 2004 Lillestrøm Tel: 06384 aadukenquiries@mmm.com www.3m.no/auto
3M Latvija K.Ulmana 5 Riga, LV-1004 Tel: +371 67066120 aadukenquiries@mmm.com www.3m.lv	3M Eesti OU Pärnu mnt. 158 11317 Tallinn Tel: +372 6 115 902 aadukenquiries@mmm.com www.3m.ee	3M Lietuva A.Goštauto str. 40 A LT-01112 Vilnius Tel: +370 5 2160780 aadukenquiries@mmm.com www.3m.lt

© 3M 2020. 3M is a trademark of the 3M company. All rights reserved