



Automotive Aftermarket Division

3M™ 09034/09035 Perfect-it™ Gelcoat Boat Wash

1) Part Numbers

09034 : 473ml
09035 : 946ml

2) Description and end uses

3M™ Perfect-It™ Boat Wash is 3M's best product solution to clean a variety of boat surfaces. The product is a professional strength concentrate. It effectively cleans the surfaces from stem to stern without stripping wax.

3) Physical Properties

Container	Various (See Above)
Colour	Clear/Faint Yellow
Flash Point - °C	No Flash @ 20°C, 38°C, 60°C or 93°C
Viscosity (CPS) Brookfield Viscometer	100 – 1000 cps @ 25°C
Solids Content (Appx.)	0%
Solvent	0.1% VOC

4) Directions for Use

Pour 3 caps full of Boat Wash per gallon of water into a bucket. Apply solution with a soft sponge or soft bristle brush until debris is removed from the surface. Wash the residual boat soap off of the boat surface with a consistent flow of water, completely removing boat soap from the boat. Wipe the boat dry with a clean soft terry cloth/towel, a microfiber detailing cloth or a chamois.

5) Storage

Keep from freezing.



Technical Data Sheet

Effective: 19/08/2020 Supersedes: 25/07/2019

6) Safety

Refer to product label and safety data sheet for health and safety information before using the product.

3M™ Perfect-It™ Boat Wash is designed FOR PROFESSIONAL INDUSTRIAL USE ONLY.

7) Disclaimer

All statements, technical information and recommendations are based on tests we believe to be reliable as at the date of hereof, but the accuracy or completeness thereof is not guaranteed. Please ensure before using the product that it is suitable for your intended use. Since the conditions and methods of use of the product and of the information referred to herein are beyond our control, other than for fraudulent misrepresentation, 3M expressly disclaims any and all liability as to any results obtained or arising from any use of the product or reliance on such information



Technical Data Sheet

Effective: 19/08/2020 Supersedes: 25/07/2019

For Additional Health and Safety Information

<p>3M United Kingdom plc Automotive Aftermarket 3M Centre, Cain Road, Bracknell, RG12 8HT Tel: +44 (0)161 237 6391 aadukenquiries@mmm.com www.3Mbodyshop.co.uk</p>	<p>3M Ireland Limited Automotive Aftermarket The Iveagh Building Carrickmines Park Carrickmines , Dublin 18 Tel: +353 12160301 aadukenquiries@mmm.com www.3Mbodyshop.co.uk</p>	<p>3M Denmark a/s Automotive Aftermarket Hannemanns Allé 53 2300 København S Tel: +45 43480100 aadukenquiries@mmm.com www.3MAuto.dk</p>
<p>3M Finland, Suomen 3M Oy Automotive Aftermarket Keilaranta 6 02150 Espoo Tel: 09 5252 1 aadukenquiries@mmm.com www.3M.fi/autotuotteet</p>	<p>3M Svenska AB Automotive Aftermarket Herrjärva torg 4 170 67 Solna Tel: 08-922100 aadukenquiries@mmm.com www.3M.se/bileftermarkad</p>	<p>3M Norge AS Automotive Aftermarket Kanalveien 2 2004 Lillestrøm Tel: 06384 aadukenquiries@mmm.com www.3m.no/auto</p>
<p>3M Latvija K.Ulmana 5 Riga, LV-1004 Tel: +371 67066120 aadukenquiries@mmm.com www.3m.lv</p>	<p>3M Eesti OU Pärnu mnt. 158 11317 Tallinn Tel: +372 6 115 902 aadukenquiries@mmm.com www.3m.ee</p>	<p>3M Lietuva A.Goštauto str. 40 A LT-01112 Vilnius Tel: +370 5 2160780 aadukenquiries@mmm.com www.3m.lt</p>

© 3M 2020. 3M and Perfect-It are trademarks of the 3M company. All rights reserved