



Automotive Aftermarket Division

3M™ 50410 Weld Thru Coating

1) Part Numbers

50410

2) Description and end uses

Weld Thru II: 377 ml Aerosol spray can

3M™ 50410 Weld Thru II Coating is a sprayable, weldable zinc-based coating designed to prevent corrosion from forming between welded metal panels.

- Fast drying
- Easy to weld through without altering welder settings
- Excellent and consistent spray-ability
- Efficient corrosion protection
- Good adhesion to bare metal

3M™ 50410 is designed to be used for both spot welding and MIG welding operations in the automotive repair process.

It helps restoring the original zinc-based protection used in automotive construction and will dramatically reduce risk of corrosion development on welded steel parts and panels.

A 500 hours salt spray exposure (ASTM B117) showed significant reduction in corrosion over untreated metal

When compared to a copper-based weld through coating, after 250 hours salt spray exposure, the zinc-based 3M™ 50410 coating showed a far better protection of the metal sheet than the copper-based product.



Technical Data Sheet

Effective: 19/08/2020 Supersedes: 15/06/2007

3) Physical Properties

Colour	Silver grey
Packaging	377ml (361g) aerosol can
Tack Free Time	10 minutes (at 23°C, 50% RH)
Solvent	Acetone
Flash Point	-104°C, Closed cup
% Solids (Typical)	64 %
V.O.C.	700 g/l
Specific Gravity	0.796
Storage conditions	+ 5°C to + 30°C
Shelf Life	24 months under normal storage conditions (date of manufacturing in American style on bottom of can)

4) Directions for Use

- Remove all paint, rust, oil and other contaminant from the surface to be coated. Sand remaining coatings with P60-P120 grit abrasive.
- Clean and degrease surface with 3M™ 08984.
- Shake can well for approx. 1 minute after agitator ball is heard. Shake frequently during use.
- Hold can about 15cm from surface to be coated. Apply to all bare surfaces and edges in the vicinity of the intended weld.
- Two thin layers are recommended to obtain the correct thickness and optimum corrosion protection.
- Weld after product has dried (about 10 to 20 minutes).
- Invert can and spray to purge nozzle.

Note:

- Do not apply filler or other topcoat over 3M™ 50410 as this may causes lifting. It is recommended to remove 3M™ 50410 from any surfaces to be painted.
- Spot weld in the first 24 hours. Longer time reduces conductivity.

5) Storage

Store at room temperature in flammables storage area. Rotate stock on a “first-in-first-out” basis. When stored at the recommended conditions in original, unopened containers, this product has a shelf life see container for details. Use in a well-ventilated area.



Technical Data Sheet

Effective: 19/08/2020 Supersedes: 15/06/2007

6) Safety

Please refer to the Material Safety Data Sheet or contact your local 3M™ Toxicology Department.

Pressurised container. Protect from sunlight and do not expose to temperature exceeding 50°C. Do not pierce or burn, even after use. Do not spray on a naked flame or incandescent material.

3M™ 50410 Weld Thru II Coating is designed FOR PROFESSIONAL USE ONLY.

7) Disclaimer

All statements, technical information and recommendations are based on tests we believe to be reliable as at the date of hereof, but the accuracy or completeness thereof is not guaranteed. Please ensure before using the product that it is suitable for your intended use. Since the conditions and methods of use of the product and of the information referred to herein are beyond our control, other than for fraudulent misrepresentation, 3M expressly disclaims any and all liability as to any results obtained or arising from any use of the product or reliance on such information.



Technical Data Sheet

Effective: 19/08/2020 Supersedes: 15/06/2007

For Additional Health and Safety Information

<p>3M United Kingdom plc Automotive Aftermarket 3M Centre, Cain Road, Bracknell, RG12 8HT Tel: +44 (0)161 237 6391 aadukenquiries@mmm.com www.3Mbodyshop.co.uk</p>	<p>3M Ireland Limited Automotive Aftermarket The Iveagh Building Carrickmines Park Carrickmines , Dublin 18 Tel: +353 12160301 aadukenquiries@mmm.com www.3Mbodyshop.co.uk</p>	<p>3M Denmark a/s Automotive Aftermarket Hannemanns Allé 53 2300 København S Tel: +45 43480100 aadukenquiries@mmm.com www.3MAuto.dk</p>
<p>3M Finland, Suomen 3M Oy Automotive Aftermarket Keilaranta 6 02150 Espoo Tel: 09 5252 1 aadukenquiries@mmm.com www.3M.fi/autotuotteet</p>	<p>3M Svenska AB Automotive Aftermarket Herrjärva torg 4 170 67 Solna Tel: 08-922100 aadukenquiries@mmm.com www.3M.se/bileftermarkad</p>	<p>3M Norge AS Automotive Aftermarket Kanalveien 2 2004 Lillestrøm Tel: 06384 aadukenquiries@mmm.com www.3m.no/auto</p>
<p>3M Latvija K.Ulmana 5 Riga, LV-1004 Tel: +371 67066120 aadukenquiries@mmm.com www.3m.lv</p>	<p>3M Eesti OU Pärnu mnt. 158 11317 Tallinn Tel: +372 6 115 902 aadukenquiries@mmm.com www.3m.ee</p>	<p>3M Lietuva A.Goštauto str. 40 A LT-01112 Vilnius Tel: +370 5 2160780 aadukenquiries@mmm.com www.3m.lt</p>

© 3M 2020. 3M is a trademark of the 3M company. All rights reserved