

| Product        | Image   | Description   | Applications  | Usage Characteristics  |
|----------------|---|---|---|--|
| Finish Line    |    | 3.5mm wide single high strength filament<br>Green carrier   | Edge trims on single or multiple layer films and laminated graphics                           | <ul style="list-style-type: none"> <li>Filament is extremely strong and can only be cut with a knife</li> <li>Will cut multiple film layers e.g. laminated prints</li> <li>Do not stretch tape when creating curves</li> <li>Best used for gentle curves</li> </ul>  |
| Design Line    |    | 3.5mm wide single ultra-fine filament<br>Green carrier  | Edge trims on single layer films with intricate designs and/or sharp curves                   | <ul style="list-style-type: none"> <li>Ultra-fine filament can be snapped by hand</li> <li>Use only for single layer graphics e.g. 1080</li> <li>Pull filament with care to avoid snapping</li> <li>Tape can be stretched slightly when creating curves</li> <li>Best option for very tight curves</li> <li>Thinner filament creates sharpest cut</li> </ul> |
| Tri Line       |    | 3 Ultra-fine filaments<br>2 versions <ul style="list-style-type: none"> <li>6mm filament spacing</li> <li>9mm filament spacing</li> </ul> Green carrier | Creating 6mm and 9mm gaps and/or pinstripes on single layer films                             | <ul style="list-style-type: none"> <li>Ultra-fine filament can be snapped by hand</li> <li>Use only for single layer graphics e.g. 1080</li> <li>Pull filament with care to avoid snapping</li> <li>Tape can be stretched slightly when creating gentle curves</li> </ul>  |
| Bridge Line    |    | 12.7mm wide single high strength filament<br>Green carrier  | Creating trims in wide gaps such as between doors or panel seams                              | <ul style="list-style-type: none"> <li>Filament is extremely strong and can only be cut with a knife</li> <li>Will cut multiple film layers e.g. laminated prints</li> <li>Do not stretch tape when creating curves</li> <li>Best used for gentle curves</li> </ul>  |
| Perf Line      |    | 6.35mm wide single high strength filament<br>Green carrier  | Edge trims of perforated window graphics to create a 3mm gap between graphic and rubber seals | <ul style="list-style-type: none"> <li>Filament is extremely strong and can only be cut with a knife</li> <li>Will cut multiple film layers e.g. laminated prints</li> <li>Do not stretch tape when creating curves</li> <li>Best used for gentle curves</li> </ul>  |
| PPF Line       |  | 2 part tape <ul style="list-style-type: none"> <li>Cutting tape</li> <li>Cover tape</li> </ul> Clear carrier  | Edge trimming of Paint Protection Film  | <ul style="list-style-type: none"> <li>Will cut multiple film layers</li> <li>Suitable for wet application</li> <li>Eliminates need for pre-cut kits or templates</li> </ul>   |
| Precision Line |  | 3.5mm wide single metal filament<br>Blue carrier  | Edge trimming tough films   | <ul style="list-style-type: none"> <li>Suitable for tough films such as reflective, polyester, chrome, metallic and all other vinyl and non-vinyl films</li> <li>Will cut multiple film layers e.g. laminated prints</li> </ul>  |