


















3M™ Plate Mounting Tapes

	18 Series Tapes	17 Series Tapes	15 Series Tapes	10 Series Tapes	13 Series Tapes	19 Series Tapes	12 Series Tapes	11 Series Tapes
	<i>Firm</i>  <i>Soft</i>							
15 Thou Tapes	E1815	E1715	E1515, E1515H	E1015, E1015H	E1315, E1315H	E1915, 1915H, E1915S		E1115
20 Thou Tapes	L1820, E1820	L1720, E1720	L1520, E1520	L1020, E1020, E1020H	L1320, E1320	L1920S, E1920, E1920S	L1220, E1220	L1120, E1120
40 Thou Tapes	E1840H			E1040				
60 Thou Tapes	E1860H			E1060, E1060H				
								
Tape selection & application	Plate contains mostly solids in a combination of solid and halftone images.	Slightly more solids in a combination of solid and halftone images.	High speed printing with fine type reverses and expanded colour gamut.	Solid and halftone areas are equally important.	High speed printing of combination work when halftone areas exceed solid.	High speed when process and halftone images predominate.	Low density for high speed process work and screen printing.	Low density for high quality process work and screen printing.
Product Identification	 Blue	 Teal	 Purple	 White	 Yellow	 Pink	 Orange	 Tan/Beige