



# 3M™ Liqui-Cel™ EXF-8×20 Industrial Series Membrane Contactor

## Typical Properties


Membrane Characteristics	
Cartridge Configuration	Extra-Flow with Center Baffle
Liquid Flow Guidelines	1 – 11 m <sup>3</sup> /hr (5 – 50 gpm)
Membrane Type	XIND Fiber
	Recommended for CO <sub>2</sub> removal from liquid and other gas transfer applications
Membrane/Potting Material	Polypropylene / Epoxy
Priming Volume (approximate)	
Shellside	6.7 L (1.8 gal)
Lumenside	5.2 L (1.4 gal)

Pressure Guidelines*	
Maximum Shellside <b>LIQUID</b> Working Temperature/ Pressure	25°C, 4.8 barg (77°F, 70 psig) 40°C, 2.1 barg (104°F, 30 psig)
If no vacuum is used, 1.0 barg (15 psig) can be added to pressures above. If operating using air sweep, the liquid or air temperature should not exceed 30°C for any length of time. Exceeding 30°C will reduce contactor life.	
Maximum Applied Gas Pressure	2.1 barg at 25°C (30 psig at 77°F)
Maximum applied gas pressure is for integrity testing at ambient temperatures. Normal operating pressures are typically lower.	
* See Operating Guide for complete temp/pressure limits for housings and membrane. <b>Note:</b> Liquid pressure should always exceed gas pressure.	

Housing Options and Characteristics	
Material	<b>PVC housing</b> Due to the nature of the material, scratches, blemishes and other marks may be visible on the housing surface. These do not impact contactor function. <b>Engineering thermoplastic end caps</b>
Port Connections	
Shellside (Liquid Inlet/Outlet)	1 Inch Female NPT 1.5 Inch Grooved pipe fitting Note: both options are standard on 1 end cap
Lumenside	1 Inch Female NPT



Weight (approximate)	
Dry	13 kg (28 lbs)
Water-filled (shellside)	19 kg (43 lbs)

Regulatory	
Complies with the limits as set by RoHS Directive 2011/65/EU Annex II; recasting 2002/95/EC.	



All dimensions are nominal values. See 3M.com/Liqui-Cel for all housing drawings.

# 3M™ Liqui-Cel™ EXF-8×20 Industrial Series Membrane Contactor



Curves represent nominal values using water at 25° C. Characteristics may change under different operating conditions.

Test conditions:  
CO<sub>2</sub> Removal: Air sweep mode at 5 scfm.

**Technical Information:** The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

**Product Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

**Warranty, Limited Remedy, and Disclaimer:** Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

3M and Liqui-Cel are trademarks of 3M Company. All other trademarks are the property of their respective owners. © 2017 3M Company. All rights reserved.



ISO 9001



**Separation and Purification Sciences Division**  
13840 South Lakes Drive  
Charlotte, North Carolina  
28273 USA  
Phone: +1 980 859 5400

**3M Deutschland GmbH**  
**Separation and Purification Sciences Division**  
Öhder Straße 28  
42289 Wuppertal Germany  
Phone: +49 202 6099 - 0  
Fax: +49 202 6099 - 241

LC-1034  
Rev. 01/2017

[3M.com/Liqui-Cel](http://3M.com/Liqui-Cel)