

# ANZ Aluminum Repair Procedures

## Sealing and Coating

### Aluminium General Seam Sealer

#### Application: Non-Direct to Metal

1



#### Surface Prep

Cover all bare metal areas with a quality Urethane or Epoxy two part primer. After allowing to cure as per manufacturers recommendations, scuff primer in sealer application areas using a maroon Scotch-Brite™ Hand Pad. Blow off with clean, dry air.

2



#### Clean

Use a clean cloth or paper towel to clean repair area with all purpose cleaner and degreaser followed by a VOC compliant wax and grease remover. **DO NOT spray or saturate seams with cleaner.**

3



#### Apply Seam Sealer

Apply seam sealer over the prepared seam. Tool to re-create OEM appearance.

Visit [www.3m.com.au/aad](http://www.3m.com.au/aad) or [www.3m.co.nz/aad](http://www.3m.co.nz/aad) for more SOPs and videos

**Note: Use caution when working on aluminium parts. Use tools that have been cleaned properly or designated for use on aluminium to reduce potential cross contamination. Do not re-use abrasives that were previously used on steel repairs.**

### Product List ANZ

Scotch-Brite™ Durable Flex Hand Pad, MX-HP, 115mm x 230mm, Very Fine, PN 64659 OR



Scotch-Brite™ 7447 PRO Hand Pads, Very Fine grade, 150mm x 230mm, PN 64926



3M™ All Purpose Cleaner and Degreaser Concentrate, 3.78 litre, PN 38350



3M™ Urethane Seam Sealer, PN 08689, 08684, 08694 or



3M™ MSP Seam Sealer, PN 08370 or



3M™ Multi Purpose Seam Sealer PN 50740



3M™ EZ Sand Multi-Purpose Repair Material, 200mL, PN 05887



### Think About Your Health

3M™ E-A-R™ Skull Screws™ Ear Plug, PN P1300



3M™ Half Facepiece Respirator, PN 07502 with appropriate cartridge



3M™ Lexa™ Protective Eyewear, PN 15200 or 3M Secure Fit AF401SF-AS



For ordering information, contact your 3M Sales Representative