



# ANZ Aluminum Repair Procedures


## Paint Application Systems

### 3M™ PPS™ Paint Preparation System

An innovative, all-in-one disposable system that enables painters to eliminate expensive liquid coating waste left on mixing cups and filters by mixing directly in the PPS cup. Mix, measure, filter, spray and temporarily store your coating materials.



	Part No.	Description
<b>3M™ Accuspray™ Spray Gun Kits</b>		
	16570	Model HG18, 1.8mm
	16577	Model HG14, 1.4mm
	16587	Model HGP (Pressurized)
<b>3M™ Accuspray™ Atomizing Heads</b>		
	16612	1.4mm
	16611	1.8mm
	16609	2.0mm



### Spot Repair

Ideal for spot repairs that require 90ml of material or less.



3M™ PPS™ Kit 90ml Lids and Liners, PN 16028, full diameter 200 micron filters

3M™ PPS™ Kit 90ml Lids and Liners, PN 16328, full diameter 125 micron filters


### 1 Panel Repair

Ideal for small areas that require 180ml of material or less.



3M™ PPS™ Kit 180ml Mini Size, PN 16114, full diameter 200 micron filters


3M™ PPS™ Kit 180ml Mini Size, PN 16314, full diameter 125 micron filters



For ordering information, contact your 3M Sales Representative



## 2 Panel Repair



Ideal for areas that require 400ml of material or less.




3M™ PPS™ Kit 400ml Midi Size, PN 16112,  
full diameter 200 micron filters

3M™ PPS™ Kit 400ml Midi Size, PN 16312,  
full diameter 125 micron filters



## 3 Panel Repair



Ideal for large areas that require 650ml of material or less.




3M™ PPS™ Kit ,650ml Standard Size, PN 16000,  
200 micron filters

3M™ PPS™ 650ml Kit Standard Size, PN 1630,  
full diameter 125 micron filters



## 4 Panel Repair



Ideal for large jobs that require 850ml of material or less.



3M™ PPS™ 850ml Kit Large Size, PN 16024,  
200 micron filters

3M™ PPS™ Kit 850ml Large Size, PN 16325,  
full diameter 125 micron filters



For ordering information, contact your 3M Sales Representative