

**SEALED-BLOK™
SELF RETRACTING LIFELINE**

MAGNETIC RETRACTION CONTROL (MRC)



**PATENT-PENDING MAGNETIC TECHNOLOGY TO
CONTROL LIFELINE RETRACTION SPEED**




THE ULTIMATE IN FALL PROTECTION

PRODUCT SHEET

SEALED-BLOK™ SELF RETRACTING LIFELINE

Traditional
Sealed-Blok



Sealed-Blok
with MRC



*** 3X slower
retraction speed
when compared
to traditional
SRL's**



Demo Video



3400846

SRL with Magnetic Retraction Control (MRC)
.....
50 ft. (15m) of 3/16" (5mm) 316 stainless steel
wire rope with swivel snap hook, stainless steel
carabiner and magnetic retraction.

FEATURES:

- Utilizes magnetic eddy current technology to reduce retraction speed by 3X—greatly reducing the potential for lock-up during uncontrolled retraction.
- Slower retraction speed reduces risk of damage to the paint on a ladder when the lifeline is accidentally released.
- Super corrosion resistant housing for added protection against caustic environments.
- 316SS wire rope for added protection in corrosive environments.



FAST-LINE™ ALLOWS EASY REPLACEMENT OF STAINLESS CABLE

- Trained users can replace cable in the field
- Reduce downtime and costs

