



Fall Protection

One device.

Many fall protection applications.

3M™ DBI-SALA® Nano-Lok™ Wrap Back Self-Retracting Lifeline

Fall protection just got streamlined with the 3M™ DBI-SALA® Nano-Lok™ Wrap Back SRL. Functioning as both a fall protection device and tie-off adapter, it allows safety managers to consolidate multiple equipment capabilities in one versatile solution. The Nano-Lok™ Wrap Back SRL is approved for overhead or foot level tie-off applications.* It connects to beams, rebar walls and other structures that can properly support fall arrest forces—helping protect workers in a wide variety of at-height environments.



*Non-sharp edges only.

► Streamlines equipment selection

Combines fall protection and tie-off capabilities for overhead and foot-level applications (non-sharp edges) into one device.

► Connects easily

Built-in pin-style connector attaches directly to your harness.

► Built to last

Dyneema® fiber 3/4 in. (19 mm) web lifeline and impact-resistant thermoplastic housing help withstand harsh environments.

Learn more at 3M.com/FallProtection



3M Fall Protection
Personal Safety Division
3833 SALA Way
Red Wing, MN 55066 USA

Phone 800-328-6146
Email 3mfallprotection@mmm.com
Web 3M.com/FallProtection

Dyneema® is a trademark of DSM. 3M, DBI-SALA and Nano-Lok are trademarks of 3M and its affiliates.
© 3M 2017. All rights reserved.

Model #	3M™ DBI-SALA® Nano-Lok™ Wrap Back SRLs
3101654	Single-leg SRL with tie-back snap hook x 8 ft. (2.4 m)
3101658	Single-leg SRL with steel rebar hook x 8 ft. (2.4 m)
3101653	Twin-leg SRL with tie-back snap hooks x 8 ft. (2.4 m)
3101659	Twin-leg SRL with steel rebar hooks x 8 ft. (2.4 m)