

Classically cool.

3M[™] Décor Overlaminate 8600M-101, Classic Linen

Effortlessly fresh, with a crisp, uniform pattern.

- ► Adds depth to the look and feel of graphics
- ➤ Designs are printed on the base film a flat surface for superior image quality
- ► Cast vinyl film will not shrink
- ► Guards against scuffs and is cleanable

Take your brand to the surface at 3M.com/WallWraps or call 1-800-328-3908.



▲ Printed on 3M™ Print Wrap Film IJ180mC-10.

