

3M Science.
Applied to Life.™

3M Automotive Aftermarket

3M™ Cubitron™ II Product Range

CUBITRON™ II


CUBITRON™ II



Cuts 30% Faster. Lasts Twice As Long.

3M™ Cubitron™ II DA Discs are a revolutionary advancement in automotive abrasive technology featuring triangular shaped ceramic mineral. As the triangular shaped grain wears, it continually fractures to form sharp points that slice through the substrate, wear evenly and provide extra-long life and consistency.

- Cuts 30% faster than premium abrasives
- Lasts up to twice as long
- Delivers finer, more uniform finish
- Requires less pressure



3M Precision Shaped Grain

3M precision shaped grain in Cubitron™ II DA Discs continuously fractures to form sharp points and edges — slicing cleaner and faster, staying cooler and lasting many times longer.





VS.




Conventional Grain

Conventional ceramic abrasive grain is irregular in shape. Instead of a clean, machining action, the grain “plows” through the metal, causing heat build up, slower cutting and shorter life.




3M™ Cubitron™ II Clean Sanding Hookit™ Abrasive Discs



| Part No. | Size | Grade | Qty |
|----------|-------|-------|--------------|
| 31371 | 150mm | 80+ | 50 Discs/Box |
| 31372 | | 120+ | |

3M™ Cubitron™ II Fibre Roloc™ Discs



| Part No. | Size | Grade | Qty |
|----------|------|-------|--------------|
| 33377 | 50mm | 36+ | 15 Discs/Box |
| 33379 | | 60+ | |
| 33380 | | 80+ | |
| 33389 | 75mm | 36+ | 15 Discs/Box |
| 33391 | | 60+ | |
| 33392 | | 80+ | |

3M™ Cubitron™ II File Belts



| Part No. | Size | Grade | Qty |
|----------|--------------|-------|--------------|
| 33437 | 10mm x 330mm | 36+ | 10 Belts/Box |
| 33439 | | 60+ | |
| 33440 | | 80+ | |
| 33620 | 12mm x 330mm | 36+ | 10 Belts/Box |
| 33621 | | 60+ | |
| 33622 | | 80+ | |
| 33449 | 20mm x 520mm | 36+ | 10 Belts/Box |
| 33451 | | 60+ | |
| 33452 | | 80+ | |

3M™ Cubitron™ II Cut-Off Wheels



| Part No. | Size | Grade | Qty |
|----------|------|-------|--------------|
| 33456 | 75mm | — | 5 Wheels/Box |

3M™ Cubitron™ II Abrasive Fibre Discs



| Part No. | Size | Grade | Qty |
|----------|-------|-------|-------------|
| 33395 | 100mm | 36+ | 5 Discs/Box |
| 33397 | | 60+ | |
| 33398 | | 80+ | |

Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy and Disclaimer: Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

For health and safety information please refer to product labels and Safety Data Sheets.



**3M Automotive
Aftermarket Division**
Building A, 1 Rivett Rd
North Ryde, NSW, 2113

Phone 136-136
Web www.3M.com.au/aad



"LIKE" us on FACEBOOK
www.FACEBOOK.COM/3MCollisionRepairANZ



Subscribe to our channel to watch comprehensive instructional
videos www.youtube.com/3Maadaustralia

3M, Cubitron, Hookit, Roloc and Stikit are trademarks of
3M Company. Please recycle. Printed in Australia.
© 3M 2015. All rights reserved.